

1 2 3 4 5 6 7 8

A

A

B

B

C

C

D

D

E

E

F





F

G

G

H

H



MATERIAL

Insulator : PBT+30% Glass fiber
Contact Pin : Brass

SPECIFICATION

Current Rate : 3 AMP
Insulation Resistance : 100000MΩMin. at DC 500V
Contact Resistance : 20mΩMax. at DC 100mA
Dielectric Voltage : 750V AC for one minute

RoHS
Compliant

HSM 玄茂科技股份有限公司
HSUAN MAO TECHNOLOGY CO., LTD.

APPD.
核准 HELEN
DWG.
製圖 ABBY
DATE 制表日
2011/03/23

SCALE
比例 參考
UNIT
單位 MM
PAGE
張數 1 OF 1

TOLERANCE
容許公差
0 ± 0.30
.00 ± 0.20
ANG. ± 3°
SIZE.
紙張尺寸 A4
REV.
版次 A
PART NAME 品名
2.54mm MINI JUMPER 2P H:6.5mm
CLOSE COVER ROHS LOW-LEAD
PART NO.
料號 C2700-02ABXX00R

1 2 3 4 5 6 7 8