

Search This Product Catalogue

By Keyword

Go

- Telecommunication Access Products
- Product Catalogue for Telecommunication Access Products
- 3M Dynatel Diagnostic Test Equipment
- Cabinets
- Copper Splicing
- Fiber and Copper Closures and Terminals
- Fiber Cable Assemblies
- Fiber Connectors, Splices, Couplings and Cable Assemblies
- Fiber Mgt System
- Locating and Marking
- Quante Products
- Related Products

[Product Catalogue for Telecommunication Access Products](#) [Fiber and Copper Closures and Terminals](#) [Copper Closures and Terminals](#) [Direct Buried](#) [Better Buried \(Gravity Poured\)](#)

3M 8882 Inline Better Buried Closure Kit BB3X12-SB/2DC-LHS

 [Printer-friendly format](#)



3M 8882 Better Buried Closures are rigid body splice closures designed for direct burial. When filled with 3M 8882 Reenterable Encapsulating Compound, the closure can be reentered for splice rework.

[\[click to enlarge\]](#)

3M Order Code : 80 - 6108 - 6338 - 5
Bar Code : 0 00 51138 57551 9

Additional Information

The Better Buried and 89 Series Closures use a gravity fill method of encapsulating and protecting the cable splice. Both kits are simple to install and are offered with a full product offering to cover the complete cable ranges found in the outside plant. In addition, both kits can be ordered with 4442 High Gel reenterable encapsulant. The 89 Series can also be purchased with 4407

Learn More . . .

[Packaging Data](#)

[Full Text . . .](#)

Characteristics

Bonding Type	Rigid
China RoHS - Below MCV	Yes
EU RoHS Compliant	Yes
Sheath Opening	7 Inch
Splice Terminal Closure	Filled
Splicing Connector Used	MS2, 3M710, Scotchlok
Tapes / Compound included	No