







THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
R. K. SEIFRIED

05/18/90

CHK
F. KIBLER

8-18-92

APVD

NAME

PRODUCT SPEC

APPLICATION SPEC

MATERIAL

FINISH

WEIGHT

0

CUSTOMER DRAWING

SCALE 4:1

SHEET 1 OF 2

REV M

TE Connectivity

HDI, 2 ROW, RIGHT ANGLE PIN ASSEMBLY, WITH MOUNTING EARS, 3.05 [.120] LONG SOLDER TAILS

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A1

00779

533295

—

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

1

2

3

4

5

6

7

8

9

HOUSING MATERIAL: THERMOPLASTIC, COLOR—NATURAL.

CONTACT MATERIAL: PHOSPHOR BRONZE.

FINISH:

MATING AREA: MEETS THE PERFORMANCE REQUIREMENTS OF PRODUCT SPECIFICATION 108—9063; BASED ON TELCORDIA DR—1217—CORE APPLICATIONS IN UNCONTROLLED ENVIRONMENTS.

SOLDER TAILS AREA: TIN—LEAD PLATED.

RIGHT ANGLE PIN RECOMMENDED P.C. BOARD HOLE SIZES ARE 0.94—1.09 [.037—.043]; RECOMMENDED PAD DIA IS 1.52 [.060].

MOUNTING EARS AND HARDWARE PURCHASED SEPARATELY, KIT PART NUMBER 533050—1.

6. DIMENSIONS IN BRACKETS ARE IN INCHES.

PART NUMBER IS OBSOLETE.

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

FINISH:

CONTACT FINISH: .00127—.00254 [.000050—.000100] NICKEL UNDERPLATE ALL OVER; .000762 [.000030] GOLD PLATE IN CONTACT AREA, TIN—LEAD PLATED POSTS.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—	SEE SHEET 1	—	—	—

△	—	—	—	—	—	—	1—533295—9	
△	—	—	—	—	—	—	1—533295—8	
△	—	—	—	—	—	—	1—533295—7	
△	—	—	—	—	—	—	1—533295—6	
△	—	—	—	—	—	—	1—533295—5	
△	187.96 [7.400]	74	191.77 [7.550]	201.93 [7.950]	209.55 [8.250]	150	1—533295—4	
△	—	—	—	—	—	—	1—533295—3	
△	—	—	—	—	—	—	1—533295—2	
△	—	—	—	—	—	—	1—533295—1	
△	—	—	—	—	—	—	1—533295—0	
△	OBSOLETE	124.46 [4.900]	49	128.27 [5.050]	138.43 [5.450]	146.05 [5.750]	100	533295—9
△	—	—	—	—	—	—	—	533295—8
△	—	—	—	—	—	—	—	533295—7
△	—	—	—	—	—	—	—	533295—6
△	—	—	—	—	—	—	—	533295—5
△	60.96 [2.400]	24	64.77 [2.550]	74.93 [2.950]	82.55 [3.250]	50	533295—4	
△	—	—	—	—	—	—	—	533295—3
△	35.56 [1.400]	14	39.37 [1.550]	49.53 [1.950]	57.15 [2.250]	30	533295—2	
△	22.86 [.900]	9	26.67 [1.050]	36.83 [1.450]	44.45 [1.750]	20	533295—1	
	E	D	C	B	A	POSN	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC

± —
± —
± —
± 0.13 [.005]
± —

ANGLES
FINISH

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC

± —
± —
± —
± 0.13 [.005]
± —

ANGLES
FINISH

MATERIAL

DWN
R. K. SEIFRIED
CHK
F. KIBLER
APVD
—

05/18/90
8—18—92
—

PRODUCT SPEC
—
APPLICATION SPEC
—
WEIGHT
0

SIZE
A1

CAGE CODE
00779

DRAWING NO
533295

RESTRICTED TO
—

CUSTOMER DRAWING

SCALE
4:1

SHEET
2

OF
2

REV
M

TE Connectivity

HDI, 2 ROW, RIGHT ANGLE PIN ASSEMBLY,
WITH MOUNTING EARS, 3.05 [.120]
LONG SOLDER TAILS

4805 (1/15)