



## NOTES:



- UL LISTED AND CSA CERTIFIED FOR:
  - 600V MAX VOLTAGE RATING
  - 221° F (105 C) MAX TEMP. RATING (CSA)
  - 257° F (125°C) MAX TEMP. RATING (UL)
  - STRANDED COPPER WIRE ONLY.
- MATERIAL:
  - STAMPING- BRASS, NICKEL PLATED  
- COPPER, NICKEL PLATED  
(FOR DNF10-250F1MB)
  - HOUSING-TYPE 6/6 NYLON
- DIMENSIONS IN BRACKETS ARE IN mm OR mm<sup>2</sup>
- COLORS ARE TRANSLUCENT
- SEE [www.panduit.com](http://www.panduit.com) FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
- WIRE STRIP LENGTH:  $9/32^{+1/32}_{-0}$  (7.1<sup>+0.8</sup><sub>-0</sub>)  
 $3/8^{+1/32}_{-0}$  (9.5<sup>+0.8</sup><sub>-0</sub>)  
(FOR DNF10-250F1MB)



LISTED  
20H3  
E78522



CERTIFIED  
LR31212

| PART NUMBER   | TAB SIZE                   | WIRE RANGE<br>AWG (mm <sup>2</sup> ) | COLOR<br>(note 4) | MAX.<br>INSUL. | DIMENSIONS in |               |              | CRIMP TOOLS                               |
|---------------|----------------------------|--------------------------------------|-------------------|----------------|---------------|---------------|--------------|-------------------------------------------|
|               |                            |                                      |                   |                | A ±.03        | B ±.01        | C ±.01       |                                           |
| DNF18-250F1MB | .250 X .032<br>(6,3 X 0,8) | 22-18<br>(1,5-1,0)                   | RED               | .136<br>(3,45) | .91<br>(23,1) | .45<br>(11,4) | .34<br>(8,6) | CT-600-A<br>CT-520<br>CT-1525<br>CT-2500  |
| DNF14-250F1MB | .250 X .032<br>(6,3 X 0,8) | 16-14<br>(1,5-2,5)                   | BLUE              | .160<br>(4,06) | .91<br>(23,1) | .45<br>(11,4) | .34<br>(8,6) |                                           |
| DNF10-250F1MB | .250 X .032<br>(6,3 X 0,8) | 12-10<br>(4,0-6,0)                   | YELLOW            | .220<br>(5,59) | .96<br>(24,4) | .45<br>(11,4) | .36<br>(9,1) | CT-600-A<br>CT-1550<br>CT-1551<br>CT-2500 |

**PANDUIT** CORP.

TINLEY PARK, ILLINOIS

13 8/11 SHOR MODIFIED NOTE #5, ADDED INSTALLATION TOOLS

12 07/10 SRB Corrected tab size for DNF10-250F1MB

LOOSE PC. FULLY INSULATED UNI-MALE DISCONNECT  
.250 X .032

REV DATE BY DESCRIPTION

DRAWN BY JV

CHK'D

SCALE

DRAWING NO.

A41402