


GKS Series

Multi-Entry Trapped Key-Operated Safety Interlock Switch



DESCRIPTION

The introduction of the GKS product marks a significant new product class for Honeywell. Honeywell's switching expertise has been applied to a cost-effective, trapped key safety interlock switch. This product allows OEMs to hold a door or gate closed while a hazard still exists. This is particularly important where there is momentum in the machine. In other words, when the machine is signaled to stop, the momentum in

the machine can mean that parts of the machine are still moving and pose an injury risk if the access gate or door is not held closed. Global approvals and standards are important to Honeywell's customers; therefore, the GKS product conform to the requirements of IEC60947-5-1 and carries cULus, CE and CCC approvals.

FEATURES

- Global approvals (CE, cULus, CE, and CCC)
- Glass-filled polyester body
- Power-to-lock and power-to-unlock schemes for key trap
- Flexible switching arrangement
- 24 Vdc, 110 Vac, and 230 Vac coil voltages
- Over-ride mechanism in cover
- Head may be rotated into 4 different positions
- Three conduit openings (knock-out style)
- Switch position provides status

BENEFITS

- Product may be applied to most applications worldwide
- Tough, cost-effective, double-insulated enclosure
- Choice of key trapping methodology
- Four contacts that can be arranged in any configuration¹
- Multiple voltages provide for every geography
- Has a method to open door (in case of power loss, etc.)
- One part number may be used for multiple applications
- Flexible wiring options
- Can diagnose status of gate/door (gate/door closed and locked, gate/door closed and unlocked, gate/door open)

¹ There will be minimum volume requirements for unreleased options.

POTENTIAL APPLICATIONS

- Woodworking machinery
- Printing/paper finishing equipment
- Plastic molding equipment
- Packaging machinery
- Bailing
- Pumping equipment
- Semiconductor manufacturing equipment
- Packaging wrapping
- Specialty equipment
- Machine tool
- Robot cell

GKS Series

SPECIFICATIONS

Designation and Utilization Category		Rated Operational Current I _e (A) at Rated Operational Voltage U _e (V)		
		120 Vac	125 Vdc	240 Vac/250 Vdc
AC15	B300	3 A	—	1.5 A
DC13	Q300	—	0,55 A	0,27 A

Rated thermal current (I _{th})	5 A
Sealing	IP67; NEMA 1, 4X, 12, 13
Rated impulse withstand (U _{imp})	2500 V
Pollution degree	3 (macro-environment, installation environment)
Rated insulation voltage (U _i)	600 V
Operating temperature range	-25 °C to 50 °C [-13 °F to 122 °F]
Storage temperature range	-40 °C to 85 °C [-40 °F to 185 °F]
Short-circuit protective device (type/maximum rating)	Class J fuse (5 A/600 Vac)
Expected mechanical life	1,000,000 operations
Conditional short-circuit current	1000 A
Solenoid operating voltage and power	24 Vac: +10 %, -15 %, 4 W 230 Vac: +10 %, -15 %, 9 W 110 Vac: +10 %, -15 %, 8 W 24 Vdc: +10 %, -20 %, 7 W

Complies with:

Low Voltage Directive 73/23/EEC, as amended by directive 93/68/EEC.

Machinery Directive 98/37/EEC only as the directives relate to the components being used in a safety function.

IEC/EN60947-5-1.

PART NUMBER TREE

GKS	X	XX	X	X	X	X
Series	Conduit	Contacts	Head Orientation	Locking Principal	Solenoid Voltage	Additional Function
Door	A - 1/2 NPT	21 - 2NC/1NO/1NO	L - Front	A - Power to unlock	2 - 24 Vac/dc	L - LED
Interlock	C - M20	22 - 2NC/1NO/1NC	N - Back	S - Power to lock	5 - 110 Vac	
Safety Limit		46 - 3NC/1NO	P - Left		6 - 230 Vac	
Switch,		47 - 4NC	M - Right			
Solenoid						

NOTE: The part number tree is provided to demonstrate the potential combinations of components. Actual availability of individual product combinations will depend on the popularity of that type. Please check with your local distributor or Honeywell representative for the available types in your region.


LED OPTION

The built-in LED is suitable for direct installation in the M20 x 1.5/0.5 in NPT thread, one of the three cable entries in the GKS safety switch. The built-in LED can indicate to the user whether the solenoid is unlocked/locked or whether the door is open/closed. The switching element can be wired individually.

Parameter	Value
LED color	Red
Connection	2 connection cables
Screw-in thread	M20 x 1.5/ 0.5 in NPT
Operating voltage/current consumption	24 Vdc/45 Ma 115 Vac/15 mA 230 Vac/15 mA
Degree of protection	IP67

Multi-Entry Trapped Key-Operated Safety Interlock Switch

MOUNTING DIMENSIONS (SWITCH AND OPTIONAL LED)



GKS Series

SWITCH ORDER GUIDE (ACTIVE LISTINGS)

Catalog Listing	Description
GKSA46LA2	0.5 in conduit, 3NC/1NO, head to front, power to unlock, 24 Vdc solenoid
GKSA46LA5	0.5 in conduit, 3NC/1NO, head to front, power to unlock, 110 Vac solenoid
GKSC46LA2	20 mm conduit, 3NC/1NO, head to front, power to unlock, 24 Vdc solenoid
GKSC46LA6	20 mm conduit, 3NC/1NO, head to front, power to unlock, 230 Vac solenoid

KEY ORDER GUIDE (ACTIVE LISTINGS)

Catalog Listing	Description	Min. Actuating Radius
GKZS6	Straight key	min. R 160 [6.30]
GKZS7	90° key	min. R 160 [6.30]
GKZS8	Left-right adjustable key	min. R 32 [1.26]
GKZS4	Up-down adjustable key	min. R 45 [1.77]
GKZS9	Multidirectional key	Moveable max. 18 degrees
GKZSF	Funnel key	min. R 160 [6.30]

CIRCUIT AND TRAVEL DIAGRAMS

Circuit Drawing	Inserted & Locked	Inserted & Unlocked	Removed & Unlocked
GKS..21..			
GKS..22..			
GKS..46..			
GKS..47..			

NOTE: This 'truth table' shows the switch status in various conditions. In each column, there is a change in switch contact position from the previous column. It is possible to determine the status of the switch by examining the combination against the table. This can be essential for operational reasons. For instance, the machine should not be started until the key is not only in the head, but is also trapped.

The **first column** depicts the key inserted and the key trapped in that position – this would be the typical run position for the machine – all doors closed. The **second column** illustrates the key inserted, but not trapped – this would be the safe-to-open the door position (as determined by the application's safety scheme). The **third column** shows the key extracted or door-open position.

Multi-Entry Trapped Key-Operated Safety Interlock Switch

KEY DIMENSIONS

GKZS6 2.0 [0.08] 5.9 [0.23] 22.00 [0.9] 75.2 [2.96] 41.7 [1.64] 20.0 [0.79] 15.0 [0.59] 18.7 [0.74] 3.0 [0.12] Ø5.0 [0.20] MIN. R160 [6.30] 23.0 [0.91] MAX. INSERTION DISTANCE 25.5 [1.00] MIN. INSERTION DISTANCE	GKZS7 16.0 [0.63] 2.0 [0.08] 4.0 [0.16] 16.8 [0.66] 56.0 [2.20] 40.0 [1.57] 22.7 [0.89] 26.2 [1.03] MIN. R 160 [6.30] 4.0 [0.16] MAX. INSERTION DISTANCE 6.0 [0.24] MIN. INSERTION DISTANCE	GKZS8 Ø5.5 [0.22] 40.0 [1.57] 26.0 [1.02] 19.0 [0.75] 2.0 [0.08] 18.8 [0.66] 18.0 [0.75] 2.0 [0.08] 50.0 [1.97] Recommend to apply glue after key set-up (LOCTITE 609) 21.0 [0.83] MAX. INSERTION DISTANCE 23.5 [0.93] MIN. INSERTION DISTANCE MIN. R 32 [1.26]
GKZS4 Ø5.5 [0.22] 50.0 [1.97] 40.0 [1.57] 20.0 [0.79] 2.0 [0.08] 16.8 [0.66] 19.0 [0.75] 2.0 [0.08] Recommend to apply glue after key set-up (LOCTITE 609) 21.0 [0.83] MAX. INSERTION DISTANCE 23.5 [0.93] MIN. INSERTION DISTANCE MIN. R 45 [7.77]	GKZS9 Ø5.5 [0.22] 56.0 [2.20] 40.0 [1.57] 20.0 [0.79] 2.0 [0.08] 16.8 [0.66] 18.0 [0.71] 12.0 [0.47] 4.0 [0.16] MOVABLE MAX.18° MOVABLE MAX.18° 20.0 [0.79] MAX. INSERTION DISTANCE 22.0 [0.87] MIN. INSERTION DISTANCE	GKZSF 6.0 [0.24] 24.0 [0.94] 38.0 [1.42] 20.5 [0.81] 32.2 [1.27] 28.7 [1.13] 4.0 [0.16] 16.8 [0.66] 2.8 [0.10] 17.0 [0.67] 10.0 [0.39] MAX. INSERTION DISTANCE 12.0 [0.47] MIN. INSERTION DISTANCE MIN. R 160 [6.30]

WARNING

IMPROPER INSTALLATION

- Consult with local safety agencies and their requirements when designing a machine-control link, interface, and all control elements that affect safety.
- Strictly adhere to all installation instructions

Failure to comply with these instructions could result in death or serious injury.

WARRANTY/REMEDY

Honeywell warrants goods of its manufacture as being free of defective materials and faulty workmanship. Honeywell's standard product warranty applies unless agreed to otherwise by Honeywell in writing; please refer to your order acknowledgement or consult your local sales office for specific warranty details. If warranted goods are returned to Honeywell during the period of coverage, Honeywell will repair or replace, at its option, without charge those items it finds defective. **The foregoing is buyer's sole remedy and is in lieu of all other warranties, expressed or implied, including those of merchantability and fitness for a particular purpose. In no event shall Honeywell be liable for consequential, special, or indirect damages.**

While we provide application assistance personally, through our literature and the Honeywell web site, it is up to the customer to determine the suitability of the product in the application.

Specifications may change without notice. The information we supply is believed to be accurate and reliable as of this printing. However, we assume no responsibility for its use.

WARNING

MISUSE OF DOCUMENTATION

- The information presented in this product sheet is for reference only. Do not use this document as a product installation guide.
- Complete installation, operation, and maintenance information is provided in the instructions supplied with each product.

Failure to comply with these instructions could result in death or serious injury.

SALES AND SERVICE

Honeywell serves its customers through a worldwide network of sales offices, representatives and distributors. For application assistance, current specifications, pricing or name of the nearest Authorized Distributor, contact your local sales office or:

E-mail: info.sc@honeywell.com

Internet: www.honeywell.com/sensing

Phone and Fax:

Asia Pacific	+65 6355-2828
	+65 6445-3033 Fax
Europe	+44 (0) 1698 481481
	+44 (0) 1698 481676 Fax
Latin America	+1-305-805-8188
	+1-305-883-8257 Fax
USA/Canada	+1-800-537-6945
	+1-815-235-6847
	+1-815-235-6545 Fax

Sensing and Control

Honeywell

1985 Douglas Drive North

Golden Valley, MN 55422

www.honeywell.com/sensing

004743-3-EN IL50 GLO Printed in USA
March 2011
© 2011 Honeywell International Inc. All rights reserved.

Honeywell