

ケースハンドル

CASE HANDLES


A-56
鉄製

特 徴 Feature

- プルターン機構のため施錠状態が保持され振動などによる自然開扉を防止します。
- ディテント効果でカチッと施錠を確認(A-56-A)
- 埋込みタイプで盤面はスッキリ(A-56-B)
- Pull-turn mechanism keeps locking positively from vibration or other movement to prevent natural door open.
- Detent makes the lock click.(A-56-A)
- Embedded type. Board surface is neat.(A-56-B)

仕 様 ●製品質量 : A-56-A/143g
A-56-B/180g

- 材 質
ベース/冷間圧延鋼板 (SPCC)
ハンドル/亜鉛合金 (ZDC)
ケース/冷間圧延ステンレス鋼板 (SUS304)
- 表面仕上
ベース/亜鉛めっきクロメート処理 (MFZn-C)
ハンドル/梨地クロムめっき (MZCr)
ケース/バレル研磨
- 付 属 品 : 専用止め金・取付けビス
- ガスチャンバードア
- 標準在庫品
- 本図は右仕様です。左仕様はお問合せください。
- 本製品の止め金取付け用ねじは、緩み防止のため「緩み防止剤」の塗布をお奨め致します。

用 途
納 期
備 考

Specifications

- Mass: A-56-A: 143g
A-56-B: 180g
- Material
Base: Cold rolled steel (SPCC)
Handle: Zinc alloy (ZDC)
Case: Cold rolled stainless steel (SUS304)
- Finish
Base: Zinc plating chromate treatment (MFZn-C)
Handle: Aventurine chrome plating (MZCr)
Case: Barrel polishing
- Accessories: Special stopper plate and screws
- Gas chamber doors
- Drawings show the right-hand use.
- Left-hand use is available. Consult us.
- It is recommended that thread-locking fluid be used to prevent loosening of the mounting screws for the catch.


Specific use
Remarks

- Mass: A-56-A: 143g
A-56-B: 180g
- Material
Base: Cold rolled steel (SPCC)
Handle: Zinc alloy (ZDC)
Case: Cold rolled stainless steel (SUS304)
- Finish
Base: Zinc plating chromate treatment (MFZn-C)
Handle: Aventurine chrome plating (MZCr)
Case: Barrel polishing
- Accessories: Special stopper plate and screws
- Gas chamber doors
- Drawings show the right-hand use.
- Left-hand use is available. Consult us.
- It is recommended that thread-locking fluid be used to prevent loosening of the mounting screws for the catch.

ロック機構=施錠保持






A-56-A




A-56-B

[A-56-A]


回転角度90°
Turning angle



2-M4タップ
tap






パネル穴明け寸法
Panel drilling dimensions




[A-56-B]


回転角度90°
Turning angle



2-M4タップ
tap



パネル穴明け寸法
Panel drilling dimensions




商品番号 Product No.	RoHS	CAD	適用板厚 (mm) Applicable panel thickness	コード Code	単 価 Price	量販価格 数量 Quantity	Bulk Price 単価 Price
A-56-A-L	●		0~2.3	03444	¥1,150	10個~	¥1,104
A-56-A-R	●	2D	0~2.3	01742	¥1,150	10個~	¥1,104
A-56-B-L	●	3D	1.6~2.3	03445	¥1,100	10個~	¥1,056
A-56-B-R	●	2D/3D	1.6~2.3	01743	¥1,100	10個~	¥1,056

●: RoHS指令対応品
▲: RoHS指令に対応可能です。

※大量のご注文は更にお安くなります。

使用例
Example of application



ハンドル・取手
つまみ・周辺機器



A

クレモン

ローラー
締り

特装密閉
ハンドル

フリーザー
密 閉

平 面
スイング

ギア式

平 面
ハンドル

ポップ
ハンドル

リフト
ハンドル

アジャスト
ハンドル

ラッチ式

スナッチ

リンク

フック式

ロック
ハンドル

L 型
ハンドル

T 型
ハンドル

ROUND-SHAPED / SMALL-SIZED HANDLES

丸型
小型

押ボタン

取 手

つまみ

止め金
ロッド棒

ジョイント
リンク

ワイヤ