

HSS Stub Drills



DIN897RN/BS328

Flute geometry

Right hand, standard helix have a 135° split point on diameters 3.0mm - 13mm. Above 13mm and below 3mm they will be standard 118° point.

Application

For use on automatic and capstan lathes or portable drills. Ideal for hand drilling in thin sections of material.

Metric

Size (mm)	Flute Length (mm)	Overall Length (mm)	Order Code	Price Each
1.00	6	26	148-5452	— —
1.20	8	30	137-6090	— —
1.40	9	32	137-6091	— —
1.50	9	32	No Order Code	— —
1.60	10	34	137-6092	— —
1.70	10	34	137-6094	— —
1.80	11	36	137-5902	— —
2.00	12	38	138-9507	— —
2.10	12	38	137-6095	— —
2.20	13	40	148-8973	— —
2.30	13	40	137-6096	— —
2.40	14	43	137-6097	— —
2.50	14	43	138-9504	— —
2.60	14	43	137-6098	— —
2.70	16	46	137-6099	— —
2.80	16	46	137-6296	— —
2.90	16	46	137-6000	— —
3.00	16	46	138-9508	— —
3.10	18	49	137-6101	— —
3.20	18	49	148-5458	— —
3.30	18	49	138-9505	— —
3.40	22	55	137-6102	— —
3.50	22	55	No Order Code	— —
3.60	22	55	No Order Code	— —
3.70	22	55	137-6103	— —
3.80	22	55	137-6104	— —
3.90	22	55	137-6297	— —
4.00	22	55	148-5457	— —
4.10	22	55	137-6105	— —
4.20	22	55	138-9509	— —
4.40	24	58	137-6106	— —
4.50	24	58	148-5459	— —
4.60	24	58	137-6107	— —
4.80	26	62	137-6108	— —
4.90	26	62	137-5903	— —
5.00	26	62	138-9510	— —
5.10	26	62	137-6109	— —
5.20	26	62	137-5904	— —
5.30	26	62	137-6110	— —
5.40	28	66	137-6112	— —
5.50	28	66	148-5454	— —
5.60	28	66	137-6113	— —
5.70	28	66	137-6114	— —
5.80	28	66	137-6115	— —
5.90	28	66	137-6116	— —
6.00	28	66	148-5460	— —
6.10	31	70	137-6117	— —
6.20	31	70	137-6001	— —
6.30	31	70	137-6002	— —
6.40	31	70	137-6118	— —
6.50	31	70	148-5456	— —
6.60	31	70	137-6298	— —
6.70	31	70	137-6119	— —
6.80	34	74	137-6003	— —
6.90	34	74	137-6120	— —
7.00	34	74	148-5461	— —
7.10	34	74	137-6121	— —
7.20	34	74	137-6122	— —
7.30	34	74	137-6124	— —
7.40	34	74	137-6125	— —
7.50	34	74	147-4048	— —
7.60	37	79	137-6126	— —
7.90	37	79	137-6127	— —
8.00	37	79	150-6421	— —
8.10	37	79	137-6128	— —
8.20	37	79	137-5905	— —
8.30	37	79	137-6129	— —
8.50	37	79	147-4049	— —
9.00	40	84	148-5464	— —
9.10	40	84	137-6130	— —
9.30	40	84	137-6131	— —
9.50	40	84	150-6422	— —
9.60	43	89	137-6132	— —
9.70	43	89	137-6133	— —
10.00	43	89	148-5466	— —
10.20	43	89	148-5462	— —
10.50	47	95	147-4051	— —
11.00	47	95	148-5467	— —
11.50	47	95	137-6004	— —
12.00	51	102	148-5468	— —
12.50	51	102	148-8974	— —
13.00	51	102	147-4076	— —
13.50	54	107	137-6005	— —
14.00	54	107	148-5469	— —
14.50	56	111	137-6134	— —
15.00	56	111	148-5470	— —
15.50	58	115	137-6006	— —
16.00	58	115	148-5471	— —
17.00	60	119	137-6136	— —
17.50	62	123	137-6137	— —
18.00	62	123	137-6008	— —
18.50	64	127	137-6138	— —
20.00	66	131	137-6139	— —

18.50	64	127	137-6138	— —
20.00	66	131	137-6139	— —
21.00	68	136	137-6140	— —
22.00	70	141	137-6141	— —
24.00	75	151	137-6142	— —
25.00	75	151	137-6143	— —

Fractional

505685

Size (inches)	Flute Length (mm)	Overall Length (mm)	Order Code	Price Each
$\frac{3}{64}$	8	30	137-6144	— —
$\frac{1}{16}$	10	34	137-5906	— —
$\frac{5}{64}$	12	38	137-6009	— —
$\frac{3}{32}$	14	43	148-5445	— —
$\frac{7}{64}$	16	46	137-5907	— —
$\frac{1}{8}$	18	49	150-6423	— —
$\frac{5}{32}$	22	55	148-5447	— —
$1\frac{1}{64}$	24	58	137-6145	— —
$\frac{9}{16}$	26	62	148-5448	— —
$1\frac{3}{64}$	26	62	137-6146	— —
$\frac{7}{32}$	28	66	148-5449	— —
$\frac{1}{4}$	28	66	No Order Code	— —
$1\frac{7}{64}$	34	74	137-6148	— —
$\frac{9}{32}$	34	74	137-6149	— —
$1\frac{9}{64}$	37	79	137-6185	— —
$\frac{5}{16}$	37	79	137-6150	— —
$2\frac{1}{64}$	37	79	137-6186	— —
$1\frac{1}{32}$	40	84	148-5450	— —
$2\frac{3}{64}$	40	84	137-6300	— —
$\frac{3}{8}$	43	89	148-5451	— —
$2\frac{5}{64}$	43	89	137-6187	— —
$1\frac{3}{32}$	43	89	137-6188	— —
$2\frac{7}{64}$	47	95	137-6189	— —
$\frac{7}{16}$	47	95	137-6190	— —
$2\frac{9}{64}$	47	95	137-6191	— —
$1\frac{5}{32}$	51	102	137-6192	— —
$3\frac{1}{64}$	51	102	137-6193	— —
$\frac{1}{2}$	51	102	137-6010	— —
$\frac{9}{16}$	56	111	137-6301	— —
$1\frac{1}{16}$	62	123	137-6151	— —
$\frac{3}{4}$	66	131	137-6194	— —