






Modular Jack

154-UL616B

KOBI CONN



Dimensions: In.

ELECTRICAL SPECIFICATIONS

Current Rating:	1.5A
Voltage Rating:	150V max.
Breakdown Voltage:	500VAC for 1 Minute
Insulation Resistance:	10M

SPECIFICATIONS

Contacts:	0.014" Thickness, Phosphor Bronze Alloy Selective, 50 Micron Gold Plating over Nickel Over Tin
Housing:	25% Glass Filled Nylon 66
Lead Length:	4"

Date Last Revised: 10-15-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300601

154-UL616B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[154-UL616B](#)