

## Isobar Home/Business Theater Surge Suppressor - Ultimate-performance surge and line noise protection for all components

MODEL NUMBER: HTPOWERBAR10



### Description

Tripp Lite's HTPOWERBAR10 Isobar Home/Business Theater Surge Suppressor provides ultimate protection--5700 joules--stopping damaging surges and filtering disruptive line noise so components perform at their peak! You can see and hear the difference: sharper, crisper video; deeper, fuller audio and longer component life spans. Perfect for large home/business theater installations: high-definition TVs, PVRs, satellite and A/V receivers, subwoofers, DVD/CD players and more. Exclusive Isolated Filter Banks eliminate noise interference between components. 10 outlets (with transformer spacing and plug-in safety covers), 3-line coaxial protection and 1-line tel/modem protection safeguard an entire home/business theater system. \$500,000 [Ultimate Lifetime Insurance](#) coverage (USA and Canada only). Includes metal housing, color-coordinated outlet/plug labels, 16 diagnostic LEDs, 8-ft. cord with a right-angle plug, two 6-ft. gold coaxial cables and 6-ft. phone cord.

### Features

- 5700 joules surge suppression rating with EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans)
- \$500,000 [Ultimate Lifetime Insurance](#) (USA and Canada only) covers connected components against surge damage...for life!
- Isolated Filter Banks eliminate interference between connected components
- Metal housing safely withstands the strongest surges
- 10 surge-protected NEMA 5-15R AC outlets safeguard an entire home/business theater system
- Widely-spaced outlets accommodate up to 6 transformers
- 4 plug-in safety covers protect against accidental contact
- 3 sets of surge-protected Type F gold coaxial connectors (with two included 6-ft. gold coaxial cables) safeguard components on cable, satellite and antenna line
- 1-line tel/modem surge protection (with included 6-ft. phone cord) safeguards personal video recorders (PVRs) on a single dial-up line. Built-in splitter (1 jack in and 2 jacks out) allow simultaneous connection of two devices sharing a single line
- 8-ft. cord with right-angle NEMA 5-15P plug provides convenient location anywhere within a home/business theater system

### Highlights

- 10 outlets / 8-ft. cord
- 5700 joule rating
- Isolated Filter Banks / metal housing
- 3-line coaxial (gold) surge protection
- 1-line tel/modem surge protection
- \$500,000 [Ultimate Lifetime Insurance](#) (USA and Canada only)

### Applications

- Perfect for large home/business theater installations: high-definition TVs, PVRs, satellite and A/V receivers, subwoofers, DVD/CD players and more

### Package Includes

- HTPOWERBAR10 Home/Business Theater Surge Suppressor
- Two 6-ft. gold coaxial cables and 6-ft. phone cord
- Instruction manual with warranty information

- 16 diagnostic LEDs alert user to 6 input voltage levels, 6 amp usage levels and 4 operational conditions (protection, grounding, power, switched status)
- Keyhole slots provide convenient wall or cabinet mounting
- Illuminated master switch provides one-touch power control over all components. Circuit breaker protects against dangerous system overload
- Metal housing (gold) stands up to the most demanding environments
- UL and cUL listed
- Lifetime product warranty
- Color-coordinated outlet/plug labels

## Specifications

OVERVIEW	
Intended Application	Audio/Video
Style	Strip
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Circuit Breaker (amps)	15
Outlet Quantity / Type	10 NEMA 5-15R
Number of Outlets	10
Transformer Accommodation	Accommodates 6 transformers
INPUT	
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P
Input Plug Features	Space-saving right-angle input plug
Input Cord Length (ft.)	8
Input Cord Length (m)	2.4
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
LEDS ALARMS & SWITCHES	
Switches	Combination AC circuit breaker and illuminated 2 position on/off power switch
Diagnostic LEDs	16 diagnostic LEDs alert user to 6 input voltage levels, 6 amp usage levels and 4 operational conditions (protection, grounding, power, switched status)
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	5700

AC Suppression Response Time	NM = instantaneous CM = < 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
UL1449 Let Through Rating	330V - UL verified
Isolated Filter Banks	10
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	3 line
Network (Ethernet) Protection	No
<b>PHYSICAL</b>	
Unit Dimensions (hwd / in.)	19 x 3.75 x 5
Unit Dimensions (hwd / cm)	48.3 x 9.5 x 12.7
Unit Weight (lbs.)	4.5
Unit Weight (kg)	2
Material of Construction	Metal
Integrated Keyhole Mounting Tabs	Keyhole mounting slots allow desk or wall mounting
Color (AC Line Cord)	Black
<b>SPECIAL FEATURES</b>	
Right-Angle Plug	Yes
<b>CERTIFICATIONS</b>	
UL1449 3rd Edition (AC Suppression)	UL1449
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
cUL / CSA (Canada)	cUL
Approvals	Exceeds IEEE 587 category A&B specifications
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Connected Equipment Insurance  
(U.S., Canada & Puerto Rico)

\$500,000 [Ultimate Lifetime Insurance](#)

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.