

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

ALL RIGHTS RESERVED.

|     |
|-----|
| LOC |
|-----|

|  |      |
|--|------|
|  | DIST |
|--|------|

REVISIONS

|  |  |  |
|--|--|--|
|  |  |  |
|--|--|--|

LTR

DESCRIPTION

DATE \_\_\_\_\_

|     |
|-----|
| DWN |
|-----|

|      |
|------|
| APVD |
|------|

|  |    |
|--|----|
|  | E1 |
|--|----|

REVISÉ PER ECO-11-005139

26APR11

RK

HMR





NOTES:

1. MATERIAL: 66NYLON UL94V-0, COLOR: WHITE, BLUE


2. APPLICABLE CONNECTOR PART NUMBER:

X-353293-X(REC ASS'Y)

3 PROFILE DEVIATION AT LOCATION SHOWN ALLOWED  
UP TO 1.5 MAX



|               |            |      |      |      |     |             |            |
|---------------|------------|------|------|------|-----|-------------|------------|
| 0.30          | 35.5       | 33.9 | 31.8 | 28.5 | 40  | 9-353294-0  | 4-353294-0 |
| 0.29          | 34.0       | 32.4 | 30.3 | 27.0 | 38  | 8-353294-8  | 3-353294-8 |
| 0.28          | 32.5       | 30.9 | 28.8 | 25.5 | 36  | 8-353294-6  | 3-353294-6 |
| 0.27          | 31.0       | 29.4 | 27.3 | 24.0 | 34  | 8-353294-4  | 3-353294-4 |
| 0.26          | 29.5       | 27.9 | 25.8 | 22.5 | 32  | 8-353294-2  | 3-353294-2 |
| 0.25          | 28.0       | 26.4 | 24.3 | 21.0 | 30  | 8-353294-0  | 3-353294-0 |
| 0.24          | 26.5       | 24.9 | 22.8 | 19.5 | 28  | 7-353294-8  | 2-353294-8 |
| 0.23          | 25.0       | 23.4 | 21.3 | 18.0 | 26  | 7-353294-6  | 2-353294-6 |
| 0.22          | 23.5       | 21.9 | 19.8 | 16.5 | 24  | 7-353294-4  | 2-353294-4 |
| 0.21          | 22.0       | 20.4 | 18.3 | 15.0 | 22  | 7-353294-2  | 2-353294-2 |
| 0.20          | 20.5       | 18.9 | 16.8 | 13.5 | 20  |             |            |
| WEIGHT<br>(g) | D          | C    | B    | A    | Pos | BLUE        | WHITE      |
|               | DIMENSIONS |      |      |      |     | PART NUMBER |            |

|                        |  |                                                                                                           |  |                                                                                            |  |                                                                                                       |  |
|------------------------|--|-----------------------------------------------------------------------------------------------------------|--|--------------------------------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------------|--|
| DIMENSIONS:<br>mm      |  | TOLERANCES UNLESS OTHERWISE SPECIFIED:<br>0 PLC ±<br>1 PLC ±<br>2 PLC ±<br>3 PLC ±<br>4 PLC ±<br>ANGLES ± |  | DWN<br>T. FURUYA 12JUL96<br>CHK<br>J. TANIGAWA 12JUL96<br>APVD<br>SEI FONG                 |  |  TE Connectivity |  |
|                        |  |                      |  | NAME<br>AMP Mini Common Terminated (CT) Connector 1.5mm PITCH<br>DOUBLE ROW HOLDER HOUSING |  | SIZE<br>A3                                                                                            |  |
| MATERIAL<br>SEE NOTE 1 |  | FINISH<br>           |  | PRODUCT SPEC<br>108-5525<br>APPLICATION SPEC<br>114-5223<br>WEIGHT<br>SEE TABLE            |  | CAGE CODE<br>00779                                                                                    |  |
| CUSTOMER DRAWING       |  |                                                                                                           |  | DRAWING NO<br>C-353294                                                                     |  | SCALE 5:1                                                                                             |  |
|                        |  |                                                                                                           |  | SHEET 1 OF 1                                                                               |  | REV E1                                                                                                |  |