

FO connecting cable - VS-SCRJ-GOF-CONF - 1654727

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Customer-specific SC-RJ cable sets, for multi-mode 50/125 µm fiberglass

RoHS

Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	2,272.000 g
Custom tariff number	85447000
Country of origin	Switzerland

Technical data

Mechanical characteristics

Minimum external conductor diameter	8 mm
Weight	0 g

Ambient conditions

Ambient temperature (operation)	-20 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C

Material data

Housing material	PBT/PA
------------------	--------

Standards and Regulations

Impact strength	2 Nm / 10 x
-----------------	-------------

FO connecting cable - VS-SCRJ-GOF-CONF - 1654727

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260705
eCl@ss 7.0	27440309
eCl@ss 8.0	27061803
eCl@ss 9.0	27061803

ETIM

ETIM 2.0	EC000764
ETIM 3.0	EC001121
ETIM 4.0	EC000034
ETIM 5.0	EC000034

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Accessories

Accessories

Protective cover

Protective covers - VS-SCRJ-PC - 1653757



IP67 protective cover, for covering the male inserts in the sleeve housings IP67, VS-SC-RJ-..., VS-04-..., VS-06-... and VS-08-...