





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	DIMENSIONS			WEIGHT
	' A '	' B '	' C '	lbs 10 (g) pcs
JP131W----	0.66 (16.76) (REF)	0.44 (11.18)	0.270 (6.89)	0.45 (204.12)



SECTION A-A
(BEND RADIUS
CONTROL)



DIMENSIONS IN BRACKETS ARE METRIC [mm]

[illegible]

G03043CC_PB_JP131W_00

PANDUIT

CORP. TINLEY PARK, ILLINOIS

J-PRO J-HOOK
WALL MOUNT
(JP131W-)

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± 0.05 (1.3) (XXX) ± 0.010 (0.25)
(XX) ± 0.02 (0.5) ANGLES $\pm 5^\circ$

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY JAD

MAT'L:

SCALE NONE

DATE	1/19/06
------	---------

SEE NOTE 2

DRAWING NO.

GB3043CC

DWG
A
SIZE

- NOTES:

- NOTES:
1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PRODUCT COLOR.
 2. MATERIAL: NYLON 6/6
 3. PRODUCT IS DESIGNED TO SUPPORT A MAXIMUM 1 5/16" (33.34) DIAMETER BUNDLE. RECOMMENDED MAXIMUM STATIC LOAD: 25 lbs.
 4. PRODUCT INCORPORATES FEATURES ALLOWING USER TO RETAIN CABLE BUNDLES IN J-PRO J-HOOK WITH TAK-TY CABLE TIES UP TO 3/4" WIDE.
 5. PRODUCT MARKINGS:
 - cULus logo and statement:
"SUITABLE FOR USE IN AIR HANDLING SPACES IN ACCORDANCE WITH SECTION 300-22 (C) & (D) OF THE NATIONAL ELECTRIC CODE."
 - ULC logo and statement:
"IN ACCORDANCE WITH CAN/ULC S-102.2 IN SINGLE UNITS OR PAIRS, 4 ft (1220mm) MIN. SPACING, FSR=0, SDC=20."

R	1/19/06	JAD		INITIAL RELEASE	GB3043CC	R				DATE 1/19/06	SEE NOTE 2	DRAWING NO.	DWG
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP		CHK'D	GB3043CC		A SIZE	