








SWITCH FUNCTION	
POS. 1	POS. 2
ON	ON
1-2,4-5 7-8,10-11	2-3,5-6 8-9,11-12



NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: $X.X \pm 0.4$
 $X.XX \pm 0.25$
- TERMINAL NUMBERS FOR REF. ONLY
- RATING: 0.1A @ 30VDC
- TRAVEL: FULL = 2.5mm, LOCK = 1.5mm
- OPERATING FORCE: 300gf $\pm$ 70gf
- ELECTRICAL LIFE: 10,000 CYCLES
- ▲ DENOTES CRITICAL PARAMETER
- CONTACT MATERIAL: SILVER
- 2002/95/EC (RoHS) COMPLIANT
- INSULATION RESISTANCE: 100 M Ω MIN.
- DIELECTRIC STRENGTH: 500 VAC
- OPERATING TEMPERATURE: -30°C TO +85°C



TITLE TL4201EEYA w/ EPOXY

B	19691	DRAWING UPDATE	2/18/11	BGL
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE	4:1	DATE	2/18/2011	DR	BGL	DWG	P010635	REV	B
-------	-----	------	-----------	----	-----	-----	---------	-----	---

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

[TL4201EEYA](#) [TL4201EEZB](#) [TL4201EEXB](#) [TL4201EEYB](#)