

[Skip to content](#)

Search By: Part Number Text [Tips](#)




Thursday, May 04, 2006

[Sign In](#)

[Home](#) > [Products](#) > [By Type](#) > [PolySwitch Resettable Devices](#) > [Product Feature Selector](#) > Product Details

Product Details for MICROSMDD035F-2



MICROSMDD035F-2

Tyco Part Number: A72665-000

 [Active](#)

PolySwitch Resettable Devices

 [RoHS Compliant](#)

Product Highlights:

- Surface Mount Application
- Family Name = microSMD
- Surface Mount Construction
- IH (Room Temperature) = .35 Amps.
- IT (Room Temperature) = .75 Amps.

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [microSMD035F](#) (PDF, English)

Catalog Pages / Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: - UL Listed = 290300-E74889 Electrical Characteristics: IH (Room Temperature) (Amps.) = 0.35 IT (Room Temperature) (Amps.) = 0.75 Vmax Operating (V) = 6 Rmin (Ω) = 0.32 R1 Max [Post Trip] (Ω) = 1.30 UL Rated Current (Amps.) = 40 - Tripped Power Dissipation (Typical) (W) = 0.80 Termination Related Features: - Construction = Surface Mount Body Related Features: - CSA File No. = 1031175 (CA 78165-1) Contact Related Features: Family Name = microSMD	Configuration Related Features: Form Factor (inches) = 1210 Form Factor (mm) = 3225 Industry Standards: RoHS/ELV Compliance = RoHS compliant, ELV compliant Lead Free Solder Processes = Reflow solder capable to 245°C, Reflow solder capable to 260°C - RoHS/ELV Compliance History = Always was RoHS compliant - TUV Certificate No. = R72041438 Conditions for Usage: Operating Temperature (Max.) (°C) = 85 Operation / Application: - Application = Surface Mount Packaging Related Features: - Packaging Method = Tape & Reel Other: - Brand = Raychem

Languages: English | [Deutsch](#) | [Español](#) | [Português \(do Brasil\)](#) | [Italiano](#) | [正體中文 \(繁體\) \(Chinese\)](#) | [中文 \(•体\) \(Simplified Chinese\)](#) | [日本語 \(Japanese\)](#)

Country Sites: [China](#) | [Japan](#)