



Aluminum Flanged - Utility Enclosures (1411FB Series)

[Home](#)
[Products](#)
[Distributors](#)
[Technical](#)
[Contact Us](#)
[Other Options](#)

Path: [Home](#) > [Enclosure Index](#) > Aluminum Flanged - Utility Enclosures

Painted Version


[click to enlarge](#)

Unpainted Version


[click to enlarge](#)

With protective
plastic film covering


[click to enlarge](#)

Protective plastic film cover
partially removed


[click to enlarge](#)

Protective plastic
film cover removed

Key Features:

- Flanged version (for easy wall or shelf mounting) of our popular ["1411" aluminum series](#)
- 0.04" thick aluminum
- Four self-tapping screws included.
- Unpainted aluminum or black - baked powder paint.
- Unpainted aluminum version is protected through manufacturing and shipping with a plastic film cover to ensure a high quality finish. Also doubles as a removable drilling template.
- Replacement screws [1421J6](#) (Pkg. of six (6), 6-32 Philips head screws).

Part Number		PDF Reader File	AutoCAD .dwg File (zipped)	3D Solid Model .igs & .stp files (zipped)	Units	Enclosure Dimensions (Not Including Flange)		
Black Painted	Unpainted					Length	Width	Height
1411FBBBK	1411FBBU	 185K	 120K	 130K	inch	2.7	2.2	1.6
					mm	69	56	41
1411FBCBK	1411FBCU	 184K	 120K	 131K	inch	3.2	2.2	1.1
					mm	81	56	28
1411FBDBK	1411FBDU	 185K	 121K	 131K	inch	3.2	2.2	1.6
					mm	81	56	41
1411FBGBK	1411FBGU	 183K	 121K	 131K	inch	4.0	2.2	1.6
					mm	102	56	41
1411FBHBK	1411FBHU	 182K	 120K	 131K	inch	4.0	2.2	2.2
					mm	102	56	56
1411FBFBK	1411FBFU	 179K	 122K	 131K	inch	4.0	2.2	3.0
					mm	102	56	76
1411FBK BK	1411FBKU	 179K	 121K	 131K	inch	5.0	2.2	2.2
					mm	127	56	56
1411FBNBK	1411FBNU	 181K	 121K	 131K	inch	5.0	3.0	2.2
					mm	127	76	56

1411FBLBK	1411FBLU	 182K	 114K	 131K	inch	5.0	4.0	3.0
					mm	127	102	76
1411FBPBK	1411FBPU	 180K	 122K	 133K	inch	6.0	5.0	4.0
					mm	152	127	102
1411FBQBK	1411FBQU	 179K	 122K	 133K	inch	7.0	5.0	3.0
					mm	178	127	76
1411FBSBK	1411FBSU	 181K	 113K	 132K	inch	8.0	4.0	3.0
					mm	203	102	76
1411FBRBK	1411FBRU	 182K	 122K	 132K	inch	8.0	6.0	3.5
					mm	203	152	89
1411FBUBK	1411FBUU	 179K	 115K	 133K	inch	10.0	6.0	3.5
					mm	254	152	89
1411FBXBK	1411FBXU	 176K	 121K	 132K	inch	12.0	7.0	4.0
					mm	305	178	102

Exactly what you are looking for???

Link to our stocking distributors - most have "on-line" pricing, stock check and ordering!!!

Our Distributors

[Order from your favorite distributor](#)

[Home](#) | [Products](#) | [Distributors](#) | [Technical](#) | [Contact Us](#) | [Other Options](#)

Copyright; © 2013 Hammond Mfg Co Inc

URL: <http://www.hammondmfg.com>