



English | 简体中文 | 日本語

Search Entire Site [GO](#)

[Contact IDT](#) | [Investors](#) | [Press](#)

[About IDT](#)

[Products](#)

[Applications](#)

[Support](#)

[myIDT](#)

[Document Search](#) | [Package Search](#) | [Parametric Search](#) | [Cross Reference Search](#) | [Green & RoHS](#) | [Calculators](#) | [Thermal Data](#) | [Reliability & Quality](#) | [Military](#)

[Home](#) > [Products](#) > > [960008](#) > [960008AFLF](#)

[Add to myIDT \[?\]](#)

You may also like...

960008AFLF

Category:

Generic Part: [960008](#)

Market Group: PC CLOCK

Description: PC SPECIAL PURPOSE

Recommended Application: Ricoh Printer Application (Soriano) Output Features: $\hat{\text{€}}$ 2.5V - 3.3V power for GIGA/ASIC $\hat{\text{€}}$ Supports Spread Spectrum $\hat{\text{€}}$ 1 - Single-ended GIGACLK @ 125MHz $\hat{\text{€}}$ 1 - ASIC @ 33MHz $\hat{\text{€}}$ 1 - ASIC @ 80MHz - 133MHz $\hat{\text{€}}$ 1 - SDCLK @ 50MHz Features/Benefits: $\hat{\text{€}}$ Selectable SMBus address $\hat{\text{€}}$ Selectable output enable/disable via SMBus Key Specifications: $\hat{\text{€}}$ Clock jitter: <250ps $\hat{\text{€}}$ Operating current: <50mA (typical)

**Time is
money**

Parameters

Package	SSOP 28 (PYG28)
Speed	NA
Temperature	C
Voltage	3.3 V
Status	Active
Sample	Yes
Minimum Order Quantity	94
Factory Order Increment	47

Distributor Inventory

No Pricing information is available from our Distributors at this time.

Documents

Type	Title	Size	Revision Date
Misc	PC Clocks Contact Info	61 KB	05/29/2007

Package

Description	SSOP 5.3 MM
Class	PLASTIC
Moisture Sensitivity Level (MSL)	1
Category	Green
Moisture Exposure Floor Life	Unlimited @ <30°C/85% RH
Peak Reflow Temperature	260°C
Rebake Conditions	NA
Length	10.2
Mark	PYG
Width	5.3
Pitch	0.65
Thickness	1.73
Status	Active

[Home](#) | [Site Map](#) | [Legal](#) | [Careers](#) | [Contact Us](#) | [Quality](#) | [RSS](#) [What is this?](#)

Use of this website signifies your agreement to the [acceptable use](#) and [privacy policy](#). Copyright © 1997-2008 Integrated Device Technology, Inc. All Rights Reserved.