

Specifications:

Voltage Rating	12 to 24 Vdc
Frequency	1250 Hz $\pm$ 20%
Loudness (dB(A) @ 4 ft)	97 $\pm$ 8
Current Draw (Amps Max)	0.6
Sound Pulse Rate (pps)	1 to 2
Operating Temperature	-40°C to +85°C
Termination	8-32 UNC Studs
Housing	ABS, Black UL94V-0
Spike Protected	+100 / -400 Volts
Conforms to SAEJ994 (OCT 02) Standards	
Cross Reference	
ECCO	520
PRECO	240

Dimensions: Inches (mm)