







ASSEMBLY - VIEW FROM TOP




ISOMETRIC VIEW



ASSEMBLY - VIEW FROM SIDE



SECTION A-A



ASSEMBLY - VIEW FROM BOTTOM

| 1584T6**                                                     |
|--------------------------------------------------------------|
| Finish - Top - Black Painted Steel                           |
| Bottom - Aluminum Extrusion                                  |
| Rated - 120 VAC, 60 Hz, 15 Amps                              |
| Approvals - CSA Certified Standards C22.2 (No. 21-95, 42-99) |
| - UL Listed, Standard UL1363                                 |
| Cord Length                                                  |
| 1584T6A1 - 6' Foot Power Cord (NEMA 5-15P)                   |
| 1584T6B1 - 15' Foot Power Cord (NEMA 5-15P)                  |

