


PART NO.	MATERIAL	MARKER SIZE inches [mm]	LABELS PER ROW	STANDARD PKG. QTY.
C060X020YJT	GM Y2	0.600 [15.2] X 0.200 [5.08]	3	10000
C060X020KBT	GM K4			
C060X020KCT	GM K4			
C060X020CBT	GM C4			
C060X020TJT	GM T			



NOTE:
1. MILLIMETER ARE IN [].

CAD FILENAME/LAYERS		100472EF_DC_C10262/09C	
PANDUIT		CORP. TINLEY PARK, ILLINOIS	
CUSTOMER DRAWING OPTIMUM		C060X020YJT, C060X020KBT, C060X020KCT	
C060X020CBT AND C060X020TJT		THERMAL TRANSFER LABELS	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .12 (XXX) ± .025 (.XX) ± .062 ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
2	7/8/09	RVU	GMC4 WAS GMC. ADD +/- .062. REMOVE NOTE 1.
1	4/13/07	RVU	ADDED P/N: C060X020KCT, C060X020KBT, MATERIAL SHOULD BE GMK4.
0	6-5-06	RVU	DRAWING RELEASED.
REV	DATE	BY	CHK

5792	R		
4948	R		
4484	R		
ECN	R	CUST	SUP

DRAWN BY RVU	MAT'L: SEE TABLE	SCALE NTS
DATE 9-30-04		DRAWING NO. C10262
CHK'D		DWG A SIZE