

EUROPEAN POWER SOURCES

European Desk-Top



European Wall Plug-In



Output power plugs:

Compatible for use with Switchcraft 722A or PC-722A


Input for All European Models is 230 Volts A.C., 50 Hz. with CEE 7/16 Europlug

SEC.	STANCOR PART NUMBER	Rated Output			Regulated/ Unregulated	Case Style	DIMENSIONS						Weight (lbs.)	Output Plug 2.1x5.5mm Inside Polarity	Compliance
		Volts	AC/DC	mA			Length (inches) (mm)		Width (inches) (mm)		Height (inches) (mm)				
A	STAF-0381F	6.0	DC	500	Unregulated	Wall Plug-in	2.5	63.5	2.0	50.8	1.6	39.7	0.55	Negative	CE
	STAF-0797F	6.0	DC	1000	Unregulated	Wall Plug-in	2.8	69.9	2.3	57.2	1.8	46.0	0.83	Negative	CE
	STAF-2100F	6.2	DC	300	Unregulated	Wall Plug-in	2.3	57.2	1.7	42.9	1.5	38.1	0.40	Negative	CE
	STAF-2223F	9.0	DC	200	Unregulated	Wall Plug-in	2.3	57.2	1.7	42.9	1.5	38.1	0.40	Negative	CE
B	STAF-3309F	9.0	DC	300	Unregulated	Wall Plug-in	2.5	63.5	2.0	50.8	1.6	39.7	0.49	Negative	CE
	STAF-1058F	9.0	DC	500	Unregulated	Wall Plug-in	2.5	63.5	2.0	50.8	1.6	39.7	0.55	Negative	CE
	STAF-0329F	9.0	DC	1000	Unregulated	Wall Plug-in	2.8	69.9	2.3	57.2	1.8	46.0	0.93	Negative	CE
	STAF-3382F	12.0	DC	300	Unregulated	Wall Plug-in	2.5	63.5	2.0	50.8	1.6	39.7	0.55	Negative	CE
C	STAF-1454FD	12.0	DC	1000	Unregulated	Desk-Top	3.4	85.7	2.6	65.1	2.2	55.6	1.60	Negative	CE
	STAF-1948FD	12.0	DC	1200	Unregulated	Desk-Top	3.4	85.7	2.6	65.1	2.2	55.6	1.60	Negative	CE
	STAF-0354F	14.5	DC	800	Unregulated	Wall Plug-in	2.8	69.9	2.3	57.2	1.8	46.0	1.00	Negative	CE
D	STAF-1972F	15.0	DC	1000	Unregulated	Desk-Top	3.4	85.7	2.6	65.1	2.2	55.6	1.60	Negative	CE
	STAF-2098F	24.0	AC	400	Unregulated	Wall Plug-in	2.8	69.9	2.2	55.6	1.8	46.0	0.85	-	CE



CE Mark

Wall Plug-In



Desk-Top

