

Plugin units type 2 with cantilever extractionhandle, front panel unshielded

Part no.: 20817-448

Features:

- At 6 U the board position can be offset by 1 HP to the right by swapping the top and bottom board holders; thus space is created for SMD components on the left (solder) side; for board thickness 1.6 mm only



Technical information:

Description	Height	Width	Height	B
Plugin units type 2 with cantilever extractionhandle, front panel unshielded	6 U	4 HP		

Delivery comprises: kit

Item	Qty	Description
1	1	Extractor handle, trapezium shape, PPE, grey, bottom
1a	1	Extractor handle, trapezium shape, PPE, grey, top
2	2	Identification plate, Al, 1.5 mm, anodised, cut edges plain
3	2	Bearing female connector, Ms
4	1	Printed board bracket, Zn, die-cast, bottom
4a	1	Printed board bracket, Zn, die-cast, top
6	1	Front panel for extractor handle in trapezium shape, front anodised, rear iridescent green chromated
8	2	Sleeve, PA, grey, up to 7 HP front panel width
8	4	Sleeve, PA, grey, from 8 HP front panel width
9	2	Pozidrive collar screw, St, nickel-plated, M2.5 × 11 and 12.3, up to 7 HP front panel width
9	4	Pozidrive collar screw, St, nickel-plated, M2.5 × 11 and 12.3, from 8 HP front panel width
11	2	Raised countersunk screw, M2.5 × 8
13	2	Washer, A2.7, DIN 125
14	2	Pozidrive flathead screw, St, nickel-plated, M2.5 × 10

