



Section K

Wallplates

Index

Product	Page
Features and Benefits	K-2
Toggle Snap-On Wallplates	K-4
Decorator Snap-On Wallplates	K-5
Toggle Switch Wallplates	K-6
Duplex and Single Receptacle Wallplates	K-7
Single Receptacle Wallplates	K-8
Blank Wallplates	K-9
347 Volt Wallplates	K-10
Decorator Wallplates	K-11
Combination Wallplates, 2-Gang	K-12
Combination Wallplates, 3-Gang	K-14
Combination Wallplates, 4- and 5-Gang	K-15
Telephone and Coaxial Outlet Plates	K-16
Jumbo, Metal Wallplates	K-17
Pre-Marked "EMERGENCY" and Barrel Key Switch Wallplates	K-18
Pre-marked "ISOLATED GROUND" or "COMPUTER ONLY" Wallplates	K-19
Security Wallplates	K-20
Accessories and Selection Charts	K-21
Weatherproof Plates for Receptacles	K-22
Weatherproof Plates for Receptacles and Switches	K-23
Weatherproof Covers for Flanged Devices	K-24
Weatherproof Switch Plates, Covers and Locking Covers	K-25
Heavy Duty Weatherproof Covers	K-26
Weatherproof Covers	K-27
While-In-Use Weatherproof Covers	K-28
Screws and Accessories	K-30
Technical Information	K-31
Wallplate Dimensions	K-32
Custom Metal Wallplates	K-33

Features and Benefits



Nylon Wallplates



Metal Wallplates



Weatherproof Covers





Wallplates

Nylon Wallplates

Features and Benefits



Hubbell offers a wide variety of configurations, sizes, and finishes in both metal and nylon wallplates for use in industrial, institutional, commercial, and residential applications. We offer finishes in nylon, aluminum, brass, brass plated, chrome, and stainless steel.

We have totally redesigned and expanded our line of nylon wallplates featuring larger standard sized wallplates to give extra coverage to hide rough box opening, improved aesthetics, greater strength, impact resistance, along with excellent cleanability in all different types of environments.

- Standard size is $\frac{1}{8}$ inch larger to give you extra coverage to hide rough box openings. Also available in mid-size and pre-marked.
- Curved corners for improved aesthetics, for use in any application.
- Reinforcement ribs for extra strength.
- Captive screw feature holds mounting screw in place for quick and easy installation.
- High-impact, self-extinguishing nylon material, which is virtually unbreakable.
- Smooth, easy to clean finish is highly resistant to solvents and cleaning solutions, providing long life in the harshest environments.
- Non-conductive material.

Nylon wallplates are designed for durability and easy cleaning. Hubbell's standard sized wallplates are $\frac{1}{8}$ inch larger to give you that extra coverage to hide rough box openings. The depth is $\frac{1}{4}$ inch so that it will comfortably fit over the device even on imperfect installations or on retrofit work.

Nylon Wallplates



Nylon Pre-Marked Wallplates





Wallplates

Metal Wallplates

Features and Benefits



Protective film helps to prevent scratches and damage.

Stainless Steel

Provide solutions for a variety of industrial and commercial applications; with environments subjected to heavy abuse.

- The 302/304 type stainless steel wallplates are ideal for highly corrosive environments such as food processing, hospitals, static free requirements and more.

Non-magnetic:

18.0% Chromium

8.0% Nickel

- The 430 type stainless steel wallplates are aesthetically identical to the 302/304 type stainless steel wallplates and are best suited for environments where corrosion resistance is less critical.

Magnetic:

17.0% Chromium

Less than 0.5% Nickel

Smooth Solid Brass

- Provides a plush appearance with the durability of metal.
- Finish is lacquer coated to inhibit oxidation.

Anodized Aluminum

- Non-magnetic and corrosion resistance for a wide range of applications.
- Finish is lacquer coated to inhibit oxidation.

Metallic Plated Steel

- Available in either chrome or brass finishes.




Custom Metal Wallplates

Hubbell offers 40 custom configurations from 2-gang to 8-gang, in five different metal finishes. These custom openings can be configured in any combination to meet your specific requirements.


Metal Wallplates

Pre-Marked








Wallplates
Snap-On Wallplates



Toggle Snap-On Wallplates







Description	Color	Catalog Number
Snap-On Wallplate, 1-Gang, 1-Toggle Style	Ivory White	RFW1I RFW1W
		
Snap-On Wallplate, 2-Gang, 2-Toggle Style	Ivory White	RFW2I RFW2W
		
Snap-On Wallplate, 3-Gang, 3-Toggle Style	Ivory White	RFW3I RFW3W
		



Wallplates

Decorator Snap-On Wallplates

Decorator Snap-On Wallplates









Description	Color	Catalog Number
Snap-On Wallplate, 1-Gang, 1-Decorator 	Almond Ivory Light Almond White	RCW1AL RCW1I RCW1LA RCW1W
Snap-On Wallplate, 2-Gang, 2-Decorator 	Almond Ivory Light Almond White	RCW2AL RCW2I RCW2LA RCW2W
Snap-On Wallplate, 3-Gang, 3-Decorator 	Almond Ivory Light Almond White	RCW3AL RCW3I RCW3LA RCW3W
Snap-On Wallplate, 4-Gang, 4-Decorator 	Almond Ivory Light Almond White	RCW4AL RCW4I RCW4LA RCW4W
Snap-On Wallplate, 5-Gang, 5-Decorator 	Almond Ivory Light Almond White	RCW5AL RCW5I RCW5LA RCW5W
Snap-On Wallplate, 6-Gang, 6-Decorator 	Almond Ivory Light Almond White	RCW6AL RCW6I RCW6LA RCW6W



Wallplates

Toggle Switch Wallplates

Toggle Switch Wallplates

Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number
1-Gang, 1-Toggle 	Almond Black Brown Gray Ivory Light Almond Office White Red White	NP1AL NP1BK NP1 NP1GY NP1I NP1LA NP1OW NP1R NP1W	NPJ1AL NPJ1BK NPJ1 NPJ1GY NPJ1I NPJ1LA NPJ1OW NPJ1R NPJ1W	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430 S/S Beveled Steel, Almond* Steel, Gray*	SA1 SB1 SBP1 SCH1 SS1 SS1L 97071 SP1AL SP1G
2-Gang, 2-Toggle 	Almond Black Brown Gray Ivory Light Almond Office White Red White	NP2AL NP2BK NP2 NP2GY NP2I NP2LA NP2OW NP2R NP2W	NPJ2AL NPJ2BK NPJ2 NPJ2GY NPJ2I NPJ2LA NPJ2OW NPJ2R NPJ2W	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430 Steel, Almond* Steel, Gray*	SA2 SB2 SBP2 SCH2 SS2 SS2L SP2AL SP2G
3-Gang, 3-Toggle 	Almond Black Brown Gray Ivory Light Almond Office White Red White	NP3AL NP3BK NP3 NP3GY NP3I NP3LA NP3OW - NP3W	NPJ3AL NPJ3BK NPJ3 NPJ3GY NPJ3I NPJ3LA NPJ3OW NPJ3R NPJ3W	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430 Steel, Almond*	① SB3 SBP3 SCH3 SS3 SS3L SP3AL
4-Gang, 4-Toggle 	Almond Black Brown Gray Ivory Light Almond Office White White	NP4AL NP4BK NP4 NP4GY NP4I NP4LA NP4OW NP4W	NPJ4AL NPJ4BK NPJ4 NPJ4GY NPJ4I NPJ4LA NPJ4OW NPJ4W	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430 Steel, Almond*	① SB4 SBP4 ① SS4 SS4L SP4AL
5-Gang, 5-Toggle 	Almond Black Brown Gray Ivory Light Almond White	NP5AL NP5BK NP5 NP5GY NP5I NP5LA NP5W	- - - - - - -	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430 Steel, Almond*	① SB5 ① ① SS5 - SP5AL
6-Gang, 6-Toggle 	Almond Brown Gray Ivory Light Almond White	NP6AL NP6 NP6GY NP6I NP6LA NP6W	- - - - - -	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430 Steel, Almond*	① SB6 ① ① SS6 - SP6AL
7-Gang, 7-Toggle 	Almond Brown Gray Ivory White	- - - - -	- - - - -	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	① ① ① ① SS607 -
8-Gang, 8-Toggle 	Almond Brown Gray Ivory White	- - - - -	- - - - -	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	① ① ① ① SS608 -
2-Gang, 1-Toggle 	Almond Brown Gray Ivory White	- - - - -	- - - - -	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	- - - - SS740 -

Note: All standard and mid-size nylon wallplates feature pre-inserted captive screws for faster assembly, up to 6-gang.

① Available as a custom wallplate. See pages K-33 to K-38. Consult custom wallplates section for additional openings and combinations.






* Powder coat paint finish.






Wallplates

Duplex and Single Receptacle Wallplates

Duplex Receptacle Wallplates

Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number
1-Gang, 1-Duplex 	Almond	NP8AL	NPJ8AL	Aluminum	SA8
	Black	NP8BK	NPJ8BK	Brass	SB8
	Blue	-	NPJ8BL	Brass Plated	SBP8
	Brown	NP8	NPJ8	Chrome	SCH8
	Gray	NP8GY	NPJ8GY	S/S 302/304	SS8
	Ivory	NP8I	NPJ8I	S/S 430	SS8L
	Light Almond	NP8LA	NPJ8LA	S/S Beveled	97101
	Office White	NP8OW	NPJ8OW	Steel, Almond*	SP8AL
	Orange	NP8OR	-	Steel, Gray*	SP8G
	Red	NP8R	NPJ8R		
	White	NP8W	NPJ8W		
2-Gang, 2-Duplex 	Almond	NP82AL	NPJ82AL	Aluminum	SA82
	Black	NP82BK	NPJ82BK	Brass	SB82
	Brown	NP82	NPJ82	Brass Plated	SBP82
	Gray	NP82GY	NPJ82GY	Chrome	SCH82
	Ivory	NP82I	NPJ82I	S/S 302/304	SS82
	Light Almond	NP82LA	NPJ82LA	S/S 430	SS82L
	Office White	NP82OW	NPJ82OW	Steel, Almond*	SP82AL
	Orange	NP82OR	-	Steel, Gray*	SP82G
	Red	NP82R	NPJ82R		
	White	NP82W	NPJ82W		
3-Gang, 3-Duplex 	Almond	NP83AL	-	Aluminum	①
	Black	NP83BK	-	Brass	①
	Brown	NP83	-	Brass Plated	①
	Gray	NP83GY	-	Chrome	①
	Ivory	NP83I	-	S/S 302/304	SS83
	White	NP83W	-	S/S 430	-
				Steel, Almond*	SP83AL
4-Gang, 4-Duplex 	Almond	NP84AL	-	Aluminum	①
	Black	NP84BK	-	Brass	①
	Brown	NP84	-	Brass Plated	①
	Gray	NP84GY	-	Chrome	①
	Ivory	NP84I	-	S/S 302/304	SS84
	White	NP84W	-	S/S 430	-
2-Gang, 1-Duplex 	-	-	-	Brass	-
	-	-	-	Brass Plated	-
	-	-	-	Chrome	-
	-	-	-	S/S 302/304	SS748
	-	-	-	S/S 430	-

Single 15/20A Straight Blade or 15A Twist-Lock® Receptacle Wallplates

Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number
1-Gang, 1-Single 1.40 in. (35.6) Dia. Hole 	Almond	NP7AL	NPJ7AL	Aluminum	SA7
	Black	NP7BK	NPJ7BK	Brass	SB7
	Brown	NP7	NPJ7	Brass Plated	SBP7
	Gray	NP7GY	NPJ7GY	Chrome	SCH7
	Ivory	NP7I	NPJ7I	S/S 302/304	SS7
	Light Almond	NP7LA	NPJ7LA	S/S 430	SS7L
	Office White	NP7OW	NPJ7OW	Steel, Almond*	SP7AL
	Red	NP7R	NPJ7R	Steel, Gray*	SP7G
	White	NP7W	NPJ7W		
2-Gang, 1-Single 1.40 in. (35.6) Dia. Hole 	-	-	-	Aluminum	-
	-	-	-	Brass	-
	-	-	-	Brass Plated	-
	-	-	-	Chrome	-
	-	-	-	S/S 302/304	SS747
	-	-	-	S/S 430	-
2-Gang, 2-Single 1.40 in. (35.6) Dia. Hole 	-	-	-	Aluminum	①
	-	-	-	Brass	①
	-	-	-	Brass Plated	①
	-	-	-	Chrome	①
	-	-	-	S/S 302/304	SS72
	-	-	-	S/S 430	-

Note: All standard and mid-size nylon wallplates feature pre-inserted captive screws for faster assembly, up to 6-gang.

①Available as a custom wallplate. See pages K-33 to K-38. Consult custom wallplates section for additional openings and combinations.





* Powder coat paint finish.









Wallplates

Single Receptacle Wallplates

Single 20/30A Twist-Lock® Receptacle Wallplates

Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number
	Almond	NP720AL	-	Aluminum	SA720
	Black	NP720BK	-	Brass	SB720
	Brown	NP720	-	Brass Plated	①
	Gray	NP720GY	-	Chrome	①
	Ivory	NP720I	-	S/S 302/304	SS720
	Office White	NP720OW	-	S/S 430	-
	Red	NP720R	-		
	White	NP720W	-		
	-	-	-	Aluminum	-
	-	-	-	Brass	-
	-	-	-	Brass Plated	-
	-	-	-	Chrome	-
	-	-	-	S/S 302/304	SS725
	-	-	-	S/S 430	-
	-	-	-	Aluminum	-
	-	-	-	Brass	-
	-	-	-	Brass Plated	-
	-	-	-	Chrome	-
	-	-	-	S/S 302/304	SS749
	-	-	-	S/S 430	-
	-	-	-	Aluminum	-
	-	-	-	Brass	-
	-	-	-	Brass Plated	-
	-	-	-	Chrome	-
	-	-	-	S/S 302/304	SS320
	-	-	-	S/S 430	-
	-	-	-	Aluminum	-
	-	-	-	Brass	-
	-	-	-	Brass Plated	-
	-	-	-	Chrome	-
	-	-	-	S/S 302/304	SS330
	-	-	-	S/S 430	-
	-	-	-		

Single Receptacle Wallplates

Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number
	Almond	NP724AL	NPJ724AL	Aluminum	SA723
	Black	NP724BK	NPJ724BK	Brass	①
	Brown	NP724	NPJ724	Brass Plated	①
	Gray	NP724GY	NPJ724GY	Chrome	SCH723
	Ivory	NP724I	NPJ724I	S/S 302/304	SS723
	White	NP724W	NPJ724W	S/S 430	SS723L
	-	-	-	Aluminum	-
	-	-	-	Brass	-
	-	-	-	Brass Plated	-
	-	-	-	Chrome	SCH702
	-	-	-	S/S 302/304	SS702
	-	-	-	S/S 430	-
	Almond	NP703AL	NPJ703AL	Aluminum	-
	Black	NP703BK	NPJ703BK	Brass	-
	Brown	NP703	NPJ703	Brass Plated	-
	Gray	NP703GY	NPJ703GY	Chrome	-
	Ivory	NP703I	NPJ703I	S/S 302/304	SS703
	White	NP703W	NPJ703W	S/S 430	SS703L
	-	-	-	Aluminum	-
	-	-	-	Brass	-
	-	-	-	Brass Plated	-
	-	-	-	Chrome	-
	-	-	-	S/S 302/304	SS701
	-	-	-	S/S 430	-
	-	-	-	Aluminum	-
	-	-	-	Brass	-
	-	-	-	Brass Plated	-
	-	-	-	Chrome	-
	-	-	-	S/S 302/304	SS716
	-	-	-	S/S 430	-
	-	-	-		

Note: All standard and mid-size nylon wallplates feature pre-inserted captive screws for faster assembly, up to 6-gang.







① Available as a custom wallplate. See pages K-33 to K-38. Consult custom wallplates section for additional openings and combinations.



Wallplates

Blank Wallplates

Blank Wallplates, Box Mount and Strap Mount

Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number
 1-Gang, 1-Blank, Box Mount	Almond	NP13AL	NPJ13AL	Aluminum	SA13A
	Black	NP13BK	NPJ13BK	Brass	SB13
	Brown	NP13	NPJ13	Brass Plated	SBP13
	Gray	NP13GY	NPJ13GY	Chrome	SCH13
	Ivory	NP13I	NPJ13I	S/S 302/304	SS13
	Light Almond	NP13LA	NPJ13LA	S/S 430	SS13L
	Office White	NP13OW	NPJ13OW	Steel, Almond*	SP14BAL
	White	NP13W	NPJ13W	Steel, Gray*	SP14BG
 2-Gang, 2-Blank, Box Mount	Almond	NP23AL	NPJ23AL	Aluminum	SA23
	Black	NP23BK	-	Brass	SB23
	Brown	NP23	NPJ23	Brass Plated	①
	Gray	NP23GY	-	Chrome	SCH23
	Ivory	NP23I	NPJ23I	S/S 302/304	SS23
	Light Almond	NP23LA	NPJ23LA	S/S 430	SS23L
	Office White	NP23OW	NPJ23OW	Steel, Almond*	SP24BAL
	White	NP23W	NPJ23W	Steel, Gray*	SP24BG
 3-Gang, 3-Blank, Box Mount	Almond	NP33AL	-	Aluminum	①
	Brown	NP33	-	Brass	①
	Ivory	NP33I	-	Brass Plated	①
	White	NP33W	-	Chrome	①
				S/S 302/304	SS33
				S/S 430	-
				Steel, Almond*	SP34BAL
 4-Gang, 4-Blank, Box Mount	Almond	NP43AL	-	Aluminum	①
	Brown	NP43	-	Brass	①
	Ivory	NP43I	-	Brass Plated	①
	White	NP43W	-	Chrome	①
				S/S 302/304	SS43
				S/S 430	-
 1-Gang, 1-Blank, Strap Mount	Almond	NP14AL	-	Aluminum	①
	Black	NP14BK	-	Brass	SB14
	Brown	NP14	-	Brass Plated	①
	Gray	NP14GY	-	Chrome	①
	Ivory	NP14I	-	S/S 302/304	SS14
	Office White	NP14OW	-	S/S 430	SS14L
	Red	NP14R	-	Steel, Almond*	SP14AL
	White	NP14W	-	Steel, Gray*	SP14G
 2-Gang, 2-Blank, Strap Mount	Almond	NP24AL	-	Aluminum	①
	Black	NP24BK	-	Brass	①
	Brown	NP24	-	Brass Plated	①
	Gray	NP24GY	-	Chrome	①
	Ivory	NP24I	-	S/S 302/304	SS24
	Office White	NP24OW	-	S/S 430	SS24L
	Red	NP24R	-	Steel, Almond*	SP24AL
	White	NP24W	-	Steel, Gray*	SP24G
 3-Gang, 3-Blank, Strap Mount	Almond	NP34AL	-	Aluminum	①
	Brown	NP34	-	Brass	①
	Ivory	NP34I	-	Brass Plated	①
	White	NP34W	-	Chrome	①
				S/S 302/304	SS34
				S/S 430	-
				Steel, Almond*	SP34AL
 4-Gang, 4-Blank, Strap Mount	Almond	NP44AL	-	Aluminum	①
	Brown	NP44	-	Brass	①
	Ivory	NP44I	-	Brass Plated	①
	White	NP44W	-	Chrome	①
				S/S 302/304	SS44
				S/S 430	-

Note: All standard and mid-size nylon wallplates feature pre-inserted captive screws for faster assembly, up to 6-gang.

① Available as a custom wallplate. See pages K-33 to K-38. Consult custom wallplates section for additional openings and combinations.




* Powder coat paint finish.






Wallplates

347 Volt Wallplates

347 Volt Toggle Wallplates with 2.25" (57.2) Spacing Between Gangs, Stamped "347V"

Description	Color	Nylon Catalog Number	Material	Metal Catalog Number
1-Gang, 1-Toggle 2.25 in. (57.2) Spacing 	-	-	Aluminum	-
	-	-	Brass	-
	-	-	Brass Plated	-
	-	-	Chrome	-
	-	-	S/S 302/304	SS1C
	-	-	S/S 430	-
2-Gang, 2-Toggle 2.25 in. (57.2) Spacing 	-	-	Aluminum	-
	-	-	Brass	-
	-	-	Brass Plated	-
	-	-	Chrome	-
	-	-	S/S 302/304	SS2C
	-	-	S/S 430	-
3-Gang, 3-Toggle 2.25 in. (57.2) Spacing 	-	-	Aluminum	-
	-	-	Brass	-
	-	-	Brass Plated	-
	-	-	Chrome	-
	-	-	S/S 302/304	SS3C
	-	-	S/S 430	-
4-Gang, 4-Toggle 2.25 in. (57.2) Spacing 	-	-	Aluminum	-
	-	-	Brass	-
	-	-	Brass Plated	-
	-	-	Chrome	-
	-	-	S/S 302/304	SS4C
	-	-	S/S 430	-
5-Gang, 5-Toggle 2.25 in. (57.2) Spacing 	-	-	Aluminum	-
	-	-	Brass	-
	-	-	Brass Plated	-
	-	-	Chrome	-
	-	-	S/S 302/304	SS5C
	-	-	S/S 430	-
6-Gang, 6-Toggle 2.25 in. (57.2) Spacing 	-	-	Aluminum	-
	-	-	Brass	-
	-	-	Brass Plated	-
	-	-	Chrome	-
	-	-	S/S 302/304	SS6C
	-	-	S/S 430	-

347 Volt Decorator Wallplates

Description	Color	Nylon Catalog Number	Material	Metal Catalog Number
1-Gang, 1-Decorator 	Black	HPS1347BK	Aluminum	-
	Gray	HPS1347GY	Brass	-
	Ivory	HPS1347I	Brass Plated	-
	White	HPS1347W	Chrome	-
			S/S 302/304	-
			S/S 430	-
2-Gang, 2-Decorator 	Black	HPS2347BK	Aluminum	-
	Gray	HPS2347GY	Brass	-
	Ivory	HPS2347I	Brass Plated	-
	White	HPS2347W	Chrome	-
			S/S 302/304	-
			S/S 430	-
3-Gang, 3-Decorator 	Ivory	HPS3347I	Aluminum	-
	White	HPS3347W	Brass	-
			Brass Plated	-
			Chrome	-
			S/S 302/304	-
			S/S 430	-







Note: All standard and mid-size nylon wallplates feature pre-inserted captive screws for faster assembly, up to 6-gang.



Wallplates

Decorator Wallplates

GFCI, Surge Receptacles and Style Line® Device Wallplates

Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number
	Almond	NP26AL	NPJ26AL	Aluminum	①
	Black	NP26BK	NPJ26BK	Brass	SB26
	Blue	—	NPJ26BL	Brass Plated	SBP26
	Brown	NP26	NPJ26	Chrome	SCH26
	Gray	NP26GY	NPJ26GY	S/S 302/304	SS26
	Ivory	NP26I	NPJ26I	S/S 430	SS26L
	Light Almond	NP26LA	NPJ26LA	Steel, Almond*	PHPS1AL
	Office White	NP26OW	NPJ26OW	Steel, Gray*	PHPS1G
	Red	NP26R	NPJ26R		
	White	NP26W	NPJ26W		
	Almond	NP262AL	NPJ262AL	Aluminum	①
	Black	NP262BK	NPJ262BK	Brass	SB262
	Brown	NP262	NPJ262	Brass Plated	SBP262
	Gray	NP262GY	NPJ262GY	Chrome	SCH262
	Ivory	NP262I	NPJ262I	S/S 302/304	SS262
	Light Almond	NP262LA	NPJ262LA	S/S 430	SS262L
	Office White	NP262OW	NPJ262OW	Steel, Almond*	PHPS2AL
	Red	NP262R	NPJ262R	Steel, Gray*	PHPS2G
	White	NP262W	NPJ262W		
	Almond	NP263AL	NPJ263AL	Aluminum	①
	Black	NP263BK	NPJ263BK	Brass	①
	Brown	NP263	NPJ263	Brass Plated	SBP263
	Gray	NP263GY	NPJ263GY	Chrome	①
	Ivory	NP263I	NPJ263I	S/S 302/304	SS263
	Light Almond	NP263LA	NPJ263LA	S/S 430	—
	Office White	NP263OW	NPJ263OW	Steel, Almond*	PHPS3AL
	Red	NP263R	NPJ263R		
	White	NP263W	NPJ263W		
	Almond	NP264AL	NPJ264AL	Aluminum	①
	Black	NP264BK	NPJ264BK	Brass	①
	Brown	NP264	NPJ264	Brass Plated	①
	Gray	NP264GY	NPJ264GY	Chrome	①
	Ivory	NP264I	NPJ264I	S/S 302/304	SS264
	Light Almond	NP264LA	NPJ264LA	S/S 430	—
	Office White	NP264OW	NPJ264OW	Steel, Almond*	PHPS4AL
	White	NP264W	NPJ264W		
	Almond	NP265AL	—	Aluminum	①
	Black	NP265BK	—	Brass	①
	Brown	NP265	—	Brass Plated	①
	Gray	NP265GY	—	Chrome	①
	Ivory	NP265I	—	S/S 302/304	SS265
	Light Almond	NP265LA	—	S/S 430	—
	White	NP265W	—	Steel, Almond*	PHPS5AL
	Almond	NP266AL	—	Aluminum	①
	Black	NP266BK	—	Brass	①
	Brown	NP266	—	Brass Plated	①
	Gray	NP266GY	—	Chrome	①
	Ivory	NP266I	—	S/S 302/304	SS266
	Light Almond	NP266LA	—	S/S 430	—
	White	NP266W	—	Steel, Almond*	PHPS6AL

Note: All standard and mid-size nylon wallplates feature pre-inserted captive screws for faster assembly, up to 6-gang.

① Available as a custom wallplate. See pages K-33 to K-38. Consult custom wallplates section for additional openings and combinations.









* Powder coat paint finish.



Wallplates

Combination Wallplates, 2-Gang

Combination Wallplates, 2-Gang

Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number
2-Gang, 1-Toggle, 1-Duplex 	Almond Black Brown Gray Ivory Light Almond Office White Red White	NP18AL NP18BK NP18 NP18GY NP18I NP18LA NP18OW NP18R NP18W	NPJ18AL NPJ18BK NPJ18 NPJ18GY NPJ18I NPJ18LA NPJ18OW NPJ18R NPJ18W	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430 Steel, Almond* Steel, Gray*	① ① SBP18 SCH18 SS18 SS18L SP18AL SP18G
2-Gang, 1-Duplex, 1-Decorator 	Almond Black Brown Gray Ivory Light Almond Office White White	NP826AL NP826BK NP826 NP826GY NP826I NP826LA NP826OW NP826W	NPJ826AL NPJ826BK NPJ826 NPJ826GY NPJ826I NPJ826LA NPJ826OW NPJ826W	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	① SB826 ① ① SS826 -
2-Gang, 1-Toggle, 1-Decorator 	Almond Black Brown Gray Ivory Light Almond White	NP126AL NP126BK NP126 NP126GY NP126I NP126LA NP126W	NPJ126AL NPJ126BK NPJ126 NPJ126GY NPJ126I NPJ126LA NPJ126W	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430 Steel, Almond* Steel, Gray*	① SB126 SBP126 ① SS126 SS126L PJS126AL PJS126G
2-Gang, 1-Duplex, 1-Telephone  .406 in. (10.3) Hole Strap Mount	Almond Black Brown Gray Ivory White	NP128AL NP128BK NP128 NP128GY NP128I NP128W	- - - - - -	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	- - - - - -
2-Gang, 1-Toggle, 1-Telephone  .406 in. (10.3) Hole Strap Mount	Almond Black Brown Gray Ivory Office White White	NP112AL NP112BK NP112 NP112GY NP112I NP112OW NP112W	- - - - - - -	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	- - - - - -
2-Gang, 1-Decorator, 1-Telephone  .406 in. (10.3) Hole Strap Mount	Almond Black Brown Gray Ivory White	NP1226AL NP1226BK NP1226 NP1226GY NP1226I NP1226W	- - - - - -	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	- - - - - -
2-Gang, 1-Single Receptacle  1.40 in. (35.6) Hole, 1-Duplex	Almond Brown Gray Ivory White	NP78AL NP78 NP78GY NP78I NP78W	- - - - -	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	① ① ① ① SS78 -
2-Gang, 1-Single Recept.  1.60 in. (40.6) Hole, 1-Duplex	Almond Brown Ivory White	- - - -	- - - -	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	① ① ① ① SS8720 -

Note: All standard and mid-size nylon wallplates feature pre-inserted captive screws for faster assembly, up to 6-gang.

① Available as a custom wallplate. See pages K-33 to K-38. Consult custom wallplates section for additional openings and combinations.









* Powder coat paint finish.



Wallplates

Combination Wallplates, 2-Gang

Combination Wallplates, 2-Gang

Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number
 2-Gang, 1-Toggle, 1-Single Receptacle 1.40 in. (35.6) Hole	Almond	NP17AL	–	Aluminum	①
	Black	NP17BK	–	Brass	①
	Brown	NP17	–	Brass Plated	①
	Gray	NP17GY	–	Chrome	①
	Ivory	NP17I	–	S/S 302/304	SS17
	White	NP17W	–	S/S 430	–
 2-Gang, 1-Toggle, 1-Blank, Box Mount	Almond	NP113AL	NPJ113AL	Aluminum	①
	Black	NP113BK	–	Brass	①
	Brown	NP113	NPJ113	Brass Plated	①
	Gray	NP113GY	–	Chrome	①
	Ivory	NP113I	NPJ113I	S/S 302/304	SS113
	Light Almond	NP113LA	–	S/S 430	–
 2-Gang, 1-Toggle, 1-Blank, Strap Mount	Almond	–	–	Aluminum	①
	Brown	–	–	Brass	①
	Ivory	–	–	Brass Plated	①
	Light Almond	–	–	Chrome	①
	White	–	–	S/S 302/304	SS114
				S/S 430	–
 2-Gang, 1-Blank, 1-Duplex, Box Mount	Almond	NP138AL	NPJ138AL	Aluminum	①
	Black	NP138BK	–	Brass	①
	Brown	NP138	NPJ138	Brass Plated	①
	Gray	NP138GY	–	Chrome	①
	Ivory	NP138I	NPJ138I	S/S 302/304	SS138
	Light Almond	NP138LA	–	S/S 430	–
 2-Gang, 1-Blank, 1-Duplex, Strap Mount	Almond	–	–	Aluminum	①
	Brown	–	–	Brass	①
	Ivory	–	–	Brass Plated	①
	White	–	–	Chrome	①
				S/S 302/304	SS148
				S/S 430	–
 2-Gang, 1-Blank, 1-Decorator, Box Mount	Almond	NP1326AL	NPJ1326AL	Aluminum	①
	Black	NP1326BK	NPJ1326BK	Brass	①
	Brown	NP1326	NPJ1326	Brass Plated	①
	Gray	NP1326GY	NPJ1326GY	Chrome	①
	Ivory	NP1326I	NPJ1326I	S/S 302/304	SS1426*
	Light Almond	NP1326LA	NPJ1326LA	S/S 430	–
 2-Gang, 1-Telephone, .406 in. (10.3) Hole, 1-Blank, Strap Mount	Almond	NP1214AL	–	Aluminum	–
	Black	NP1214BK	–	Brass	–
	Brown	NP1214	–	Brass Plated	–
	Gray	NP1214GY	–	Chrome	–
	Ivory	NP1214I	–	S/S 302/304	–
	White	NP1214W	–	S/S 430	–
 2-Gang, 1-Single Receptacle 1.40 in. (35.6) Hole 1-Blank, Strap Mount	Almond	NP147AL	–	Aluminum	–
	Black	NP147BK	–	Brass	–
	Brown	NP147	–	Brass Plated	–
	Gray	NP147GY	–	Chrome	–
	Ivory	NP147I	–	S/S 302/304	–
	White	NP147W	–	S/S 430	–

Note: All standard and mid-size nylon wallplates feature pre-inserted captive screws for faster assembly, up to 6-gang.

① Available as a custom wallplate. See pages K-33 to K-38. Consult custom wallplates section for additional openings and combinations.








* Strap Mount.



Wallplates

Combination Wallplates, 3-Gang

Combination Wallplates, 3-Gang

Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number
	Almond	NP28AL	NPJ28AL	Aluminum	①
	Black	NP28BK	—	Brass	①
	Brown	NP28	NPJ28	Brass Plated	SBP28
	Gray	NP28GY	—	Chrome	①
	Ivory	NP28I	NPJ28I	S/S 302/304	SS28
	Light Almond	NP28LA	NPJ28LA	S/S 430	—
	Office White	NP28OW	—	Steel, Almond*	SP28AL
	White	NP28W	NPJ28W	Steel, Gray*	SP28G
	Almond	NP182AL	—	Aluminum	①
	Black	NP182BK	—	Brass	①
	Brown	NP182	—	Brass Plated	①
	Gray	NP182GY	—	Chrome	①
	Ivory	NP182I	—	S/S 302/304	SS182
	White	NP182W	—	S/S 430	—
	Almond	NP226AL	NPJ226AL	Aluminum	①
	Black	NP226BK	NPJ226BK	Brass	①
	Brown	NP226	NPJ226	Brass Plated	①
	Gray	NP226GY	NPJ226GY	Chrome	①
	Ivory	NP226I	NPJ226I	S/S 302/304	SS226
	Light Almond	NP226LA	NPJ226LA	S/S 430	—
	White	NP226W	NPJ226W	Steel, Gray*	PJS226G
	Almond	NP1262AL	—	Aluminum	①
	Black	NP1262BK	—	Brass	①
	Brown	NP1262	—	Brass Plated	①
	Gray	NP1262GY	—	Chrome	①
	Ivory	NP1262I	—	S/S 302/304	①
	Light Almond	NP1262LA	—	S/S 430	—
	White	NP1262W	—		
	Almond	—	—	Aluminum	①
	Brown	—	—	Brass	①
	Ivory	—	—	Brass Plated	①
	White	—	—	Chrome	①
				S/S 302/304	SS211
				S/S 430	—
	Almond	—	—	Aluminum	①
	Brown	—	—	Brass	①
	Ivory	—	—	Brass Plated	①
	White	—	—	Chrome	①
				S/S 302/304	SS8147
				S/S 430	—
	Almond	—	—	Aluminum	①
	Brown	—	—	Brass	①
	Ivory	—	—	Brass Plated	①
	White	—	—	Chrome	①
				S/S 302/304	SS213
				S/S 430	—

Note: All standard and mid-size nylon wallplates feature pre-inserted captive screws for faster assembly, up to 6-gang.

① Available as a custom wallplate. See pages K-33 to K-38. Consult custom wallplates section for additional openings and combinations.





* Powder coat paint finish.



Wallplates

Combination Wallplates, 4- and 5-Gang

Combination Plates, 4- and 5-Gang

Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number
4-Gang, 3-Toggle, 1-Duplex 	Almond	NP38AL	—	Aluminum	①
	Black	NP38BK	—	Brass	①
	Brown	NP38	—	Brass Plated	①
	Gray	NP38GY	—	Chrome	①
	Ivory	NP38I	—	S/S 302/304	SS38
	Light Almond	NP38LA	—	S/S 430	—
	White	NP38W	—		
4-Gang, 3-Toggle, 1-Decorator 	Almond	NP326AL	—	Aluminum	①
	Black	NP326BK	—	Brass	①
	Brown	NP326	—	Brass Plated	①
	Gray	NP326GY	—	Chrome	①
	Ivory	NP326I	—	S/S 302/304	SS326
	Light Almond	NP326LA	—	S/S 430	—
	White	NP326W	—		
4-Gang, 2-Toggle, 2-Decorator 	Almond	NP2262AL	—	Aluminum	①
	Black	NP2262BK	—	Brass	①
	Brown	NP2262	—	Brass Plated	①
	Gray	NP2262GY	—	Chrome	①
	Ivory	NP2262I	—	S/S 302/304	①
	Light Almond	NP2262LA	—	S/S 430	—
	White	NP2262W	—		
5-Gang, 4-Toggle, 1-Duplex 	Almond	NP48AL	—	Aluminum	①
	Brown	NP48	—	Brass	①
	Ivory	NP48I	—	Brass Plated	①
	White	NP48W	—	Chrome	①
				S/S 302/304	①
				S/S 430	—

Note: All standard and mid-size nylon wallplates feature pre-inserted captive screws for faster assembly, up to 6-gang.







① Available as a custom wallplate. See pages K-33 to K-38. Consult custom wallplates section for additional openings and combinations.



Wallplates

Telephone and Coaxial Outlet Plates

Telephone and Coaxial Outlet Plates

Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number
 1-Gang, 1-Tel Nylon .406 in. (10.3) Hole, Metal .640 in. (16.3) Hole, Box Mount	Almond	NP11AL	NPJ11AL	Aluminum	①
	Black	NP11BK	-	Brass	①
	Brown	NP11	NPJ11	Brass Plated	①
	Gray	NP11GY	-	Chrome	①
	Ivory	NP11I	NPJ11I	S/S 302/304	SS11*
	Light Almond	NP11LA	NPJ11LA	S/S 430	SS11L*
	Red	NP11R	-		
	White	NP11W	NPJ11W		
 1-Gang, 1-Tel Nylon .406 in. (10.3) Hole, Metal .640 in. (16.3) Hole, Strap Mount	Almond	NP12AL	-	Aluminum	①
	Black	NP12BK	-	Brass	SB12*
	Brown	NP12	-	Brass Plated	SBP12*
	Gray	NP12GY	-	Chrome	SCH12*
	Ivory	NP12I	-	S/S 302/304	SS12*
	White	NP12W	-	S/S 430	SS12L*
 1-Gang, 1-Tel .625 in. (15.9) Hole, Box Mount	Almond	NP737AL	-	Aluminum	-
	Brown	NP737	-	Brass	-
	Ivory	NP737I	-	Brass Plated	-
	White	NP737W	-	Chrome	-
				S/S 302/304	-
				S/S 430	-
 1-Gang, 1-Tel .625 in. (15.9) Hole, Strap Mount	Almond	NP730AL	-	Aluminum	-
	Black	NP730BK	-	Brass	-
	Brown	NP730	-	Brass Plated	-
	Gray	NP730GY	-	Chrome	-
	Ivory	NP730I	-	S/S 302/304	-
	White	NP730W	-	S/S 430	-
 1-Gang, 1-Tel .380 in. (9.7) Hole, Box Mount or Strap Mount	Almond	-	-	Aluminum	①
	Brown	-	-	Brass	①
	Ivory	-	-	Brass Plated	①
	White	-	-	Chrome	①
				S/S 302/304	SS739
				S/S 302/304, Strap Mount	SS738
				S/S 430	-
 2-Gang, 2-Tel Nylon .406 in. (10.3) Hole, Metal .640 in. (16.3) Hole, Box Mount	Almond	NP21AL	-	Aluminum	①
	Black	NP21BK	-	Brass	①
	Brown	NP21	-	Brass Plated	①
	Gray	NP21GY	-	Chrome	①
	Ivory	NP21I	-	S/S 302/304, Strap Mount	SS22*
	White	NP21W	-	S/S 430	-
 2-Gang, 1-Tel .640 in. (16.3) Hole, Box Mount	Almond	-	-	Aluminum	-
	Brown	-	-	Brass	-
	Ivory	-	-	Brass Plated	-
	White	-	-	Chrome	-
				S/S 302/304	SS741*
				S/S 430	-

Note: All standard and mid-size nylon wallplates feature pre-inserted captive screws for faster assembly, up to 6-gang.

① Available as a custom wallplate. See pages K-33 to K-38. Consult custom wallplates section for additional openings and combinations.









* .50" (12.7) I.D. nylon bushing provided.



Wallplates

Jumbo, Metal Wallplates

Jumbo, Smooth, Stainless Steel Type 302/304 Wallplates

Configuration	Catalog Number	Configuration	Catalog Number
1-Gang, 1-Toggle 	SSJ1	1-Gang, 1-Single Receptacle for 2.09–2.13 in. (53.1–54.1) Dia. Face 	SSJ723
2-Gang, 2-Toggle 	SSJ2	1-Gang, 1-Blank, Box Mount 	SSJ13
1-Gang, 1-Duplex 	SSJ8	1-Gang, 1-Telephone Opening, .640 in. (16.3) Box Mount 	SSJ11*
2-Gang, 2-Duplex 	SSJ82	2-Gang, 1-Toggle, 1-Duplex 	SSJ18
1-Gang, 1-Decorator 	SSJ26	2-Gang, 1-Toggle, 1-Decorator 	SSJ126
2-Gang, 2-Decorator 	SSJ262	3-Gang, 2-Toggle, 1-Decorator 	SSJ226
1-Gang, 1-Single Receptacle for 1.36–1.39 in. (34.5–35.3) Dia. Face 	SSJ7		


Note: *.50 in. (12.7) I.D. nylon bushing provided.
Specifications are subject to change without notice.

Oversize dimensions (see page K-32 for more details).

1-Gang, 5.25 in. x 3.50 in. (133.4 x 88.9).

2-Gang, 5.25 in. x 5.31 in. (133.4 x 134.9).

3-Gang, 5.25 in. x 7.12 in. (133.4 x 180.8).






Jumbo Wallplate



Wallplates

Pre-Marked "EMERGENCY" and Barrel Key Switch Wallplates

Pre-Marked "EMERGENCY" Wallplates



Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number
1-Gang, 1-Duplex 	Red	-	NPJ8RMEV	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	- - - - SS8MEV -
1-Gang, 1-Toggle 	Red	-	NPJ1RME	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	- - - - SS1ME -
2-Gang, 2 Duplex 	-	-	-	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	- - - - SS82MEV -

Note: Mid-size plate dimensions shown on page K-32.
All lettering .25 in. (6.3) high.



See page K-30 for security screwdriver and screws ordering information.

Stainless Steel Barrel Key Switch Wallplates

Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number
1-Gang, with on/off markings 	-	-	-	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	- - - - SS12RKL -
1-Gang, with position markings 	-	-	-	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	- - - - SS12RKLM -
2-Gang, with on/off markings 	-	-	-	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	- - - - SS22RKL -
2-Gang, with position markings 	-	-	-	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	- - - - SS22RKLM -





Note: See Section C, page C-8 for barrel key switch selection.






Wallplates

Pre-Marked Wallplates

Pre-Marked "ISOLATED GROUND" Wallplates

Description	Color	Nylon Standard	Nylon No Marking	Material	Metal Catalog Number
1-Gang, 1-Duplex 	Orange	NP80IG	NP80R	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	- - - - - -
1-Gang, 1-Decorator 	Orange	NP260IG	-	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	- - - - - -
1-Gang, 1-Single Recept. 1.40 in. (35.6) Hole for 1.36–1.39 in. (34.5–35.3) Dia. face 	Orange	NP70IG	-	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	- - - - - -
1-Gang, 1-Single Recept. 1.60 in. (40.6) Hole for 20 and 30A Twist-Lock® with 1.55–1.58 in. (39.4–40.1) Dia. face 	Orange	NP7200IG	-	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	- - - - - -

Pre-Marked "COMPUTER ONLY" Wallplates

Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number
1-Gang, 1-Duplex 	Orange Ivory	- -	NPJ8CO NPJ8C	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	- - - - - -
2-Gang, 2-Duplex 	Orange	-	NPJ82CO	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	- - - - - -
1-Gang, 1-Decorator 	Blue Ivory	- -	NPJ26CBL NPJ26C	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	- - - - - -

1-Gang Louver Plate, Box Mount

Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number
1-Gang, Vertical Mounted Louver 	- - - -	- - - -	- - - -	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	① SB771 SBP771 ① SS771 -

Note: * Mid-size plate dimensions shown on page K-32.

① Available as a custom wallplate. See pages K-33 to K-38. Consult custom wallplates section for additional openings and combinations.



Wallplates

Security Wallplates



SWP1



SWP8

1-Gang, White

Description	Catalog Number
1-Toggle switch	SWP1
1-Duplex receptacle	SWP8
1-GFCI/Style Line® opening	SWP26
1-Telephone or TV opening .640 in. (16.3)	SWP12
1-Blank	SWP13



SWP82



SWP18

2-Gang, White


Description	Catalog Number
2-Toggle switches	SWP2
2-Duplex receptacles	SWP82
1-Toggle switch, 1-Duplex receptacle	SWP18
2-GFCI/Style Line® openings	SWP262
1-Toggle switch, 1-GFCI/Style Line® opening	SWP126
1-Duplex receptacle, 1-Telephone or TV	SWP812
1-Duplex receptacle, 1-Blank	SWP813
2-Blank	SWP23



SWP28

3-Gang, White

Description	Catalog Number
2-Toggle switches, 1-Duplex receptacle	SWP28



Dimensions

	A	B	C	D	E	F	G	H
1-Gang (mm)	3.77" (95.8)	5.52" (140.2)	.55" (14.0)	3.37" (85.6)	5.13" (130.3)	1.00" (25.4)	4.63" (117.6)	2.88" (73.2)
2-Gang (mm)	5.52" (140.2)	5.52" (140.2)	.55" (14.0)	5.13" (130.3)	5.13" (130.3)	1.00" (25.4)	4.63" (117.6)	4.63" (117.6)
3-Gang (mm)	7.39" (187.71)	5.52" (140.21)	.55" (14.0)	7.00" (177.8)	5.13" (130.3)	1.00" (25.4)	4.63" (117.6)	6.50" (165.1)

Specifications

Tamper resistant wallplate 1-gang duplex receptacle shall be of the following construction:

Cover plate: One piece #14 cold rolled zinc plated steel. Plate shall have a five stage baked white polyester powder enamel finish. Gloss: 85%; reflectance: 93%; hardness minimum: 2H and pass 600 hour salt spray test.

Back plate: #10 cold rolled galvanized steel. Plate assembly shall use four (4) #8-32 X ½ inch stainless steel T-15 TORX® head screws with center pin reject. Plate must be UL listed to UL 514D and comply with the NEC®.

NEC® is a registered trademark of the The National Electrical Code.
TORX® is a registered trademark of Textron Inc.

Wallplates

Accessories and Selection Charts



Brass Locking Cover Plate

Description	Catalog Number
Locking cover plate for single 15 and 20A straight blade receptacles and 15A Twist-Lock® receptacles. Straight cylinder type lock. All cylinder locks keyed alike.	HBL96067



HBL96067
shown with receptacle
(sold separately)

Weather Shield Plate

Description	Catalog Number
20° angle plate for duplex receptacles.	HBL6187



HBL6187
shown with receptacle
and back box
(sold separately)

Catalog Number of Receptacles in Groups A through E below

Group A		Group B			Group C	Group D	Group E
Boss diameter 1.36" to 1.39" (34.5 to 35.3)		Boss diameter 1.55" to 1.58" (39.4 to 40.1)			Boss diameter 1.68" to 1.72" (42.7 to 43.7)	Boss diameter 2.09" to 2.13" (53.1 to 54.1)	Boss diameter 2.28" to 2.44" (57.9 to 62.0)
HBL23000HG	HBL5661	HBL23CM10	HBL2530	HBL2770	HBL45105	HBL7962	HBL7301A
HBL23030	HBL6810	HBL2310	HBL26CM10	HBL2810	HBL45205	HBL9350	HBL8330A
HBL4560	HBL7210B	HBL2320	HBL2610	HBL2820	HBL45305	HBL9308	HBL8350A
HBL4710	HBL7250	HBL2330	HBL2620	HBL2830	HBL45905	HBL9315	HBL8430A
HBL4760	HBL7310B	HBL2340	HBL2630	HBL3330		HBL9330	HBL8450A
HBL5251	HBL7310BG	HBL2410	HBL2640	HBL3330G		HBL9360•	HBL8460A
HBL52CM61	HBL7535	HBL2420	HBL2650	HBL3430		HBL9365•	HBL9430A
HBL5261	HBL7582	HBL2430	HBL2710	HBL3430G		HBL9367•	HBL9450A
HBL53CM61	HBL8210	HBL2440	HBL2720	HBL3520			HBL9460A
HBL5361	HBL8310	HBL2450	HBL2730	HBL7410B			
HBL5461	HBL8410	HBL2460	HBL2740	HBL7410BG			
HBL5552B	HBL8420	HBL2510	HBL2750				
		HBL2520	HBL2760				

Wallplates for Single Receptacles

Description	Group A		Group B		Group C		Group D		Group E
	Boss diameter 1.36" to 1.39" (34.5 to 35.3)		Boss diameter 1.55" to 1.58" (39.4 to 40.1)		Boss diameter 1.68" to 1.72" (42.7 to 43.7)		Boss diameter 2.09" to 2.13" (53.1 to 54.1)		Boss diameter 2.28" to 2.44" (57.9 to 62.0)
	1-Gang	2-Gang	1-Gang	2-Gang	1-Gang	2-Gang	1-Gang	2-Gang	2-Gang
Smooth nylon, brown.	NP7*	–	NP720*	–	–	–	NP724*	NP703*	–
Cast aluminum.	HBL7320	–	HBL7320	–	HBL3394	–	HBL9419	–	–
Stainless steel, 302/304, smooth.	SS7**	–	SS720	–	SS725	–	SS723	SS703	SS701

Note: See pages K-7 and K-8 for complete plate descriptions.

* Catalog number indicated is Brown, add with the following to designate color: "BK" for Black, "I" for Ivory.

** Catalog number indicated is Stainless Steel, replace "SS" with the following prefix to designate material: "SA" for Anodized Aluminum, "SB" for Solid Brass.

Weatherproof Lift Covers for WDL "Closed" and WDL "Open", Wet Locations, 1-Gang

Description	Group A	Group B	Group C	Group D		
	Boss diameter 1.36" to 1.39" (34.5 to 35.3)	Boss diameter 1.55" to 1.58" (39.4 to 40.1)	Boss diameter 1.68" to 1.72" (42.7 to 43.7)	Boss diameter 2.09" to 2.13" (53.1 to 54.1)	50A Twist-Lock® Receptacles	30A 4W Hubbell® Receptacles
Thermoplastic, with cover "open", gray.	HBL7423WO	HBL7425WOA	HBL7424WO	–	HBL7774WO [▲]	–
Thermoplastic, with cover "open", yellow.	HBL74CM23WO	HBL74CM25WOA	HBL74CM24WO	–	HBL77CM74WO [▲]	–
Cast aluminum, with cover "closed".	HBL7420	HBL7420	HBL3393	HBL9420 HBL9425*	HBL7770	HBL20405 [†] HBL20446 [†]

Note: • 50A 2P 3W.

[▲]The "CS" versions of 50A Twist-Lock® receptacles will only fit these thermoplastic plates.

[†] HBL20446 plate painted red for use with HBL20443 only. HBL20405 plate is for use with HBL20403 only. See Section B, page B-65 for devices.



Wallplates

Weatherproof Covers for Receptacles

For FS/FD Box Mounting

IP44
SUITABILITY**HBL7777A****HBL7774WO****HBL9420****HBL20405****HBL7770****For Receptacles with Face Diameters of 2.28–2.44 in. (57.9–62.0)**

Description	Catalog Number
Thermoplastic, 2-gang, WET LOCATIONS with cover “closed,” gray.	HBL7777A[▲]
Thermoplastic, 2-gang, WET LOCATIONS with cover “closed,” yellow.	HBL77CM77A[▲]
Thermoplastic, 2-gang, WET LOCATIONS with cover “closed,” gray.	HBL7777[▽]

For Receptacles with Face Diameters of 2.09–2.13 in. (53.1–54.1)

Description	Catalog Number
Cast aluminum, WET LOCATIONS with cover “closed.”	HBL9420
Cast aluminum, no lift cover, NOT weatherproof.	HBL9419

For 50A Twist-Lock[®] Single Receptacles

Description	Catalog Number
Thermoplastic, WET LOCATIONS with cover “open,” gray.	HBL7774WO[*]
Thermoplastic, WET LOCATIONS with cover “open,” yellow.	HBL77CM74WO[*]
Cast aluminum, WET LOCATIONS with cover “closed.”	HBL7770
Galvanized Steel, fits 4" square or 2-gang box.	HBL50SC

For 30A, 4 Wire Hubbellock[®] Receptacles



Description	Catalog Number
Cast aluminum, WET LOCATIONS with cover “closed.”	HBL20405
Cast aluminum, WET LOCATIONS with cover “closed,” red.	HBL20446
Cast aluminum, no lift cover, NOT weatherproof.	HBL20406

Note: [▲] Will fit FS/FD boxes having plate mounting holes on 3.25 in. x 3.75 in. (82.6 x 95.3) centers.[▽] Will only fit old style porcelain face devices.^{*} The “CS” versions of 50A Twist-Lock[®] will only fit these plates.**Weatherproof Covers for Single Receptacles for Use on FS/FD Boxes**

Note: All weatherproof plates are UL Listed for WET LOCATIONS WITH COVER CLOSED, for intermittent use in wet locations or use in damp locations. Those with suffix “WO” are listed for WET LOCATIONS with cover open in continuous use. All plates are gasketed and self-closing.

Accessories

Description	Catalog Number
Sub-plate for mounting and weatherproofing flanged devices with mounting centers of 1.76", 1.94" or 2.13" such as HBL7556, HBL4716, etc. when used with a HBL7420 or HBL7425WOA type weatherproof plate.	7452^{**}
Adapter plate for mounting HBL7423WO, HBL7424WO, HBL7425WOA or HBL7420 plates to standard boxes.	HBL7349^{**}

Note: ^{**} Not listed by Underwriter's Laboratories Inc.**Typical Plate, 1-Gang****7452****HBL7349**



Wallplates

Weatherproof Covers for Receptacles and Switches

Vertical, for FS/FD box mounting

IP44
SUITABILITY

For Receptacles with Face Diameters of 1.36–1.39 in. (34.5–35.3)

Description	Catalog Number
Thermoplastic, WET LOCATIONS with cover "open," gray.	HBL7423WO
Thermoplastic, WET LOCATIONS with cover "open," yellow.	HBL74CM23WO
Cast aluminum, WET LOCATIONS with cover "closed."	HBL7420
Cast aluminum, no lift cover, NOT weatherproof.	HBL7320



HBL7423WO

For Switches & Receptacles with Face Diameters of 1.55–1.58 in. (39.4–40.1)

Description	Catalog Number
Thermoplastic, WET LOCATIONS with cover "open," gray.	HBL7425WOA
Thermoplastic, WET LOCATIONS with cover "open," yellow.	HBL74CM25WOA
Thermoplastic, WET LOCATIONS with cover "open," white.	HBL74CM25WOAW
Cast aluminum, WET LOCATIONS with cover "closed."	HBL7420*
Cast aluminum, no lift cover, NOT weatherproof.	HBL7320
Thermoplastic, WET LOCATIONS with cover "open," gray.	HBL7428WOG†
Thermoplastic, WET LOCATIONS with cover "open," yellow.	HBL7428WOY†
Thermoplastic, WET LOCATIONS with cover "open," red.	HBL7428WOR†



HBL7425WOA

For Receptacles with Face Diameters of 1.68–1.72 in. (42.7–43.7)

Description	Catalog Number
Thermoplastic, WET LOCATIONS with cover "open," gray.	HBL7424WO
Thermoplastic, WET LOCATIONS with cover "open," yellow.	HBL74CM24WO
Cast aluminum, WET LOCATIONS with cover "closed."	HBL3393
Cast aluminum, no lift cover, NOT weatherproof.	HBL3394



HBL7424WO

Note: * Cast aluminum lift cover with fibershield for standard toggle and PresSwitch® Switches.

† Features two #6-32 threaded inserts to back mount device to cover.

All weatherproof lift cover plates on this page are listed by Underwriters Laboratories, Inc. as "WDL Closed" for use in wet locations with cover closed and in damp locations.

Weatherproof Covers for Single Receptacles on FS/FD Boxes

Note: All weatherproof plates are UL Listed for WET LOCATIONS WITH COVER CLOSED for intermittent use in wet locations or use in damp locations. Those with suffix "WO" are listed for WET LOCATIONS with cover open in continuous use. All plates are gasketed and self-closing.



HBL7420


2011 National Electrical Code (NEC®)

406.9 Receptacles in Damp or Wet Locations.

(A) Damp Locations. A receptacle installed outdoors in a location protected from the weather or in other damp locations shall have an enclosure for the receptacle that is weatherproof when the receptacle is covered (attachment plug cap not inserted and receptacle covers closed). An installation suitable for wet locations shall also be considered suitable for damp locations. A receptacle shall be considered to be in a location protected from the weather where located under roofed open porches, canopies, marquees, and the like, and will not be subjected to a beating rain or water runoff. All 15- and 20-ampere, 125- and 250-volt nonlocking receptacles shall be listed weather-resistant type.

FPN: The types of receptacles covered by this requirement are identified as 5-15, 5-20, 6-15 and 6-20 in ANSI/NEMA WD 6-2002, National Electrical Manufacturers Association Standard for Dimensions of Attachment Plugs and Receptacles.

(B) Wet Locations. 15- and 20-ampere, 125- and 250-volt receptacles installed in a wet location shall have an enclosure that is weatherproof whether or not the attachment plug cap is inserted. For other one- or two-family dwellings, an outlet box hood installed for this purpose shall be listed, and where installed on an enclosure supported from grade as described in 314.23(B) or as described in 314.23(F) shall be identified as "extra-duty." All 15- and 20-ampere, 125- and 250-volt nonlocking-type receptacles shall be listed weather-resistant type.



Typical Plate, 1-Gang

HBL7320





HBL3393

NEC® is a registered trademark of the The National Electrical Code.



Wallplates

Weatherproof Covers for Flanged Devices*For Flanged Inlets and Flanged Receptacles***IP44**
SUITABILITY**WP1****WP2****WP1****Weatherproof Cover For Flanged Inlets and Flanged Receptacles**

For 15 and 20A, 2-pole 2-wire and 3-wire Insulgrip® flanged inlets and flanged outlets.

Straight Blade, 2-Pole, 3-Wire Flanged Inlets		Flanged Receptacles
	HBL5278C	HBL5279C
	HBL5378C	HBL5379C
	HBL5478C	HBL5479C
	HBL5678C	HBL5679C

Twist-Lock® 2-Pole, 2-Wire and 2-Pole, 3-Wire Flanged Inlets		Flanged Receptacles
	HBL8815C	HBL8809C
	HBL7524C	HBL7526C
	HBL4716C	HBL4715C
	HBL4586C	HBL4585C
	HBL4786C	HBL4785C

WP2**Weatherproof Cover For Flanged Inlets and Flanged Receptacles**

For 20 and 30A, 3-, 4- and 5-wire Insulgrip flanged inlets and flanged outlets.

Twist-Lock 2-pole, 3-wire; 3-pole, 4-wire; 4-pole, 4-wire; 5-wire Flanged Inlets		
	HBL2315	HBL2425
	HBL2325	HBL2435
	HBL2335	HBL2445
	HBL2345	HBL2455
	HBL2615	HBL2465
	HBL2625	HBL2715
	HBL2635	HBL2725
	HBL2645	HBL2735
	HBL2655	HBL2745
	HBL3325C	HBL2755
	HBL2415	HBL2765

Flanged Receptacles		
	HBL2316	HBL2416
	HBL2326	HBL2426
	HBL2336	HBL2436
	HBL2346	HBL2446
	HBL2356	HBL2456
	HBL2616	HBL2466
	HBL2626	HBL2716
	HBL2636	HBL2726
	HBL2646	HBL2736
	HBL2656	HBL2746
	HBL3326C	HBL2756


Wallplates

Weatherproof Switch Plates, Covers and Locking Covers


IP44
 SUITABILITY

Weatherproof Plates


Description	Catalog Number
Clear bubble plate, silicone rubber for use with all general purpose AC toggle and PresSwitch® Switches. Fits both FS/FD and standard boxes.	HBL1795

**HBL1795**

Weatherproof Plates

Description	Catalog Number
Gray neoprene PresSwitch® Plate. Fits FS/FD and standard boxes.	HBL1750*
Same as above except yellow.	HBL17CM50*


Note: * Not listed by Underwriter's Laboratories Inc.

**HBL1750**

Weatherproof Plates

Description	Catalog Number
Gray neoprene PresSwitch® Plate with 125V red pilot light. Fits only FS/FD boxes.	HBL1785*
Same as above except yellow.	HBL17CM85*

Note: * Not listed by Underwriter's Laboratories Inc.

**HBL1785**

Weatherproof Covers

Description	Catalog Number
Cast aluminum lift cover plate with fiber shield. For standard toggle and PresSwitch® Switches. Fits only FS/FD boxes.	HBL7420

**HBL7420**

Brass Locking Covers Attachment for Switches

Description	Catalog Number
Straight keying (all locks alike) appropriate for most applications. Straight cylinder type lock, each HBL96061 ordered operates on the same key—all locks are keyed alike.	HBL96061*
Same as above except in dull chrome finish to match stainless steel plates.	HBL96061DCH*
Straight keying (individual).	HBL96062*
Straight cylinder type lock, each HBL96062 ordered operates on a different key. All locks are keyed differently and individually. This type cannot be master keyed.	

Note: * Not listed by Underwriter's Laboratories Inc.



HBL96061
 shown with wallplate and switch
 (sold separately)



Wallplates

Heavy Duty Weatherproof Covers for Duplex, GFCI, Surge Receptacles and Style Line® Devices

IP44
 SUITABILITY


HBL5221

Duplex Covers For Vertical Mounting

Description	Dimensions		Catalog Number
	Height x Width x Depth		
Thermoplastic, gray, for FS/FD box mounting.	4.56" x 2.89" x 1.08"		HBL5221
Thermoplastic, yellow, for FS/FD box mounting.	4.56" x 2.89" x 1.08"		HBL52CM21
Thermoplastic, gray, for device mounting.	4.56" x 2.89" x 1.08"		HBL5222
Thermoplastic, yellow, for device mounting.	4.56" x 2.89" x 1.08"		HBL52CM22



HBL5206WO

Duplex Covers For Horizontal Mounting

Description	Dimensions		Catalog Number
	Height x Width x Depth		
Cast aluminum, for device mounting.	2.88" x 4.56" x 0.79"		HBL5205WO
Cast aluminum, for FS/FD box mounting.	2.88" x 4.56" x 0.79"		HBL5206WO
Zinc die cast, commercial grade, for device mounting.	2.90" x 4.60" x 0.75"		CWP8H



CWP8H



WPFS26

GFCI, Surge and Style Line Covers

Description	Dimensions		Catalog Number
	Height x Width x Depth		
Die cast aluminum, vertical position, device mount.	4.56" x 2.81" x 0.75"		WP26
Die cast aluminum, vertical position, FS/FD box mount.	4.56" x 2.81" x 0.75"		WPFS26
Zinc die cast, commercial grade, horizontal position, device mount.	2.30" x 4.75" x 0.73"		CWP26H

Note: All weatherproof plates are UL Listed for WET LOCATIONS WITH COVER CLOSED, for intermittent use in wet locations or use in damp locations. Those with Suffix "WO" are listed for WET LOCATIONS with cover open in continuous use. All plates are gasketed and self-closing.



CWP26H



Wallplates

Weatherproof Covers for Duplex, Single, GFCI, Surge Receptacles and Style Line® Devices and Switches

Weatherproof Covers for Vertical Mounting

Description	Dimensions	
	Height x Width x Depth	Catalog Number
Zinc die cast, gray, duplex cover for box mounting.	4.58" x 2.82" x 0.57"	RW51470
Zinc die cast, gray, 1.40 in. (35.6) cover for single receptacle or toggle switch for device mounting.	4.56" x 2.81" x 0.88"	RW51550*
Zinc die cast, gray, GFCI, Surge and Style Line® cover for device mounting.	4.58" x 2.81" x 0.57"	RW51040

**RW51470****RW51550****RW51040**


1-Gang Weatherproof Covers for Horizontal Mounting

Description	Dimensions	
	Height x Width x Depth	Catalog Number
Zinc die cast, gray, duplex cover for device mounting.	2.82" x 4.57" x 0.79"	RW51810
Zinc die cast, gray, 1.40 in. (35.6) cover for single receptacle or toggle switch for device mounting.	2.81" x 4.56" x 0.99"	RW51520*
Zinc die cast, gray, GFCI, Surge and Style Line® cover for device mounting.	2.82" x 4.56" x 0.52"	RW51020

**RW51810****RW51020****RW51520**

2-Gang Weatherproof Covers for Vertical Mounting

Description	Dimensions	
	Height x Width x Depth	Catalog Number
Zinc die cast, gray, duplex cover for device mounting.	4.54" x 4.54" x 0.75"	RW51320
Zinc die cast, gray, one duplex/one GFCI, Surge and Style Line® cover for box mounting.	4.54" x 4.54" x 0.77"	RW51330
Zinc die cast, gray, 1.40 in. (35.6) cover for single receptacle or toggle switch for device mounting.	4.54" x 4.54" x 0.77"	RW51380
Zinc die cast, gray, two GFCI, Surge and Style Line® cover for box mounting.	4.54" x 4.56" x 0.73"	RW51450

**RW51320****RW51330****RW51380****RW51450**

Note: All weatherproof plates are UL Listed for WET LOCATIONS WITH COVER CLOSED, for intermittent use in wet locations or use in damp locations. All plates are gasketed and self-closing.

* C-UL US Listed.



Wallplates

While-In-Use Weatherproof Covers

For Maximum In-Use Protection

**WP826****Cast Aluminum, 1-Gang, Vertical**

Description	Dimensions		Catalog Number
	Height x Width x Depth		
Rectangular, multi-application. Adapter plates included: Duplex, toggle, single receptacle 1.56" dia., and GFCI/Style Line® devices.	6.13" x 3.38" x 3.50"		WP826

**WP826H****Cast Aluminum, 1-Gang, Horizontal**

Description	Dimensions		Catalog Number
	Height x Width x Depth		
Rectangular, multi-application. Adapter plates included: Duplex, toggle, single receptacle 1.56" dia., and GFCI/Style Line® devices.	3.38" x 6.13" x 3.50"		WP826H

**WP700****Cast Aluminum, 1-Gang, Vertical Deep**

Description	Dimensions		Catalog Number
	Height x Width x Depth		
Rectangular, multi-application. Adapter plates included: Duplex, toggle, single receptacle 1.56" dia., and GFCI/Style Line® devices.	6.13" x 3.38" x 5.00"		WP700

**HBLWLC****Specifications****Metallic**

- Die cast Alloy 360 copper-free® aluminum for maximum corrosion resistance and durability. Alloy 360 has less than .004% copper content.
- Finish is baked aluminum lacquer.
- NEMA® 3R rating when used with the appropriate weatherproof outlet box which is intended for outdoor use primarily to provide a degree of protection against rain, sleet, and damage from external ice formation.
- Box or device mount for flexibility of installation.
- Gaskets are closed-cell foam.
- Meets OSHA lockout/tagout requirements.
- Latching covers hold securely.
- Large cord openings.
- Clearly marked UL and CSA logos.
- Covers include gasket and mounting screws. Lids have gasketless design.
- UL Listed/CSA Certified.
- Devices not included.
- Holes for padlocks are ¼ inch (6.4) diameter.
- Drill points in four corners for box mounting.

Locking Device

Description	Catalog Number
Locking device for weatherproof covers.	HBLWLC

NEMA® is a registered trademark of The National Electrical Manufacturers Association.

Wallplates

While-In-Use Weatherproof Covers

For Maximum In-Use Protection

IP66
SUITABILITY

**IMPROVED
DESIGN**

1-Gang Weatherproof Covers for Vertical Mounting

Description	Dimensions Height x Width x Depth	Catalog Number
Thermoplastic, gray, duplex, GFCI, toggle and single receptacles, diameter 1.34", 1.40", 1.60", 1.72", 2.03" and 2.15"	5.91" x 4.32" x 2.84"	RW57300



Thermoplastic, gray, extra deep, duplex, GFCI, toggle and single receptacles, diameter 1.34", 1.40", 1.60", 1.72", 2.03" and 2.15"	5.91" x 4.32" x 4.82"	RW57350
--	-----------------------	----------------



RW57300



RW57350

1-Gang Weatherproof Covers for Horizontal Mounting

Description	Dimensions Height x Width x Depth	Catalog Number
Thermoplastic, gray, duplex, GFCI, toggle and single receptacles, diameter 1.34", 1.40", 1.60", 1.72", 2.03" and 2.15"	5.91" x 4.32" x 2.84"	RW57400



RW57400

2-Gang Weatherproof Covers for Vertical Mounting

Description	Dimensions Height x Width x Depth	Catalog Number
Thermoplastic, gray, duplex, GFCI, toggle and single receptacles, diameter 1.34", 1.40", 1.60", 1.72", 2.03" and 2.15"	5.94" x 5.54" x 2.84"	RW57750



RW57750

Thermoplastic, gray, duplex, GFCI, toggle and single receptacles, diameter 1.34", 1.40", 1.60", 1.72", 2.03" and 2.15"	5.94" x 5.54" x 4.82"	RW57900
--	-----------------------	----------------



RW57900

Thermoplastic, gray, single receptacles, diameter 1.34", 1.40", 1.60", 1.72", 2.03" and 2.15"	5.94" x 5.54" x 4.82"	RW57950
---	-----------------------	----------------



RW57950


Note: Required by the NEC® for while-in-use outdoor power distribution. Thermoplastic covers provide protection for use in wet locations with the cover closed, NEMA® 3R rated. Meets NEC 406.8 – receptacles in damp or wet locations. Holes for padlocks are .40 inch.

NEC® is a registered trademark of the The National Electrical Code.
NEMA® is a registered trademark of The National Electrical Manufacturers Association.



Wallplates

Screws and Accessories



RA12AL



RA756I



RA40



HBL7298



HBL7341



HBL7342RKL



HBL7372RKL

Screws, 6-32 Thread, 100 Count

Description	Color	Catalog Number	Material	Catalog Number
Decorator Wallplate Screws, Oval Head Milled Slot, 3/8 in. Long – 6-32 Thread, 100 per Box (Order 1 to receive a box of 100)	Almond	RA38ALPK100	Brass	RA38BR
	Black	RA38BKPK100	Chrome	RA38CH
	Brown	RA38PK100	Stainless Steel	RA38SS
	Gray	RA38GYPK100		
	Ivory	RA38IPK100		
	Light Almond	RA38LAPK100		
	White	RA38WPK100		
Standard Wallplate Screws, Oval Head Milled Slot, 1/2 in. Long – 6-32 Thread, 100 per Box (Order 1 to receive a box of 100)	Almond	RA12ALPK100	Brass	–
	Black	RA12BKPK100	Chrome	–
	Brown	RA12PK100	Stainless Steel	–
	Gray	RA12GYPK100		
	Ivory	RA12IPK100		
	Light Almond	RA12LAPK100		
	White	RA12WPK100		
Standard Wallplate Screws, Oval Head Milled Slot, 5/8 in. Long – 6-32 Thread, 100 per Box (Order 1 to receive a box of 100)	Almond	–	Brass	RA58BR
	Black	–	Chrome	RA58CH
	Brown	–	Stainless Steel	RA58SS
	Gray	–		
	Ivory	–		
	Light Almond	–		
	White	–		
Standard Wallplate Screws, Oval Head Milled Slot, 1.0 in. Long – 6-32 Thread, 100 per Box (Order 1 to receive a box of 100)	Ivory	RA88IPK100	Stainless Steel	RA88SS
	White	RA88WPK100		

Single Count Screws and Accessories

Description	Color	Catalog Number
Blank toggle adapter, to fill a toggle opening.	Brown	RA756
	Ivory	RA756I
	White	RA756W
Mounting strap, with screws.	Steel	RA40
Red rectangular jewel in metal frame for switch plates.	Red	HBL7298
Brass plated screw, standard slot, .38 in. (9.7) long.		HBL7341
Stainless steel screw, standard slot, .38 in. (9.7) long.		HBL7341SS
Security spanner head screws, 6-32 thread, 100 count.		HBL7342RKL
Screwdriver with spanner head security bit.		HBL7372RKL



Wallplates

Technical Information

Specifications

Listings

Non-Metallic Plates	UL Standard 514D.
Metallic Plates	UL Standard 514D.
Certification	UL Files #E31999, E92074. CSA Standard C22.2 No. 42.1. CSA File 1733174.

Nylon Plate

Thickness	.06 in. (1.5).
Mounting Screw(s)	Steel (painted slotted screw head).
Feature	Captive mounting screw hole.
Operating Temperature	-40°C to 85°C.
Appearance	Smooth.

302/304 Stainless Steel (18% Chromium, 8% Nickel) Plate

Thickness	.035 in. (0.9) nominal.
Mounting Screw(s)	302/304 stainless steel (18% chromium, 8% nickel). Slotted screw head.
Appearance	Horizontal brushed finish.

430 Stainless Steel (17% Chromium, less than 0.5% Nickel) Plate

Thickness	.035 in. (0.9) nominal.
Mounting Screw(s)	302/304 stainless steel (17% chromium, less than 0.5% nickel). Slotted screw head.
Appearance	Horizontal brushed finish.

Brass (70% Copper, 30% Zinc) Plate

Thickness	.04 in. (1.0).
Mounting Screw(s)	Brass (70% Copper, 30% Zinc). Slotted screw head.
Appearance	Horizontal brushed finish.

Aluminum Plate

Thickness	.05 in. (1.3).
Mounting Screw(s)	302/304 stainless steel (17% chromium, less than 0.5% nickel). Slotted screw head.
Appearance	Horizontal brushed finish.

Brass Plated Steel Plate

Thickness	.03 in. (0.8) nominal.
Mounting Screw(s)	Brass slotted head.
Appearance	Polished, coated to inhibit oxidation.

Chrome Plated Steel Plate

Thickness	.03 in. (0.8) nominal.
Mounting Screw(s)	302/304 stainless steel (17% chromium, less than 0.5% nickel). Slotted screw head.
Appearance	Polished, coated to inhibit oxidation.

Steel Painted Plate


Thickness	.03 in. (0.8) nominal.
Mounting Screw(s)	Steel (painted slotted screw head).
Appearance	Powder coat paint.




Wallplates

Wallplate Dimensions


Product Dimensions



Size	Standard Metal		Painted Metal		Size	Jumbo Metal	
	Height	Width	Width			Height	Width
1-Gang	4.50" (114.3)	2.87" (72.9)	2.75" (69.8)		1-Gang	5.25" (133.4)	3.50" (88.9)
2-Gang	4.50" (114.3)	4.60" (116.8)	4.56" (115.8)		2-Gang	5.25" (133.4)	5.31" (134.9)
3-Gang	4.50" (114.3)	6.41" (162.8)	6.38" (162.1)		3-Gang	5.25" (133.4)	7.12" (180.8)
4-Gang	4.50" (114.3)	8.22" (208.8)	8.18" (207.8)				
5-Gang	4.50" (114.3)	10.03" (254.8)	10.00" (254.0)				
6-Gang	4.50" (114.3)	11.81" (300.0)	11.81" (300.0)				
7-Gang	4.50" (114.3)	13.68" (347.5)					
8-Gang	4.50" (114.3)	15.44" (392.1)					




Size	Standard Nylon		Size	Mid-Size Nylon	
	Height	Width		Height	Width
1-Gang	4.63" (117.6)	2.88" (73.2)	1-Gang	4.88" (124.0)	3.13" (79.5)
2-Gang	4.63" (117.6)	4.69" (119.1)	2-Gang	4.88" (124.0)	4.94" (125.4)
3-Gang	4.63" (117.6)	6.50" (165.1)	3-Gang	4.88" (124.0)	6.75" (171.5)
4-Gang	4.63" (117.6)	8.31" (211.1)	4-Gang	4.88" (124.0)	8.56" (217.4)
5-Gang	4.63" (117.6)	10.12" (256.1)			
6-Gang	4.63" (117.6)	11.93" (303.0)			



Size	Snap-On Nylon	
	Height	Width
1-Gang	4.68" (118.9)	2.94" (74.7)
2-Gang	4.68" (118.9)	4.75" (120.7)
3-Gang	4.68" (118.9)	6.56" (166.6)
4-Gang	4.68" (118.9)	8.37" (212.6)
5-Gang	4.68" (118.9)	10.18" (258.6)
6-Gang	4.68" (118.9)	11.99" (304.5)

Wallplate Openings and Mounting Dimensions

#6-32 Oval Head Screws Typical



Note: Specifications are subject to change without notice.



Wallplates

Custom Metal Wallplates

How To Select A Custom Metal Wallplate

Step 1:

Determine wallplate material and enter in box marked "Catalog Number"

Smooth Metal Material	Code
Anodized Aluminum	AL
Brass plated steel	BP
Solid brass	BR
Chrome plated steel	CH
Stainless steel 302/304	SS

Determine number of gangs required and enter in box marked "Catalog Number" next to material.

Number of Gangs	Code
1-gang	1
2-gang	2
3-gang	3
4-gang	4
5-gang	5
6-gang	6
7-gang	7
8-gang	8

Enter Catalog Number

♦ WC* SS 4

Step 2:

Enter quantity.


Step 3: Select the custom metal wallplate configuration.

Refer to the custom wallplate configuration chart to select a configuration for each gang in the wallplate. Each configuration has a specific 3-digit code located in the right hand side of the chart on pages K-34 to K-38. Enter this 3-digit configuration code in the corresponding box on the order form grid to match the position required on the finished custom wallplate.

Item No.	Catalog Number	Quantity	Code	Position 1	Position 2	Position 3	Position 4
1	WCSS4		H*	001	149	008	026
2							

Note: * WC and H are preprinted on the distributor order form.
Number to use for pricing.

The 3-digit numbers listed at the upper right of the Sample Order Form (001, 149, etc.) represent the custom metal wallplate selected on the right. See Configuration Chart and Hubbell Configuration Selector Guide on pages K-34 to K-38 for additional configuration choices.





Wallplates

Custom Metal Wallplates

Configuration Chart

	001 Switch.		079 Barrel Key Switch with hash marks.		456 .375" (9.5) Dia. Round Box Mtd.
	007 Single Receptacle. 1.40" ID (35.6)		080 Barrel Key Switch with On/Off and hash marks.		458 .500" (12.7) Dia. Round Box Mtd.
	008 Duplex Receptacle.		091 Single Receptacle. 1.60" ID (40.5) Hole.		411 .635" (16.1) Dia. Round Box Mtd.
	011 1-gang .635" ID (16.1) Hole Box Mounted with .50" ID (12.7) Nylon Bushing.		098 Single Receptacle. 2.16" ID (54.7) Hole.		435 9-Pin Vertical Box Mtd.
	012 1-gang .635" ID (16.1) Hole Strap Mtd. incl. Strap with .50" ID (12.7) Nylon Bushing.		135 Vertical Mounted Louver.		438 15-Pin Vertical Box Mtd.
	013 Blank Box Mount.		149 Totally Blank (no mounting holes).		295 25-Pin Vertical Box Mtd.
	014 Blank Strap Mtd. incl. Strap.	Coax/Twinax and Modular Jack Openings			314 IBM® Type Opening Box Mounted.
	026 Rectangular Opening.		422 .51" (12.8) Dia. "D" Box Mtd. .44" (11.1) Flat Dia.		415 IBM® Type Opening with One .586" X .762" (14.9 X 19.3).
	055 1-gang .375" ID (9.5) Hole Strap Mtd. incl. Strap.		425 .51" (12.8) Dia. "D" Box Mtd. .47" (12) Flat Dia.	Voice/Data Opening	
	056 1-gang .375" ID (9.5) Hole Box Mounted.		428 .58" (14.7) Dia. "D" Box Mtd. .55" (14) Flat Dia.		470 .542" X .750" Vertical Box Mtd. (13.8 X 19.0).
	057 1-gang .50" ID (12.7) Hole Strap Mtd. incl. Strap.		430 .76" (19.2) Dia. "D" Box Mtd. .73" (18.6) Flat Dia.		473 .586" X .762" Vertical Box Mtd. (14.9 X 19.4).
	058 1-gang .50" ID (12.7) Hole Box Mounted.		423 .51" (12.8) Dia. "D" Box Mtd. .44" (11.1) Flat Dia.		476 .586" X .815" Vertical Box Mtd. (14.9 X 20.7).
	078 Barrel Key Switch.		426 .51" (12.8) Dia. "D" Box Mtd. .47" (12) Flat Dia.		479 .575" X .783" Vertical Box Mtd. (14.6 X 19.9).
			429 .58" (14.7) Dia. "D" Box Mtd. .55" (14) Flat Dia.		471 .542" X .750" Vertical Box Mtd. (13.8 X 19.0).
			431 .76" (19.2) Dia. "D" Box Mtd. .73" (18.6) Flat Dia.		474 .586" X .762" Vertical Box Mtd. (14.9 X 19.4).
					477 .586" X .815" Vertical Box Mtd. (14.9 X 20.7).
					480 .575" X .783" Vertical Box Mtd. (14.6 X 19.9).

Note: For detailed dimensions of the above configurations, see pages K-35 to K-38. Available in smooth metal, standard size only up to and including 8-gang type.


IBM® is a registered trademark of International Business Machines Corporation.



Wallplates


Custom Metal Wallplates

Configuration Selector Guide




Configuration
001

Toggle Switch Plate.




Configuration
014

Blank Plate (Strap Mount).




Configuration
007

Single 15 or 20A Straight
Blade Receptacle.
15A Twist-Lock® Receptacle.




Configuration
026

GFI/Rectangular Opening.




Configuration
008

Duplex Receptacle.




Configuration
055

Single, .375" (9.5)
Telephone (Strap Mount).




Configuration
011

Single, .635" (16.1)
Telephone (Box Mount).




Configuration
056

Single, .375" (9.5)
Telephone (Box Mount).




Configuration
012

Single, .635" (16.1)
Telephone (Strap Mount).




Configuration
057

Single, .50" (12.7)
Telephone (Strap Mount).



Configuration
013

Blank Plate (Box Mount).



Configuration
058

Single, .50" (12.7)
Telephone (Box Mount).


Note: Specifications are subject to change without notice.



Wallplates


Custom Metal Wallplates

Configuration Selector Guide




Configuration
078

Barrel Key Switch.




Configuration
079

Barrel Key Switch
with hash marks.




Configuration
080

Barrel Key Switch
with On/Off and
hash marks.




Configuration
091

Single 20 or 30A Twist-Lock®
Receptacle.




Configuration
098

Single Receptacle,
30 or 50A Straight Blade,
3 Wire Power Outlet.




Configuration
135

Louvered Plate, Strap Mount.




Configuration
149

Totally Blank Plate.




Configuration
295

RS232 Port Single 25-Pin
(Box Mount).




Configuration
314

IBM® Type (Box Mount).




Configuration
411

Dual .635" (16.1) Holes
(Box Mount).



Configuration
415

IBM® Type and Modular Jack
(Box Mount).



Configuration
422

Single .505" (12.8) D-Hole
(Box Mount).


Note: Specifications are subject to change without notice.

IBM® is a registered trademark of International Business Machines Corporation.

Wallplates


Custom Metal Wallplates

Configuration Selector Guide




Configuration
423

Dual .505" (12.8) D-Holes
(Box Mount).




Configuration
431

Dual .755" (19.2) D-Holes
(Box Mount).




Configuration
425

Single .505" (12.8) D-Hole
(Box Mount).




Configuration
435

Single 9-Pin RS232
(Box Mount).




Configuration
426

Dual .505" (12.8) D-Holes
(Box Mount).




Configuration
438

Single 15-Pin RS232
(Box Mount).




Configuration
428

Single .580" (14.7) D-Hole
(Box Mount).




Configuration
456

Dual .375" (9.5) Round
(Box Mount).




Configuration
429

Dual .580" (14.7) D-Holes
(Box Mount).




Configuration
458

Dual .50" (12.7) Round
(Box Mount).



Configuration
430

Single .755" (19.2) D-Hole
(Box Mount).



Configuration
470

Single Modular Jack
(Box Mount).








Note: Specifications are subject to change without notice.



Wallplates

Custom Metal Wallplates

Configuration Selector Guide

**Configuration 471**Dual Modular Jack
(Box Mount).**Configuration 473**Single Modular Jack
(Box Mount).**Configuration 474**Dual Modular Jack
(Box Mount).**Configuration 476**Dual Modular Jack
(Box Mount).**Configuration 477**Dual Modular Jack
(Box Mount).**Configuration 479**Single Modular Jack
(Box Mount).**Configuration 480**Dual Modular Jack
(Box Mount).

Note: Specifications are subject to change without notice.