



Aluminum Foil Tape

431 • 439L (Linered)

Technical Data

May, 2017

Product Description	3M™ Aluminum Foil Tape 431 and 439L is a 2-mil nominal dead soft aluminum foil with transparent acrylic adhesive for many permanent sealing, holding, splicing or masking applications requiring the protection offered by a foil backing.			
IMPORTANT: 3M™ Aluminum Foil Tape 431 and 439L are not intended for medical usage. Neither 3M nor the Food and Drug Administration have evaluated or reviewed this tape for medical application. User assumes all risk and liability whatsoever in connection with usage of product in a medical application.				

Product Construction	Backing	Adhesive	Color	Liner (3M tape 439L)	Standard Roll Length
	Aluminum foil	Acrylic	Shiny silver	Tan Kraft paper with silicone	60 yds. (55 m)

Typical Physical Properties	Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.	ASTM Test Method
Adhesion to Steel:	41 oz./in. width (45 N/100 mm)	D-3330
Tensile Strength at Break: 3M tape 431	19 lbs./in. width (338 N/100 mm)	D-3759
3M tape 439L	18 lbs./in. width (315 N/100 mm)	D-3759
Elongation at Break:	3M tape 431 5% 3M tape 439L 3%	D-3759
Backing Thickness:	1.9 mils (0.05 mm)	D-3652
Total Tape Thickness:	3.1 mils (0.08 mm)	D-3652
Liner Thickness:	3M tape 439L 5.6 mils (0.14 mm)	D-3652
Water Vapor Transmission Rate:	0.05 gms H ₂ O/100 sq. in./24 hrs. (0.77 g/m ² /24 hrs.)	D-3833
Temperature Use Range:	-65° to 300°F (-54° to 149°C)	
Weight:	0.0096 lbs./yd./in. width (.0049 kg/m/24 mm)	

Features	<ul style="list-style-type: none">Flame resistant. Meets U.L. 723, Class "L" low flammability rating (File R 7311).Meets requirements of F.A.R. 25.853(a).Foil backing provides an excellent reflective surface for both heat and light.Good aging performance both indoors and outdoors.Low moisture vapor transmission rate offers excellent sealing and patching performance.Best results attained when applied to clean dry surface above 32°F (0°C).
----------	--

3M™ Aluminum Foil Tape

431 • 439L (Lined)

Application Ideas

- Seal and patch tears in truck trailers, as well as other outdoor equipment.
- Reflect heat away from sensitive areas.
- Thermal heat conduction.
- General purpose holding, patching, sealing applications – indoors or out.
- Splicing of thin gauge foils.
- Good maskant in electroplating of aluminum because it will not contaminate the bath.
- Decorative.

Storage

Store under normal conditions of 60° to 80°F (16° to 27°C) and 40 to 60% R.H. in the original carton.

Shelf Life

To obtain best performance, use this product within 24 months from date of manufacture.

Product Selection and Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy and Disclaimer

Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. **3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE.** If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability

Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

ISO 9001

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standard.

3M

Industrial Adhesives and Tapes Division

3M Center, Building 225-3S-06

St. Paul, MN 55144-1000

800-362-3550 • 877-369-2923 (fax)

www.3M.com/industrial

Printed in U.S.A.

©3M E 70-0709-5013-7 (5/17)