




UNIT:mm


10000±100mm



HDMI 19P/M MOLDING TYPE
INNER MOLD NO.:HJ-CT-091
OUTER MOLD NO.:HJ-CT-092/093
(MOULD NO.)

HDMI 19P/M MOLDING TYPE
INNER MOLD NO.:HJ-CT-091
OUTER MOLD NO.:HJ-CT-092/093
(MOULD NO.)

PIN ASSIGNMENT



- 1.ELECTRICAL TEST
- (1).100% open short & miss wire test
- (2).Insulation resistance:DC/300V 5Mohm(Min)
- (3).Contactor resistance:≤3ohm Max
- 2.HDTV-DVD TEST:1080P (高清电视测试 : 1080P)
- 3.RoHS compliant

⑦	OUT JACKET	16g	OUTER MOLD:45P PVC COLOR:BLACK
⑥	IN JACKET	8g	INNER MOLD:CLEAR LDPE
⑤	CONN	2	HDMI 19P/M SOLDER STYLE SHORT BODY PIN 3U" SHELL-PLATED GOLD INSULATION BLACK
④	TUBE	2	HEAT SHRINK TUBE CLEAR ODO.8*L=20mm.
③	TUBE	10	HEAT SHRINK TUBE CLEAR ODO.0*L=6mm .
②	TUBE	10	HEAT SHRINK TUBE BLACK ODO.8*L=9mm.
①	CABLE	1	28#1/0.32BC+FPPE ID0.95*1P+D 1/0.32BC+HDPE ID0.6+AL]*4P+(1/0.32BC+HDPE ID0.70)*1P+(1/0.32BC+HDPE ID0.70)*5C+AL+D 1/0.32BC+B 28#/0.12ALMG+PVC BLACK ODO7.3MM

Cnc Tech, LLC				
Industrial Cable and Connector Technology				
DRAWN BY	zhonghs	DRAWING NO.	VG/LJQ-094-001	
CHECKED BY		CUSTOMER	CNC	
APPROVAL BY		ITEM NO.	740-10010-01000	
DECIDE BY		DATE	2012-02-14	
VERSIONS/EDITEDN	A/0	PROJECTION		

