


WILL ACCEPT 26-20 AWG WIRE

- BACKSHELL KIT INCLUDES:
- (1) SOLDER CUP CONNECTOR
 - (1) BACKSHELL WITH STRAIN RELIEF, (2) SCREWS
 - (2) ASSEMBLY SCREWS
 - (2) SPRING LATCHES
 - (1) RUBBER GROMMET



SERIES 110-YYY-203L001
POSITIONS 014
024 - NOT AVAILABLE
036
050
GENDER 1 = MALE
2 = FEMALE
TERMINATION: 0 = SOLDER CUP
SHELL PLATING 3 = NICKEL
HARDWARE OPTIONS:
00 = NOT AVAILABLE
PLATING OPTIONS 1 = GOLD FLASH

MATERIALS:

INSULATOR: GLASS-FILLED THERMOPLASTIC
UL RATED 94V-0 - 230°C PROCESS TEMP.
CONTACTS: COPPER ALLOY
SHELL: STEEL, NICKEL PLATED

RoHS COMPLIANT

ELECTRICALS:
CONTACT CURRENT RATING: 5 AMPS
DIELECTRIC WITHSTANDING VOLTAGE: AC 1200 R.M.S.
INSULATION RESISTANCE: 1000 mohms MINIMUM AT 500V DC
CONTACT RESISTANCE: 30 mOHMS MAXIMUM
OPERATING TEMPERATURE: -55°C TO +125°C

	A	B	C	D
14	1.729	.992	1.252	.622
	43.92	25.20	31.79	15.80
24	2.167	1.417	1.225	.622
	55.05	36.00	31.11	15.80
36	2.669	1.925	1.295	.622
	67.80	48.90	32.90	15.80
50	3.260	2.519	1.407	.622
	82.80	64.00	35.75	15.80



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:WAYNE ROBBINS

CHECKED:

SCALE:1:1

DWG NO.

DATE:7-15-05

DATE:

SHEET1 OF1

REV3

110-YYY-203L001

NorComp