



PANDUIT PART NO.	PACKAGE QTY.	MAX BUNDLE DIA	LENGTH L ±.2 [5]
MLT2DH-L	50	2"[50]	18.5"[470]
MLT4DH-L	50	4"[101]	28.0"[711]
MLT5DH-L	50	5"[127]	34.0"[863]
MLT6DH-Q	25	6"[152]	40.0"[1016]



BODY WRAPS AROUND TWO TIMES
ENTERING HEAD TWICE
(NOT TO SCALE)


NOTES:

1. APPLICATION TOOLS - GS4MT, PPTMT, ST2MT, ST3MT, AND HTMT
2. MINIMUM LOOP TENSILE STRENGTH - 600 LBS. (2669 NEWTONS)
WHEN TESTED ON A 1.5" MANDREL.
3. BRACKETS [] DENOTE DIMENSIONS IN MILLIMETERS, AND ARE
SHOWN FOR REFERENCE ONLY
4. TOLERANCES:
.XXX = ±.010 [.25] .XX = ±.02 [.5]
.X = ±.03 [.8] ANGLES = ±2°
5. MATERIAL: 304 STAINLESS STEEL

FULLY ROUNDED
EDGES ALONG
STRAP BODY

SECTION A - A

SCALE: 6x



					PANDUIT CORP. TINLEY PARK, ILLINOIS DOUBLE WRAPPED METAL LOCKING TIE HEAVY SERIES -304 STAINLESS STEEL
04A	2/12	MIM	RGRO	NOTE #3 METRIC DIMENSIONS NOTED AS BEING SHOWN FOR REFERENCE ONLY	
REV	DATE	BY	CHK	DESCRIPTION	DRAWN BY JAMB
					CHK'D DPN
					SCALE 2x
					DRAWING NO. N41142BS_DC