


REV.	DATE	DESCRIPTION
NC	01/29/03	INITIAL RELEASE



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex						
7						DRAWN	G.R.S.	01/29/03								
6						CHECKED										
5						ISSUED				PART DESCRIPTION SMA FOUR (4) HOLE PANEL RECEPTACLE PLUG						
4	GASKET	SILICONE	RED	1												
3	INSULATOR	TEFLON	NATURAL	1					PART NO. 132144							
2	CONTACT PIN	BER. COPPER	GOLD	1												
1	HOUSING/BODY	BRASS	GOLD	1			SHEET 1 OF 1									
	DESCRIPTION	MATERIAL	FINISH	QTY		CAD FILE C:/132/132144.DWG			DWG. NO.	132144.dwg	REV.	NC	SIZE	A	SCALE	NA