

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200670192

Status:

Active

Overview:

Brad Micro-Change (M12) Connectors

Description:

Micro-Change (M12) Single-Ended Cordset, 3 Poles, Female (Straight) to Pigtail with PNP LED Sensors, 22 AWG, PUR Cable, 2.0m (6.56') Length



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR6837

General

Product Family

Industrial Cordsets

Series

120067

Connector End A

Micro-Change (M12)

Connector End B

Pigtail

IP Rating

IP67

Material - Contact

Copper Alloy

Overview

Brad Micro-Change (M12) Connectors

Product Name

Micro-Change (M12)

Protocol

N/A

Region

Europe

Type

Single Ended

UPC

78678885471

Physical

Cable Diameter

4.32mm (.170")

Cable Length

2.0m (6.56')

Color - Cable Jacket

Black

Coupling Style

Threaded

Gender

Female-Pigtail

Keyway

Single

LED Indicator

PNP Sensors

Material - Cable Jacket

PUR

Material - Connector Body

PUR

Material - Coupling Nut

Nickel-plated Brass

Material - O-Ring

Fluoro-elastomer

Material - Plating Mating

Gold

Orientation

Straight to Pigtail

Poles

3

Temperature Range - Operating

-30°C TO +80°C

Wire Size AWG

22

Wire/Cable Type

UL 21198

Electrical

Current - Maximum per Contact

4.0A

Voltage - Maximum

30V AC/DC

Material Info

Engineering Number

8030P0B03M020

Reference - Drawing Numbers

Sales Drawing

SD-120067-011

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

120067 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION