




.050" [1.27 mm] Contact Centers, Female Header, SMT with Posts- SFH Series Mates with SBH31 series (See opposite page)

SPECIFICATIONS

- Operating Temperature: -40°C to +105°C
- Processing Temperature: 230°C Max. for 60 seconds,
(260°C Max. for 10 seconds)
- UL Flammability Rating: 94V-0
- Contact Resistance: 20 milli Ohms Max.
- Current Rating: 1 Amp
- Dielectric Withstanding: 500 VAC
- Insulation Resistance: 5000 Megohms



PART NUMBER OPTIONS

SFH31 - N P P B - D 10 - SP - BK	
SERIES	COLOR
SFH31 = Female Header, .050" [1.27 mm] Contact Centers by .050" [1.27 mm] Row Spacing	BK = Black
INSULATOR MATERIAL	TERMINATION TYPE
N = Nylon	SP = Surface Mount with Guide Posts
CONTACT MATERIAL	NUMBER OF CONTACT POSITIONS
P = Phosphor Bronze	03 thru 50
CONTACT FINISH - RoHS Compliant	NUMBER OF ROWS
P = Gold Flash Overall	D = Dual Row
E = .000100" Pure Tin, Matte, Overall	CONTACT CENTERS
	B = .050" [1.27 mm]

DIMENSIONS For complete drawings, go to www.sullinscorp.com or e-mail techsupport@sullinscorp.com

Dimensions in [] are in millimeters, all others are in inches.

