



FEATURES:

- ✓ Ideal for making a temporary connection between electrical circuits
- ✓ Multiple wire lengths
- ✓ Alligator clips will attach to objects up to .300" (7.62mm) outside diameter
- ✓ Made with heat resistant Santoprene Rubber and Silicone

MATERIALS:

Alligator Clip:

Body: Nickel Plated Steel

Boot: Santoprene rubber

Wire: Silicone Insulated, 18 AWG

RATINGS:

Operating Voltage: 1,000V

Current: 10 Amperes

Temperature: -13° to 176 F (-25 to 80° C)

ORDERING INFORMATION: Model 6576-Length in inches –Color

*Standard wire length: 24" (61 cm), 36" (91 cm)

Additional lengths can be quoted upon request.

Color Code: 0 = Black, 2 = Red

Ordering example: 6576-48-2, length is 48", color is in red.

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Sales: 800-490-2361 Fax: 425-446-5844 Technical Support: technicalsupport@pomonatest.com
For "Where to Buy" information, visit the Pomona web site at www.pomonaelectronics.com