




Dimensions (In.)

Specifications:

- Type: 1/4" round single turn cermet trimmer
- STD resistance tolerance: $\pm 20\%$
- End resistance: 1% nom.
- Slider current: 50mA
- Power rating: .3W @ 70°C derating to 0 @ 100°C
- Limiting element voltage: 100VDC or AC RMS max.
- Temperature coefficient: $\pm 200\text{ppm}/^\circ\text{C}$
- End stop: 30mNm min.
- Temperature range: -25°~+100°C
- Rotational life: 200 cycles
- Values(Ω): 500, 1K, 2K, 5K, 10K, 22K, 50K, 100K, 220K, 500K, 1M

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[406PA102M](#) [406PA103M](#) [406PA502M](#) [406PA202M](#) [406PA504M](#) [406PA104M](#) [406PA105M](#) [406PA223M](#)
[406PA503M](#)