





Dimensions: mm (in.)



P.C. Mounting

POS.1	POS.2
ON	(ON)
2-3, 5-6	2-1, 5-4

Switch Function

Electrical Specifications:

- Contact rating: 0.4 VA max. / 20 V AC or DC max.
- Contact resistance: Below 100 mΩ typ. initial @ 2-4 V DC, 100 mA
- Insulation resistance: 1,000 MΩ min.
- Dielectric strength: 500 Vrms min. @ sea level

Mechanical Specifications:

- Mechanical life: 40,000 make-and-break cycles
- Operating temperature: -30°C ± 85°C

Note:

- RoHS Compliant

Soldering Process:

- Wave soldering: Recommended soldering temperature: 260±5°C
Duration of solder immersion: 5±1 seconds (PCB is 1.6mm in thickness)

Sealed Ultra-Miniature Toggle Switch
108-2UD2T1663-EV

Mountain
Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[108-2UD2T1663-EV](#)