

HUBER+SUHNER® DATA SHEET

Coaxial PCB Connector: 90_MMCX-S50-0-55/119_O

Rev.: E



Description

Straight PCB jack

Interface Standards
SUHNER-MMCX



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 6 GHz

Mechanical Data

Board mounting type surface mount
Weight 0.0002 kg

Environmental Data

Operating Temperature -40 °C to 90 °C
2002/95/EC (RoHS) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze	Gold Plating
Outer contact	Brass	Gold Plating
Body	LCP	
Insulator		

Related Documents

Outline drawing DOU-00080379
Mounting hole DOU-00012840

Ordering Information

Single package 90_MMCX-S50-0-55/119_OE
Bulk 100 pcs package 90_MMCX-S50-0-55/119_OH

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG

RF Technology

9100 Herisau, Switzerland

Phone +41 (0)71 353 41 11

Fax +41 (0)71 353 45 90

www.hubersuhner.com

HUBER+SUHNER – Excellence in Connectivity Solutions