

Spiralschläuche SBPE, SBPEFR, SBPA, SBPAV0 und SBPTFE

Technische Daten

Art.-Nr.	Lokaler Typ	Typ	Ø D	Wanddicke (WT)	Wendelbreite (P)	Bündel Ø min.	Bündel Ø max.	Material	Farbe	Rollenlänge
SBPE										
161-41000	–	SBPE1.5	1,5	0,8	6,0	1,6	8,0	PE	Natur (NA)	30 m
161-41001	–	SBPE1.5	1,5	0,8	6,0	1,6	8,0	PE	Schwarz (BK)	30 m
161-41002	–	SBPE1.5	1,5	0,8	6,0	1,6	8,0	PE	Grau (GY)	30 m
161-41100	–	SBPE4	4,0	1,0	7,8	5,0	20,0	PE	Natur (NA)	30 m
161-41101	–	SBPE4	4,0	1,0	7,8	5,0	20,0	PE	Schwarz (BK)	30 m
161-41102	–	SBPE4	4,0	1,0	7,8	5,0	20,0	PE	Grau (GY)	30 m
161-41200	–	SBPE9	9,0	1,4	12,5	10,0	100,0	PE	Natur (NA)	30 m
161-41201	–	SBPE9	9,0	1,4	12,5	10,0	100,0	PE	Schwarz (BK)	30 m
161-41202	–	SBPE9	9,0	1,4	12,5	10,0	100,0	PE	Grau (GY)	30 m
161-41300	–	SBPE16	16,0	1,6	16,0	20,0	150,0	PE	Natur (NA)	30 m
161-41301	–	SBPE16	16,0	1,6	16,0	20,0	150,0	PE	Schwarz (BK)	30 m
161-41302	–	SBPE16	16,0	1,6	16,0	20,0	150,0	PE	Grau (GY)	30 m
SBPEFR										
161-43000	–	SBPEFR1.5	1,5	0,8	6,0	1,6	8,0	PEFR	Weiß (WH)	30 m
161-43001	–	SBPEFR1.5	1,5	0,8	6,0	1,6	8,0	PEFR	Schwarz (BK)	30 m
161-43100	–	SBPEFR4	4,0	1,0	7,8	5,0	20,0	PEFR	Weiß (WH)	30 m
161-43101	–	SBPEFR4	4,0	1,0	7,8	5,0	20,0	PEFR	Schwarz (BK)	30 m
161-43200	–	SBPEFR9	9,0	1,4	12,5	10,0	100,0	PEFR	Weiß (WH)	30 m
161-43201	–	SBPEFR9	9,0	1,4	12,5	10,0	100,0	PEFR	Schwarz (BK)	30 m
161-43300	–	SBPEFR16	16,0	1,6	16,0	20,0	150,0	PEFR	Weiß (WH)	30 m
161-43301	–	SBPEFR16	16,0	1,6	16,0	20,0	150,0	PEFR	Schwarz (BK)	30 m
SBPA										
161-42000	–	SBPA1.5	1,5	0,4	6,0	1,6	8,0	PA6	Natur (NA)	30 m
161-42100	–	SBPA4	4,0	0,6	7,8	5,0	20,0	PA6	Natur (NA)	30 m
161-42200	–	SBPA9	9,0	1,0	12,5	10,0	100,0	PA6	Natur (NA)	30 m
161-42300	–	SBPA16	16,0	1,2	16,0	20,0	150,0	PA6	Natur (NA)	30 m
SBPAV0										
161-44000	–	SBPAV01.5	1,5	0,4	6,0	1,6	8,0	PA6V0	Schwarz (BK)	30 m
161-44100	–	SBPAV04	4,0	0,6	7,8	5,0	20,0	PA6V0	Schwarz (BK)	30 m
161-44200	–	SBPAV09	9,0	1,0	12,5	10,0	100,0	PA6V0	Schwarz (BK)	30 m
161-44300	–	SBPAV016	16,0	1,2	16,0	20,0	150,0	PA6V0	Schwarz (BK)	30 m
SBPTFE										
161-45000	–	SBPTFE1.5	1,5	0,5	6,0	1,6	8,0	PTFE	Natur (NA)	5 m
161-45100	–	SBPTFE4	4,0	0,7	7,8	5,0	20,0	PTFE	Natur (NA)	5 m
161-45200	–	SBPTFE9	9,0	1,0	12,5	10,0	100,0	PTFE	Natur (NA)	5 m

Alle Maße in mm. Technische Änderungen vorbehalten.