

Low Noise, High Temperature Standard Connectors





GST/HGST
\$9
Basic Pair





See Section I
for analab
Services

- ✓ Connector Ground Protects Against Electrical Noise Errors
- ✓ Write-On Window for Easy Identification
- ✓ Superior Mechanical Connection Prevents Signal Loss Due to Vibration or Wire Movement
- ✓ Rugged Glass-Filled Nylon Shell Rated from -29 to 220°C (-20 to 425°F)
- ✓ Liquid Crystal Polymer Shell Rated to -29 to 260°C (-20 to 500°F)
- ✓ Accepts Solid or Stranded Wire Up to Size 14 AWG
- ✓ High Purity Thermocouple Alloy Pins and Sockets
- ✓ Color-Coded


The GST and HGST low noise connectors are designed to provide easy connection of ground wires to probes and extension wires. The drain wire of a 20 AWG twisted shield cable or the shield of the overbraided wire is crimped and held in place by their internal hardware. They have excellent thermal and electrical characteristics to assure high accuracy. Each connector includes a write-on window, and external ground strap to provide additional mechanical rigidity and strengthen the mechanical bond between the connectors. Ground straps also maintain the electrical contact through the connector, protecting against electrical noise errors.





Accessories

Model No.	Price	Description
HCP-L	\$0.25/pkg of 5	Write-on window for HGST connector face
WCP-L	\$0.25/pkg of 5	Write-on window for GST connector face
HCP-HGST	\$1.00/pkg of 5	Write-on window for HGST connector side
WCP-GST	\$1.00/pkg of 5	Write-on window for GST connector side
GS-GST-10	\$2.75/pkg of 10	Ground straps



MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

Alloy Code [†]	Type of Thermocouple Used With Connector	Compensating Alloy Used in Connector		Shell Color	Model Number	Price		
		+	-			Pair (MF)	Female (F)	Male (M)
K	CHROMEGA®-ALOMEGA®	CHROMEGA®	ALOMEGA®	Yellow	GST-K-(*)	\$9.00	\$5.50	\$3.50
T	Copper-Constantan	Copper	Constantan	Blue	GST-T-(*)	9.00	5.50	3.50
J	Iron-Constantan	Iron	Constantan	Black	GST-J-(*)	9.00	5.50	3.50
E	CHROMEGA®-Constantan	CHROMEGA®	Constantan	Purple	GST-E-(*)	9.00	5.50	3.50
R/S	Pt/13%Rh-Pt	Copper	RNX/SNX	Green	GST-R/S-(*)	9.00	5.50	3.50
U	Uncompensated	Copper	Copper	White	GST-U-(*)	9.00	5.50	3.50
N	OMEGALLOY®	OMEGA-P®	OMEGA-N®	Orange	GST-N-(*)	13.50	8.25	5.25
K	CHROMEGA®-ALOMEGA®	CHROMEGA®	ALOMEGA®	Yellow	HGST-K-(*)	9.40	5.70	3.70
T	Copper-Constantan	Copper	Constantan	Blue	HGST-T-(*)	9.40	5.70	3.70
J	Iron-Constantan	Iron	Constantan	Black	HGST-J-(*)	9.40	5.70	3.70
E	CHROMEGA®-Constantan	CHROMEGA®	Constantan	Purple	HGST-E-(*)	9.40	5.70	3.70
R/S	Pt/13%Rh-Pt	Copper	RNX/SNX	Green	HGST-R/S-(*)	9.40	5.70	3.70
U	Uncompensated	Copper	Copper	White	HGST-U-(*)	9.40	5.70	3.70
N	OMEGALLOY®	OMEGA-P®	OMEGA-N®	Orange	HGST-N-(*)	13.90	8.45	5.45

Each connector comes complete with write-on window for connector face and sides. The ground strap replaces the side windows and maintains the electrical connection through the connector pair.

* To order, specify "MF" for connector pair, "M" for male connector only, or "F" for female connector only

† J, K, T, S and R are ANSI designations. OMEGALLOY® is generically known as Nicrosil-Nisil

Type U (uncompensated) connectors are used with type B thermocouples (Pt/6%Rh-Pt/30%Rh)

Ordering Examples: GST-K-MF, type K connector pair, \$9.00.

HGST-K-MF, Type K connector pair, \$9.40. HGST-K-F, Type K female connector, \$5.70.

HGST-J-MF, Type J connector pair, \$9.40, with GS-GST-10 replacement ground straps, \$2.75, \$9.40 + 2.75 = \$12.15.

Discount Schedule	
1-10	Net
11-49	5%
50-99	10%
100-999	15%
1000-4999	20%
5000 and over	25%