

Customer Information Sheet

DRAWING No.: M80-868XXXX

SHEET 2 OF 2

IF IN DOUBT - ASK

(C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm

SPECIFICATIONS:**MATERIAL:**MOULDING = GLASS FILLED PBT,
UL94V-0, BLACK

CONTACTS = PHOSPHOR BRONZE

FINISH:**CONTACTS:**22 = 0.75µ GOLD ON CONTACT AREA,
3.0µ 90/10 TIN/LEAD ON TAILS

05 = 0.75µ GOLD

ELECTRICAL:

CURRENT RATING (25°C) = 3.0A MAX.

CURRENT RATING (85°C) = 2.2A MAX.

WORKING VOLTAGE = 120V AC/DC

VOLTAGE PROOF = 360V AC/DC

CONTACT RESISTANCE (INITIAL) = 20 mΩ MAX.

CONTACT RESISTANCE (AFTER CONDITIONING) = 25 mΩ MAX.

INSULATION RESISTANCE (INITIAL) = 1000 MΩ MIN.

INSULATION RESISTANCE (AFTER CONDITIONING) = 100 MΩ MIN.

MECHANICAL:


DURABILITY = 500 OPERATIONS

ENVIRONMENTAL:

TEMPERATURE RANGE = -55°C TO +125°C


PACKING:

TUBE

FOR COMPLETE SPECIFICATION, SEE COMPONENT
SPECIFICATION C005XX (LATEST ISSUE)2.00 x No. OF WAYS
PER ROW + 3.55 MAX

(3.0)

2.00

2.00 x No.
OF PITCHES
PER ROW

2.00 TYP

Ø0.50 TYP

BRITISH STANDARD ORDER CODE:

B5743-2XX-M-L-X

TOTAL No. OF WAYS

04, 06, 08, 10, 12, 14, 16,
18, 20, 26, 34, 44


FINISH:

0 = SELECTIVE GOLD

2 = GOLD

NOTES:

- 2-OFF STRAIN RELIEF STRAPS M80-0030006
ARE INCLUDED WITH EACH CONNECTOR
- FOR RoHS COMPLIANT EQUIVALENT PRODUCT
USE M80-841XXXX



SECTION A-A

2.25 TYP 2.00 x No. OF PITCHES
PER ROW

Ø0.80 MAX TYP

4 x Ø0.90 MIN TYP
STRAIN RELIEF
STRAP HOLES2.00 0.50 2.00 TYP 4.75
RECOMMENDED
PCB LAYOUT

ORDER CODE:

M80-868XXXX

TOTAL No. OF WAYS

04, 06, 08, 10, 12, 14, 16,
18, 20, 26, 34, 44

FINISH:

05 = GOLD

22 = SELECTIVE GOLD

CP	14	01.10.09	10303
NAME	ISS.	DATE	C/NOTE
APPROVED: C.PENROSE			
CHECKED: R.ADDE			
DRAWN: W. J. BOURNE			
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

HARWIN USA TEL: 603 893 5376 FAX: 603 893 5396 mis@harwin.com	HARWIN Europe (UK) TEL: 023 9231 4545 FAX: 023 9231 4590 mis@harwin.co.uk	HARWIN Asia TEL: +65 6 779 4909 FAX: +65 6 779 3868 mis@harwin.com.sg
--	--	--

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCESX. = ±1mm
X.X = ±0.25mm
X.XX = ±0.10mm
X.XXX = ±0.01mm

ANGLES = ±5°

UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH: SEE ABOVE

S/AREA: mm²**TITLE:**DATAMATE DIL
HORIZONTAL MALE PC TAIL
ASSEMBLY - UNLATCHED

DRAWING NUMBER:

M80-868XXXXSHT
2
OF
2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Harwin:

[M80-8680822](#) [M80-8680422](#) [M80-7820306](#) [M80-8681622](#) [M80-8681205](#) [M80-8681822](#) [M80-8681422](#) [M80-8681222](#) [M80-8681022](#) [M80-8680622](#) [M80-8682022](#) [B5743-218-M-L-0](#) [B5743-208-M-L-0](#) [B5743-212-M-L-0](#) [B5743-216-M-L-0](#) [B5743-214-M-L-0](#) [B5743-210-M-L-0](#) [B5743-234-M-L-0](#) [B5743-204-M-L-0](#) [B5743-206-M-L-0](#) [B5743-226-M-L-0](#) [B5743-220-M-L-0](#) [M80-8681805](#) [M80-8680605](#) [M80-8683422](#) [M80-8682622](#) [M80-8684422](#) [M80-8681405](#) [M80-8531445](#)