


Dimensions: mm (In.)

**Electrical Specifications:**

- Rating: 12mA/ 24VDC
- Test Voltage Cont.-Cont.: 150V
- Continuous Current Rating: 120mA
- Power Rating: 240mW
- Insulation Resistance: 100MΩ min.
- Contact Resistance: 50m Ω max.
- Capacitance Cont.-Cont.: 0.5pF max

Mechanical Specifications:

- Contact Bounce: 5m sec max.
- Operating Force: 200gf max.
- Operating Travel: 2.5±0.2mm
- Operating Life: 500,000 cycles
- Function: Momentary

Soldering Process:

- Temperature: 265°C for 5 sec

Materials:

- Housing: nylon
- Cap: ABS
- Fixed Contact: Gold plated copper alloy
- Moving Contact: Gold plated copper alloy

Mouser Stock No.	Cap Color	LED Color	Type
107-DPS-11-1-1	Black	Red	SPDT
107-DPS-11-1-2	Black	Green	SPDT
107-DPS-11-2-1	Gray	Red	SPDT
107-DPS-11-2-2	Gray	Green	SPDT
107-DPS-11-5-1	Red	Red	SPDT
107-DPS-11-5-2	Red	Green	SPDT
107-DPS-11-8-1	White	Red	SPDT
107-DPS-11-8-2	White	Green	SPDT

Illuminated (LED) Pushbutton Switches

107-DPS-11-1-1, 107-DPS-11-1-2,
107-DPS-11-2-1, 107-DPS-11-2-2, 107-DPS-11-5-1,
107-DPS-11-5-2, 107-DPS-11-8-1, 107-DPS-11-8-2

**Mountain
Switch**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mountain Switch:

[107-DPS-11-2-1](#) [107-DPS-11-2-2](#) [107-DPS-11-8-2](#) [107-DPS-11-8-1](#) [107-DPS-11-1-1](#) [107-DPS-11-1-2](#) [107-DPS-11-5-2](#) [107-DPS-11-5-1](#)