



WCY60

WEJTAP CONN YEL

ACTIVE



Electrical division

☒ [Email Datasheet](#) [Print Datasheet](#)

FCI Brings You More

- ☒ [Contact our sales/technical support](#)
- ☒ [Sample request](#)
- ☒ [Price request](#)

Download document

Literature

- [> Wejtap Material Safety Data Sheet - Power Cell](#)
- [> Wejtap Material Safety Data Sheet - Black Powder Solvent](#)
- [> Wejtap Product Focus](#)
- [> Wejtap Brochures](#)
- [> Connector Theory and Application Brochure](#)

Application Tooling

- [> Electrical Tooling](#)

Specifications

Dimensional	Physical	Approvals / Certifications	Other Features
Dimensional			
Conductor Size (Run - Diameter)	0.722 to 0.95		
Conductor size (Run - Max)	556.5-18/1		
Conductor size (Run - Min)	5565		
Conductor Size (Run - mm)	18 mm² to 24 mm²		
Conductor Size (Run)	556.5 556.5-18/1		
Conductor size (Tap - Max)	556.5-18/1		
Conductor size (Tap - Min)	5565		
Conductor Size (Tap)	556.5 556.5-18/1		
Conductor Type (Run)	ACSR AAC		
Wire Size	AWG		
Wire Size (Tap - Diameter - in)	0.722 to 0.95		
Wire Size (Tap - mm)	18 mm² to 24 mm²		
Wire Type (Tap)	ACSR AAC		
Physical			
Color Code	Yellow		
Approvals / Certifications			
UL Listed	No		
CSA Certified	No		
Other Features			
Installation Tool	WTY		
Booster	WPBY Box 25		
UPC	78181087440		
Keyw ord	w ejtap		