


163-47313-E



DC Jack 1.3mm x 3.8mm SMD/SMT



DIMENSIONS: mm

ELECTRICAL SPECIFICATIONS

Contact Resistance:	30mΩ Max.
Insulation Resistance:	100MΩ Min. at DC 500V
Dielectric Withstand Voltage:	AC 500V for 1 minute
RoHS Compliant	

No.	Description	Q'ty	Material	Finish
1	Housing	1	PA9T	Black Color
2	Pin (ø1.3)	1	Brass	Silver Plated
3	Pin Terminal	1	0.3T Bronze	Silver Plated
4	Break Terminal	1	0.2T Bronze	Silver Plated
5	Spring	1	0.3T Phosphor Bronze	Silver Plated

Date Last Revised: 07/18/12

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301430

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

163-47313-

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[163-47313-E](#)