


Aluminum Utility (1411 Series)


Natural aluminum with a smooth brushed finish and protective film...



Painted aluminum version...

KEY FEATURES

- .040" thick aluminum.
- Four self-tapping screws included.
- Unpainted or ASA 61 grey baked enamel finish (outside only).
- Unpainted version is protected through manufacturing and shipping with a plastic skin cover to ensure a high quality finish.
- Replacement screws 1421J6 (Pkg. of 6, 6-32 Philips head screws).



Part Number		Units	Dimensions		
Grey	Unpainted		A	B	C
1411B	1411BU	inch	2.7	2.2	1.6
		mm	69	56	41
1411C	1411CU	inch	3.2	2.2	1.1
		mm	81	56	28
1411D	1411DU	inch	3.2	2.2	1.6
		mm	81	56	41
1411G	1411GU	inch	4.0	2.2	1.6
		mm	102	56	41
1411H	1411HU	inch	4.0	2.2	2.2
		mm	102	56	56
1411F	1411FU	inch	4.0	2.2	3.0
		mm	102	56	76
1411K	1411KU	inch	5.0	2.2	2.2
		mm	127	56	56
1411N	1411NU	inch	5.0	3.0	2.2
		mm	127	76	56
1411L	1411LU	inch	5.0	4.0	3.0
		mm	127	102	76
1411M	1411MU	inch	6.0	3.0	3.0
		mm	152	76	76
1411P	1411PU	inch	6.0	5.0	4.0
		mm	152	127	102
1411Q	1411QU	inch	7.0	5.0	3.0
		mm	178	127	76
1411S	1411SU	inch	8.0	4.0	3.0
		mm	203	102	76
1411R	1411RU	inch	8.0	6.0	3.5
		mm	203	152	89
1411T	1411TU	inch	10.0	2.2	1.6
		mm	254	56	41
1411U	1411UU	inch	10.0	6.0	3.5
		mm	254	152	89
1411W	1411WU	inch	12.0	3.0	2.2
		mm	305	76	56
1411X	1411XU	inch	12.0	7.0	4.0
		mm	305	178	102
1411Z	1411ZU	inch	17.0	5.0	4.0
		mm	432	127	102

Metal