

- Replacement for PAR16 high voltage 50 W Halogen lamp
- Up to 85% energy saving
- Dimmable
- Lifetime of 35,000 hrs
- Built-in TCS (Temperature Control System)
- For accent lighting; ideal for spotlighting of various objects in shops, museums, restaurants etc.



Order Code 52023

General Data

Lamp Socket GU10
Design Lens

Geometric Data

Length (mm) 58
Diameter (mm) 48.5
Weight (g) 62

Electric Data

Wattage 6.5 W
Voltage 220-240 V
Power Factor ≥ 0.90
Operating Frequency 50/60 Hz

Photometric Data

Luminous Flux (lm) 300
CRI ≥ 80
CCT 4200 K – neutral white
Luminous Intensity (cd) 1250
Beam Angle (°) 25°
Lifetime 35 000hrs

Equivalent to (W) 50 W





Order Code

52023

Product Description

LED PAR16 GU10 6.5W 4200K NW 300LM DIM Box

Technical Packaging Details

Barcode	023942520238
EAN 128	(02)00023942520238(37)40(91)162
EAN 14	50023942520233
Pack Dimensions (HxWxL)	62 mm x 50 mm x 50 mm
Pack Weight	77 g
Carton Qty (Shipping Unit)	10
Carton Dimensions (HxWxL)	285 mm x 140 mm x 60 mm
Cartons/Layer	51
Layers/Pallet	6
Units/Pallet	2040

Photometric Diagram

52023