



Specifications

Base: Weight 80 gms/m²
Thickness: 0.0040" (0.1016mm)
Resistance: 1×10^4 to $< 1 \times 10^{11}$ ohms per ANSI/ESD STM11.11
Pink Stripe: Distinguishes dissipative paper from standard non-ESD paper
Class 10,000 cleanroom compatible

Made in Canada

"It should be understood that any object, item, material or person could be a source of static electricity in the work environment. Removal of unnecessary nonconductors, replacing nonconductive materials with dissipative or conductive materials and grounding all conductors are the principle methods of controlling static electricity in the workplace, regardless of the activity."
[ESD Handbook ESD TR20.20 section 2.4 Sources of Static Electricity]

Item	Description
16100	8.5" x 11", White, 500 sheets per pack

Unless otherwise noted, tolerance is $\pm 10\%$

Specifications and procedures subject to change without notice.

Static Dissipative Paper

DESCO

DESCO WEST: 3651 WALNUT AVE., CHINO, CA 91710 **WEB SITE:** Desco.com
PHONE (909) 627-8178
DESCO EAST: ONE COLGATE WAY, CANTON, MA 02021-1407
PHONE (781) 821-8370

DRAWING NUMBER
16100

DATE:
February
2014