

CARDMASTER ABS 17/16-L3



Order symbol: ABS 17/16-L3
Product nbr: 7585105
Description: Enclosure, ABS
Remarks: Smoked transparent hinged cover

EAN: 6418074056764
El. number:
Finland: 3438241
Denmark: 8212016758
Sweden: 7585105
Norway:

Including: Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Sample photo

Dimensions:				Rating:
Length	Width	Height		
mm: 188	160	106		Ingress Protection (EN 60529): IP 65
inch: 7.4	6.3	4.2		Impact Resistance (EN 62262): IK 07
Materials:				Electrical insulation: Totally insulated
Material: ABS				Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour: RAL 7035				Flammability Rating (UL 746 C 5): UL 94 HB
Cover colour: Smoked grey				Glow Wire Test (IEC 695-2-1) °C: 650
Gasket material: EPDM and Polyurethane				NEMA Class: NEMA 1, 3, 3R, 12, 13
Temperatures:				Certificates:
Short term: -40 ... 80 °C				Gost R
Continuous: -40 ... 60 °C				
Short term: -40 ... 175 °F				
Continuous: -40 ... 140 °F				
Accessories:				
MP 17/16	Mounting plate			
FP 17/16	Front plate (aluminium)			
FC PC 17/16	Frame of PC front plate			

CARDMASTER 166x160x80-106

