

Cup Thermo-Anemometer

Pocket size Air Velocity meter and Thermometer

With water resistant housing for outdoor use

Features:

- Rotating cups provide accurate air velocity measurements
- Wide range air velocity measures m/s, ft/min, MPH, km/h, and knots
- Dual LCD digital display of Air Velocity and Temperature
- Record Max and Min values
- Datalogger stores up to 100 readings
- Water resistant housing
- Complete with four AAA batteries



Water resistant housing - ideal for outdoor use

Measurement	Range	Resolution	Basic Accuracy
m/s	0.9 to 35.0 m/s	0.1 m/s	±(2% + 0.2 m/s)
km/h	2.5 to 126.0 km/h	0.1 km/h	±(2% + 0.8 km/h)
knots	1.4 to 68.0 knots	0.1 knots	±(2% + 0.4 Knots)
ft/min	144 to 6895 Ft/min	1 ft/min	±(2% + 40 ft/min)
MPH	1.6 to 78.2 MPH	0.1 MPH	±(2% + 0.4 MPH)
Temperature	32 to 122°F (0 to 50°C)	0.1°F/°C	±1.5°F (0.8°C)

Ordering Information:

AN400Cup Thermo-Anemometer

