

6-Outlet, 10-ft-Cord Surge Suppressor with Right-Angle Hospital-Grade Plug and Receptacles

MODEL NUMBER: **SPS610HGRA**



Description

Our SPS610HGRA surge suppressor provides 6 hospital-grade outlets and protection from damaging surges and spikes with the added benefit of a convenient right-angle hospital-grade plug. The new design provides another option for convenient outlets outside the patient care area, including those tight spaces.

Features

- 1050-joule AC surge suppression rating
- Rugged all-metal housing withstands years of use without loss of ground path continuity
- 6 NEMA5-15R Hospital-Grade AC outlets
- 10-ft. AC cord with integrated, molded right angle Hospital-Grade NEMA 5-15PHG plug
- Keyhole mounting tabs and flanges
- Switch safety cover prevents accidental shutoff
- 15A electrical capacity with built-in resettable circuit breaker
- 120 volt, 50/60Hz electrical compatibility
- Certified by UL (USA) and cUL (Canada)
- UL1449 3rd Edition listed

Specifications

General Info

Product Group	SURGE PROTECTORS
---------------	------------------

OVERVIEW

Intended Application	Hospital/Medical
----------------------	------------------

Highlights

- 6 hospital-grade outlets
- 1050 joule rating
- 10-ft. cord with molded right-angle hospital-grade plug
- All metal housing

Applications

- AC power distribution and surge suppression with hospital-grade receptacles and plug where durability and reliability are required. Not for use where NEC requires hospital-grade receptacles.

Package Includes

- SPS610HGRA Surge Suppressor
- Instruction manual with warranty information

Model Type	NOT For Patient Areas
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Circuit Breaker (amps)	15
Outlet Quantity / Type	6 NEMA 5-15R-HG
Number of Outlets	6
Transformer Accommodation	Supports 1 large transformer plug accessories without covering remaining outlets
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P-HG Hospital-Grade
Input Cord Length (ft.)	10
Input Cord Length (m)	4.6
Voltage Compatibility (VAC)	120
Maximum Surge Amps	19500
LEDS ALARMS & SWITCHES	
Diagnostic LEDs	LINE POWER PRESENT (green)
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1050
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode surge suppression
Clamping Voltage (RMS)	140V
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Shipping Dimensions (hwd / in.)	2.25 x 15 x 6
Shipping Dimensions (hwd / cm)	5.7 x 38.1 x 15.24
Shipping Weight (lbs.)	3.5

Shipping Weight (kg)	1.59
Unit Dimensions (hwd / in.)	1.5 x 13.75 x 2.5
Unit Dimensions (hwd / cm)	3.81 x 34.9 x 6.35
Unit Weight (lbs.)	3.2
Unit Weight (kg)	1.45
Material of Construction	Metal
Integrated Keyhole Mounting Tabs	Includes keyhole mounting tabs and flanges
Receptacle Color	White
Color (AC Line Cord)	Gray
Style	Strip
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition (Series Number: AGIB12015SL)
UL1363 (Power Tap)	UL1363 (Series Number: AGIB12015SL)
cUL / CSA (Canada)	cUL (Series Number: AGIB12015SL)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.