


SR25A 250W SOLDERING IRON



DATA SHEET


769-3151



Iron featured without bit

SPECIFICATIONS SR25A (ANGLED) 250WATT SOLDERING IRON

NOMINAL POWER (W)	250
STANDARD VOLTAGE	230
NOMINAL TIP TEMP (°C)	460
FITTED BIT (D.F.)	¾" (19mm)
CABLE LENGTH (m)	2.0
CABLE TYPE	Rubber with European plug
HANDLE MATERIAL	Wood
COUNTRY OF ORIGIN	U.K.
WEIGHT gms. (approx.)	950
DIMENSIONS (approx.)	A: (bit) 55mm. B: 230mm. C: 90mm. D: 325mm



TYPICAL APPLICATIONS:

Used particularly with higher temperature alloys on commutators. Also used for soldering cans, boxes, transformer casings, heat exchangers & radiators.