


# PVC insulated Flexible cable



## Technical & Specification

|                       |                                                                                |
|-----------------------|--------------------------------------------------------------------------------|
| Cross-section         | 0.75mm <sup>2</sup>                                                            |
| External Dia.         | ø2.2mm ±0.1                                                                    |
| Construction          | 96 x ø0.1mm                                                                    |
| Material:             |                                                                                |
| Conductor             | Cu blank                                                                       |
| Insulator             | PVC                                                                            |
| Jacket Color          | Black/White/Blue/<br>Red/Grey/Orange/<br>Green/Yellow/Violett/<br>Yellow+Green |
| Dielectric strength   | 1kv/ 1 minute                                                                  |
| Rated voltage         | <75VDC / 50VAC                                                                 |
| Conductor Resistance  | 26Ω/KM at 20°C                                                                 |
| Insulator Resistance  | 15MΩ/KM at 20°C                                                                |
| Flame Class           | 94V-2                                                                          |
| Operating Temperature | -10 ~ 70°C                                                                     |