







SIZE	Part Number	Jack Screw Thread	Packing
25	8655MH2501LF	UNC 4-40	bulk : Qty 60
	8655MH2511LF		individual set 50 sets/carton
	8655MH2502LF	M3	bulk : Qty 60
	8655MH2512LF		individual set 50 sets/carton

NOTE:RoHS INFORMATIONS

-The LF product meets European union Directives and other country regulations as described in GS-22-009

-The product is not intended to be exposed to a manufaturing solder process

-Packaging spec:see GS-14-920



NOTES : for every sizes

Material and finish : Zinc die-cast
nickel plated


Cable strain relief : Zinc die-cast

Jackscrew : Brass, nickel plated
UNC 4-40 or M3 (see tables)

Temperature range : -55°C to +125 °C

Attenuation factor : >40 dB between 10 MHz




Other size details : see on next pages.

spec ref		dr		A Parrenin	2009/05/20	projection 	mm 	size	A3	scale	3:2	
tolerance std ISO 406 ISO 1101	TOLERANCES UNLESS OTHERWISE SPECIFIED		eng	J Dalibard	2015/09/10			ecn no		ELX-B-20414-1		
			chr	J Dalibard	2015/09/10			rel level		Released		
			appr	Aymeric Soudy	2015/09/11			product family		-		
surface  ISO 1302	linear	0.X	±/		title	STRAIGHT METAL HOODS WITH 2 METAL CLAMPS		dwg no	C-8655-1685C		rev	D
		0.XX	±/									
		0.XXX	±/									
	angular	0°	±/°	www.fci.com	cat. no.	-	Product - Customer Drw		sheet 1 of 4			





Copyright FCI.

SIZE	Part Number	Jack Screw Thread	Packing
09	8655MH0901LF	UNC 4-40	bulk : Qty 80
	8655MH0911LF		individual set 50 sets/carton
	8655MH0902LF	M3	bulk : Qty 80
	8655MH0912LF		individual set 50 sets/carton



SIZE	Part Number	Jack Screw Thread	Packing
15	8655MH1501LF	UNC 4-40	bulk : Qty 80
	8655MH1511LF		individual set 50 sets/carton
	8655MH1502LF	M3	bulk : Qty 80
	8655MH1512LF		individual set 50 sets/carton





spec ref				dr		A Parrenin		2009/05/20		projection		mm		size		A3		scale		3:2					
tolerance std				TOLERANCES UNLESS OTHERWISE SPECIFIED								eng		J Dalibard		2015/09/10						ecn no		ELX-B-20414-1	
ISO 406												chr		J Dalibard		2015/09/10						ecp no		ELX-B-20414-1	
ISO 1101												appr		Aymeric Soudy		2015/09/11						product family		-	
surface						linear		0.X		±/				title		STRAIGHT METAL HOODS		dwg no		C-8655-1685C		rev			
ISO 1302								0.XX		±/															
ISO 1302								0.XXX		±/															
angular				0°		±/°		www.fci.com		cat. no.		-		Product - Customer Drw		sheet 2 of 4									





Copyright FCI.

SIZE	Part Number	Jack Screw Thread	Packing
37	8655MH3701LF	UNC 4-40	bulk : Qty 40
	8655MH3711LF		individual set 50 sets/carton
	8655MH3702LF	M3	bulk : Qty 40
	8655MH3712LF		individual set 50 sets/carton



PRODUCT WITH
M3 THREAD
JACKSCREWS

SIZE	Part Number	Jack Screw Thread	Packing
50	8655MH5001LF	UNC 4-40	bulk : Qty 40
	8655MH5011LF		individual set 50 sets/carton
	8655MH5002LF	M3	bulk : Qty 40
	8655MH5012LF		individual set 50 sets/carton




spec ref				dr	A Parrenin	2009/05/20	projection	mm	size	A3	scale	3:2
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	J Dalibard	2015/09/10			ecn no	ELX-B-20414-1		
				chr	J Dalibard	2015/09/10						
				ISO 406					appr	Aymeric Soudy	2015/09/11	product family
ISO 1101												

surface	✓	linear	0.X	±/		title	STRAIGHT METAL HOODS WITH 2 METAL CLAMPS		dwg no	C-8655-1685C		rev	D
			0.XX	±/									
			0.XXX	±/									
ISO 1302	angular		0°	±/°	www.fci.com	cat. no.	-	Product - Customer Drw			sheet 3 of 4		


CABLING INSTRUCTIONS

1- Strip the cable and solder or crimp the wires




SCALE 3:2

2-Put the connector into a half hood and tighten the jacket with a metal clamp




SCALE 3:2

3-To get the electrical continuity between the cable outer conductor and the hood tighten the outer conductor with the other metal clamp as shown



SCALE 3:2

4-Mount the jackscrews, the other half hood and tighten with 2 screws



Copyright FCI.

spec ref		dr		A Parrenin	2009/05/20	projection 	mm 	size	A3	scale	1:1
tolerance std ISO 406 ISO 1101	TOLERANCES UNLESS OTHERWISE SPECIFIED	eng	J Dalibard	2015/09/10	ecn no			ELX-B-20414-1			
		chr	J Dalibard	2015/09/10	rel level			Released			
		appr		Aymeric Soudy	2015/09/11	product family					
surface ISO 1302	linear	0.X	±/		title	STRAIGHT METAL HOODS WITH 2 METAL CLAMPS		dwg no	C-8655-1685C		rev D
		0.XX	±/								
		0.XXX	±/								
	angular	0°	±/°	www.fci.com	cat. no.	Product - Customer Drw			sheet 4 of 4		