

Search Results

- Evaluate
  - FAQ's
- How to Buy
  - Bill of Material
  - Favorite Products List
  - Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click  to remove) Search Tips 

Text Search: 'FZOD3-3M3'

Your search criteria matched only one product, shown below

FZOD3-3M3



- Patch cords are tested to support network transmission speeds up to 10 Gb/s for link lengths up to 550 meters with an 850nm source per IEEE 802.3ae 10 GbE standard
- Pass all TIA/EIA-568-B.3 performance requirements
- Insertion loss per connection: 0.10dB typical; 0.30dB maximum
- Backward compatible for use with all 50/125µm system requirements
- Factory terminated and 100% tested for insertion loss
- Insertion loss data recorded for every multimode patch cord
- Lifetime traceability of test data to a Q.C. number on each patch cord
- SC Duplex Patch Cords include SC Duplex Clips to maintain polarity
- Highest quality flame retardant fiber optic cable with tight-buffered coating on each optical fiber

Additional lengths and availability: Patch cords are available in 1 – 10 meter lengths in 1 meter increments, and 15, 20, 25 and 30 meter lengths. Pigtails are available in 1, 2, and 3 meter lengths. Ex: To order lengths other than 1 meter, replace the 1 after the M (FZPE10-10M1) with the desired length (FZPE10-10M2 for 2 meter length). The above lengths are stock items. For other lengths, contact Customer Service for actual lead times.

▪ Part Number	FZOD3-3M3
▪ RoHS Compliance Status	RoHS directive is not applicable
▪ Note	Intended for use in fixed installations which are outside the scope of RoHS
▪ Part Description	SC to SC Patch Cord, Optimized OM4, RISER, 0.15 dB IL Loss, Duplex, 3.0mm jacketed cable – 3m.
▪ Product Type	SC Patch Cords
▪ Color	Aqua
▪ Length (m)	3
▪ Fiber Compatibility	10 GbE 50/125µ
▪ Fiber Cable Size	3.0mm
▪ Fiber Cable Type	Jacketed Cable
▪ Fiber Type	Multimode
▪ Connector 1 Type	SC Connector
▪ Connector 2 Type	SC Connector
▪ End Configurations	SC to SC
▪ Fiber Count	2
▪ Flammability Rating	Riser (OFNR)
▪ Pricing Description	SC to SC, Optimized OM4, RISER, Duplex, 3.0mm jacketed cable, 3M
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.