



General ordering data

Order No.	1793090000
Part designation	BCZ 3.81/8/180F SN GN
Version	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 8, 180°, Box
EAN	4032248227174
Qty.	50 pc(s).

System parameters

Conductor connection system	Clamping yoke connection
Outgoing direction of conductor	180°
Pitch	3.81 mm
Pitch in inch	0.15 inch
No. of poles	8
No. of rows	1
Screwdriver blade	0.4 x 2.5
Screwdriver blade standard	DIN 5264
Tightening torque, min.	0.2
Tightening torque, max.	0.25 Nm
Clamping screw	M 2
Stripping length	7 mm
L1 in mm	26.67 mm
L1 in inch	1.05 inch
Electric shock protection to DIN VDE 0470	IP 20
Electric shock protection to DIN VDE 0470	Safe from finger touch

Material data

Insulating material	PA GF
Colour	Pale green
colour chart	Similar to RAL 6021
Insulating material group	II
Flammability class UL 94	V-0
CTI	>= 475

Material data

Contact base material	Copper alloy
Contact surface	tinned

Connectable conductors

Clamping range, min.	0.08 mm ²
Clamping range, max.	1.5 mm ²
AWG, min.	28
AWG, max.	16
Solid, min. H05(07) V-U	0.2 mm ²
Solid, max. H05(07) V-U	1.5 mm ²
Flexible, min. H05(07) V-K	0.2 mm ²
Flexible, max. H05(07) V-K	1.5 mm ²
With wire end ferrule, acc. to DIN 46 228/1, min.	0.2 mm ²
With wire end ferrule, acc. to DIN 46 228/1, max.	1.5 mm ²
w. plastic collar ferrule, DIN 46228 pt 4, min.	0.2 mm ²
w. plastic collar ferrule, DIN 46228 pt 4, max.	1.5 mm ²
Gauge to EN 60999 a x b; ø	2.4 mm x 1.5 mm ; 2.4 mm

DIN IEC rating data

Rated current, min. No. pins (Tu=20°C)	17.5 A
Rated current, min. No. pins (Tu=40°C)	17.5 A
Rated voltage for overvoltage class/pollution severity II/2	320 V
Rated voltage for overvoltage class/pollution severity III/2	160 V
Rated voltage for overvoltage class/pollution severity III/3	160 V
Rated impulse withstand voltage for overvoltage class/pollution severity II/2	2.5 kV
Rated impulse withstand voltage for overvoltage class/pollution severity III/2	2.5 kV
Rated impulse withstand voltage for overvoltage class/pollution severity III/3	2.5 kV
Short-time withstand current resistance	3 x 1s with 76 A

CSA rating data

Rated voltage (Use group D)	300 V
Rated current (Use group D)	10 A
AWG conductor (field wiring), min.	28
AWG conductor (field wiring), max.	16

UL 1059 rating data

Rated voltage (Use group D)	300 V
Rated current (Use group D)	10 A
AWG conductor, min.	28
AWG conductor, max.	16

Approvals

Approvals institutes



Classifications

ETIM 2.0	NK
ETIM 3.0	EC001284
eClass 4.1	27-26-07-01
eClass 5.0	27-26-07-01
eClass 5.1	27-26-07-04

Similar products

Order No.	Part designation	Version
1941010000	BCZ 3.81/2/180F SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 2, 180°, Box
1792950000	BCZ 3.81/2/180F SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 2, 180°, Box
1793040000	BCZ 3.81/2/180F SN GN	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 2, 180°, Box
1941020000	BCZ 3.81/3/180F SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 3, 180°, Box
1792960000	BCZ 3.81/3/180F SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 3, 180°, Box
1793050000	BCZ 3.81/3/180F SN GN	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 3, 180°, Box
1941030000	BCZ 3.81/4/180F SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 4, 180°, Box
1792970000	BCZ 3.81/4/180F SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 4, 180°, Box
1793060000	BCZ 3.81/4/180F SN GN	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 4, 180°, Box
1941040000	BCZ 3.81/5/180F SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 5, 180°, Box
1792980000	BCZ 3.81/5/180F SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 5, 180°, Box

1793070000	BCZ 3.81/5/180F SN GN	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 5, 180°, Box
1941050000	BCZ 3.81/6/180F SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 6, 180°, Box
1792990000	BCZ 3.81/6/180F SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 6, 180°, Box
1793080000	BCZ 3.81/6/180F SN GN	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 6, 180°, Box
1941060000	BCZ 3.81/7/180F SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 7, 180°, Box
1837020000	BCZ 3.81/7/180F SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 7, 180°, Box
1941260000	BCZ 3.81/7/180F SN GN	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 7, 180°, Box
1941070000	BCZ 3.81/8/180F SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 8, 180°, Box
1793000000	BCZ 3.81/8/180F SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 8, 180°, Box
1941080000	BCZ 3.81/9/180F SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 9, 180°, Box
1899530000	BCZ 3.81/9/180F SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 9, 180°, Box
1941270000	BCZ 3.81/9/180F SN GN	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 9, 180°, Box
1941090000	BCZ 3.81/10/180F SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 10, 180°, Box
1793010000	BCZ 3.81/10/180F SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 10, 180°, Box
1793100000	BCZ 3.81/10/180F SN GN	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 10, 180°, Box
1941100000	BCZ 3.81/11/180F SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 11, 180°, Box
1899550000	BCZ 3.81/11/180F SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 11, 180°, Box

1941280000	BCZ 3.81/11/180F SN GN	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 11, 180°, Box
1941110000	BCZ 3.81/12/180F SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 12, 180°, Box
1793020000	BCZ 3.81/12/180F SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 12, 180°, Box
1793110000	BCZ 3.81/12/180F SN GN	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 12, 180°, Box
1941120000	BCZ 3.81/13/180F SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 13, 180°, Box
1899570000	BCZ 3.81/13/180F SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 13, 180°, Box
1941290000	BCZ 3.81/13/180F SN GN	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 13, 180°, Box
1941130000	BCZ 3.81/14/180F SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 14, 180°, Box
1899590000	BCZ 3.81/14/180F SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 14, 180°, Box
1941300000	BCZ 3.81/14/180F SN GN	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 14, 180°, Box
1941140000	BCZ 3.81/15/180F SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 15, 180°, Box
1899610000	BCZ 3.81/15/180F SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 15, 180°, Box
1941310000	BCZ 3.81/15/180F SN GN	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 15, 180°, Box
1941150000	BCZ 3.81/16/180F SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 16, 180°, Box
1793030000	BCZ 3.81/16/180F SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 16, 180°, Box
1793120000	BCZ 3.81/16/180F SN GN	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 16, 180°, Box
1941160000	BCZ 3.81/17/180F SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 17, 180°, Box

1941360000	BCZ 3.81/17/180F SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 17, 180°, Box
1941320000	BCZ 3.81/17/180F SN GN	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 17, 180°, Box
1941170000	BCZ 3.81/18/180F SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 18, 180°, Box
1941370000	BCZ 3.81/18/180F SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 18, 180°, Box
1941330000	BCZ 3.81/18/180F SN GN	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 18, 180°, Box
1941180000	BCZ 3.81/19/180F SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 19, 180°, Box
1941380000	BCZ 3.81/19/180F SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 19, 180°, Box
1941340000	BCZ 3.81/19/180F SN GN	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 19, 180°, Box
1941190000	BCZ 3.81/20/180F SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 20, 180°, Box
1941390000	BCZ 3.81/20/180F SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 20, 180°, Box
1941350000	BCZ 3.81/20/180F SN GN	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 20, 180°, Box